

## 20V P-Channel Enhancement-Mode MOSFET

**V<sub>DS</sub>** = -20V

R<sub>DS(ON)</sub>, V<sub>GS</sub>@-4.5V, I<sub>DS</sub>@-2.8A = 100 mΩ

R<sub>DS(ON)</sub>, V<sub>GS</sub>@-2.5V, I<sub>DS</sub>@-2.0A = 150 mΩ

### Features

Advanced trench process technology

High Density Cell Design For Ultra Low On-Resistance



Fully Characterized Avalanche Voltage and Current

Improved Shoot-Through FOM

we declare that the material of product  
compliance with RoHS requirements.

S- Prefix for Automotive and Other Applications Requiring  
Unique Site and Control Change Requirements; AEC-Q101  
Qualified and PPAP Capable.

**LP4101LT1G**  
**S-LP4101LT1G**



### ▼ Simple Drive Requirement

### ▼ Small Package Outline

### ▼ Surface Mount Device

### Ordering Information

Device	Marking	Shipping
LP4101LT1G S-LP4101LT1G	P41	3000/Tape & Reel
LP4101LT3G S-LP4101LT3G	P41	10,000/Tape & Reel

### Maximum Ratings and Thermal Characteristics (T<sub>A</sub> = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V <sub>DS</sub>	-20	V
Gate-Source Voltage	V <sub>GS</sub>	± 8	
Continuous Drain Current	I <sub>D</sub>	-2.3	A
Pulsed Drain Current 1)	I <sub>DM</sub>	-8	
Maximum Power Dissipation	P <sub>D</sub>	0.9	W
		0.57	
Operating Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-55 to 150	°C
Junction-to-Case Thermal Resistance	R <sub>qJC</sub>		°C/W
Junction-to-Ambient Thermal Resistance (PCB mounted) <sup>2)</sup>	R <sub>qJA</sub>	140	

Note: 1. Repetitive Rating: Pulse width limited by the Maximum junction temperature

2. 1-in<sup>2</sup> 2oz Cu PCB board



3. Guaranteed by design; not subject to production testing

# LP4101LT1G , S-LP4101LT1G

## ELECTRICAL CHARACTERISTICS


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
<b>Static</b>						
Drain-Source Breakdown Voltage	$BV_{DSS}$	$V_{GS} = 0V, I_D = -250\mu A$	-20	-	-	V
Drain-Source On-State Resistance	$R_{DS(on)}$	$V_{GS} = -4.5V, I_D = -2.8A$		69	100	$m\Omega$
Drain-Source On-State Resistance	$R_{DS(on)}$	$V_{GS} = -2.5V, I_D = -2.0A$		83	150	$m\Omega$
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -250\mu A$	-0.45		-0.95	V
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS} = -9.6V, V_{GS} = 0V$			-1	$\mu A$
Gate Body Leakage	$I_{GSS}$	$V_{GS} = \pm 8V, V_{DS} = 0V$			$\pm 100$	$nA$
Gate Resistance	$R_g$					$\Omega$
Forward Transconductance	$g_{fs}$	$V_{DS} = -5V, I_D = -4.0A$		6.5		S
<b>Dynamic <sup>3)</sup></b>						
Total Gate Charge	$Q_g$	$V_{DS} = -6V, I_D = -2.8A$ $V_{GS} = -4.5V$		15.23		nC
Gate-Source Charge	$Q_{gs}$			5.49		
Gate-Drain Charge	$Q_{gd}$			2.74		
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = -6V, R_L = 6\Omega$ $I_D = -1A, V_{GEN} = -4.5V$ $R_G = 6\Omega$		17.28		ns
Turn-On Rise Time	$t_r$			3.73		
Turn-Off Delay Time	$t_{d(off)}$			36.05		
Turn-Off Fall Time	$t_f$			6.19		
Input Capacitance	$C_{iss}$	$V_{DS} = -6V, V_{GS} = 0V$ $f = 1.0 \text{ MHz}$		882.51		pF
Output Capacitance	$C_{oss}$			145.54		
Reverse Transfer Capacitance	$C_{rss}$			97.26		
<b>Source-Drain Diode</b>						
Max. Diode Forward Current	$I_s$				-2.4	A
Diode Forward Voltage	$V_{SD}$	$I_s = -0.75A, V_{GS} = 0V$		-0.8	-1.2	V

Note: Pulse test: pulse width <= 300us, duty cycle <= 2%




## LP4101LT1G , S-LP4101LT1G


### TYPICAL ELECTRICAL CHARACTERISTICS




**Figure 1. Transfer Characteristics**



**Figure 2. On-Region Characteristics**




**Figure 3. On-Resistance versus Drain Current**




**Figure 4. On-Resistance vs. Gate-to-Source Voltage**


**LP4101LT1G , S-LP4101LT1G**  
**TYPICAL ELECTRICAL CHARACTERISTICS**




**Figure 5. Gate Charge**




**Figure 6. Capacitance**



**Figure 7. On-Resistance Vs.Junction Temperature**



**Figure 8. V<sub>th</sub> Vs.Junction Temperature**

**LP4101LT1G , S-LP4101LT1G**
**SOT-23**

**NOTES:**

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M,1982
2. CONTROLLING DIMENSION: INCH.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.1102	0.1197	2.80	3.04
B	0.0472	0.0551	1.20	1.40
C	0.0350	0.0440	0.89	1.11
D	0.0150	0.0200	0.37	0.50
G	0.0701	0.0807	1.78	2.04
H	0.0005	0.0040	0.013	0.100
J	0.0034	0.0070	0.085	0.177
K	0.0140	0.0285	0.35	0.69
L	0.0350	0.0401	0.89	1.02
S	0.0830	0.1039	2.10	2.64
V	0.0177	0.0236	0.45	0.60

