

WL2808E

Low noise, High PSRR, High speed, CMOS LDO

[Http://www.sh-willsemi.com](http://www.sh-willsemi.com)

Descriptions


The WL2808E series is a high accuracy, low noise, high speed, low dropout CMOS Linear regulator with high ripple rejection. The devices offer a new level of cost effective performance in cellular phones, laptop and notebook computers, and other portable devices.



SOT-23-5L

The current limiter's fold-back circuit also operates as a short circuit protection and an output current limiter at the output pin.


The WL2808E regulators are available in standard SOT-23-5L packages. Standard products are Pb-free and Halogen-free.



Features

- Input voltage : 2.5V~5.5V
- Output range : 1.2V~3.3V
- Output current : 200mA (@V_{OUT}<2V)(Typ.)
- 300mA (@V_{OUT}>2V)(Typ.)
- PSRR : 75dB @ 217Hz
- Dropout voltage : 170mV @ I_{OUT}=200mA
- Quiescent current : 30µA Typ.
- Shut-down current : < 1µA
- Recommend capacitor : 1uF

Pin Configuration (Top View)



For detail marking information, please see page 8.

Marking


Applications

- MP3/MP4 Players
- Cellphones, radiophone, digital cameras
- Bluetooth, wireless handsets
- Others portable electronics device

Order Information

For detail order information, please see page 8.


Typical Application



Pin Description

PIN	Symbol	Description
1	VIN	Input
2	GND	Ground
3	EN	Enable (Active high)
4	NC	Not connected
5	VOUT	Output

Block Diagram



Absolute Maximum Ratings

Parameter	Value	Unit
Power Dissipation	Internal limited	mW
V_{IN} Range	-0.3~6.5	V
V_{EN} Range	-0.3~ V_{IN}	V
V_{OUT} Range	-0.3~ V_{IN}	V
Lead Temperature Range	260	°C
Storage Temperature Range	-55 ~ 150	°C
Operating Junction Temperature Range	150	°C


Recommend Operating Ratings

Parameter	Value	Unit
Operating Supply voltage	2.5~5.5	V
Operating Temperature Range	-40~85	°C
Thermal Resistance, $R_{\theta,JA}$	250	°C/W


Electronics Characteristics (Ta=25°C, $V_{IN}=V_{OUT}+1V$, $C_{IN}=C_{OUT}=1\mu F$, unless otherwise noted)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Output Voltage	V_{OUT}	$V_{OUT} < 2V$, $V_{IN}=2.7V$, $I_{OUT}=1mA$	0.97 V_{OUT}	V_{OUT}	1.03 V_{OUT}	V
		$V_{OUT} \geq 2V$, $I_{OUT}=1mA$	0.98 V_{OUT}	V_{OUT}	1.02 V_{OUT}	
Current Limit	I_{LIM}	$V_{EN}=V_{IN}$	Ref. to Output Voltage vs. Output Current Chart		mA	
Dropout Voltage	V_{DROP}	$V_{OUT}=2.8V$, $I_{OUT}=200mA$		170	200	mV
		$V_{OUT}=2.8V$, $I_{OUT}=300mA$		250	300	
Line Regulation	ΔV_{LINE}	$V_{IN}=2.7\sim 5.5V$, $I_{OUT}=1mA$		0.01	0.15	%/V
Load Regulation	ΔV_{Load}	$V_{OUT}=2.8V$, $I_{OUT}=1\sim 300mA$		20	35	mV
Quiescent Current	I_Q	$V_{OUT}=2.8V$, $I_{OUT}=0$		30	50	μA
Short Current	I_{SHORT}	$V_{EN}=V_{IN}$, V_{OUT} Short to GND with 1Ω		90		mA
Shut-down Current	I_{SHDN}	$V_{EN}=0V$			1.0	μA
Power Supply Rejection Rate	$PSRR$	$V_{IN}=(V_{OUT}+1V)_{DC}+0.5V_{P-P}$ $F=217Hz$, $I_{OUT}=10mA$		75		dB
		$V_{IN}=(V_{OUT}+1V)_{DC}+0.5V_{P-P}$ $F=10KHz$, $I_{OUT}=10mA$		65		
EN logic high voltage	V_{ENH}	$V_{IN}=5.5V$, $I_{OUT}=1mA$	1.2			V
EN logic low voltage	V_{ENL}	$V_{IN}=5.5V$, $V_{OUT}=0V$			0.4	V
EN Input Current	I_{EN}	$V_{EN}=0$ to $5.5V$			1.0	μA
Output Noise Voltage	e_{NO}	10Hz to 100KHz, $C_{OUT}=1\mu F$		100		μV_{RMS}


Typical characteristics (Ta=25°C, V_{IN}=3.8V, V_{OUT} = 2.8V C_{IN}=C_{OUT}=1uF, unless otherwise noted)




Quiescent current vs. Supply voltage




Quiescent current vs. Supply voltage




Output voltage vs. Supply voltage









Output voltage vs. Supply voltage








Output voltage vs. Output current



Output voltage vs. Output current





PSRR


ORDER INFORMATION




Ordering No.	Vout (V)	Package	Operating Temperature	Marking	Shipping
WL2808E12-5/TR	1.2	SOT-23-5L	-40~+85°C	WL12 EYWW	Tape and Reel, 3000
WL2808E15-5/TR	1.5	SOT-23-5L	-40~+85°C	WLBF EYWW	Tape and Reel, 3000
WL2808E18-5/TR	1.8	SOT-23-5L	-40~+85°C	WLBJ EYWW	Tape and Reel, 3000
WL2808E25-5/TR	2.5	SOT-23-5L	-40~+85°C	WLCF EYWW	Tape and Reel, 3000
WL2808E28-5/TR	2.8	SOT-23-5L	-40~+85°C	WL28 EYWW	Tape and Reel, 3000
WL2808E30-5/TR	3.0	SOT-23-5L	-40~+85°C	WLDA EYWW	Tape and Reel, 3000
WL2808E33-5/TR	3.3	SOT-23-5L	-40~+85°C	WLDD EYWW	Tape and Reel, 3000

Marking:

WL** = Device Code
Y = Year

PACKAGE OUTLINE DIMENSIONS
SOT-23-5L


Symbol	Dimensions in Millimeters		
	Min.	Typ.	Max.
A	-	-	1.45
A1	0.00	-	0.15
A2	0.90	1.10	1.30
b	0.30	0.40	0.50
c	0.10	-	0.21
D	2.72	-	3.05
E	2.60	2.80	3.00
E1	1.40	1.60	1.80
e	0.95 BSC		
e1	0.95 BSC		
L	0.30	-	0.60
θ	8 ° Ref.		

TAPE AND REEL INFORMATION
Reel Dimensions

Tape Dimensions

Quadrant Assignments For PIN1 Orientation In Tape


RD	Reel Dimension	<input checked="" type="checkbox"/> 7inch	<input type="checkbox"/> 13inch
W	Overall width of the carrier tape	<input checked="" type="checkbox"/> 8mm	<input type="checkbox"/> 12mm <input type="checkbox"/> 16mm
P1	Pitch between successive cavity centers	<input type="checkbox"/> 2mm	<input checked="" type="checkbox"/> 4mm <input type="checkbox"/> 8mm
Pin1	Pin1 Quadrant	<input type="checkbox"/> Q1	<input type="checkbox"/> Q2 <input checked="" type="checkbox"/> Q3 <input type="checkbox"/> Q4