# Switching (-20V, -2.5A)

# RTR025P02

#### Features

- 1) Low On-resistance.
- 2) Built-in G-S Protection Diode.
- 3) Small and Surface Mount Package (TSMT3).

# Application

Power switching, DC / DC converter.

# ●Structure

Silicon P-channel MOS FET

# Packaging specifications

	Package	Taping
Type	Code	TL
	Basic ordering unit (pieces)	3000
RTR025P02		0

# ● Absolute maximum ratings (Ta=25°C)


Parameter		Symbol	Limits	Unit	
Drain-source voltage		$V_{DSS}$	-20	V	
Gate-source voltage		Vgss	±12	V	
Drain current	Continuous	ID	±2.5	Α	
	Pulsed	IDP *1	±10	Α	
Source current	Continuous	Is	-0.8	Α	
(Body diode)	Pulsed	Isp *1	-3.2	Α	
Total power dissipation		P <sub>D</sub> *2	1.0	W	
Channel temperature		Tch	150	°C	
Range of Storage temperature		Tstg	-55 to +150	°C	
·					

<sup>\*1</sup> Pw≤10μs, Duty cycle≤1% \*2 Mounted on a ceramic board


# ●Thermal resistance (Ta=25°C)

Parameter	Symbol	Limits	Unit
Channel to ambient	Rth (ch-A)	125	°C / W

# ●External dimensions (Unit : mm)



#### ●Equivalent circuit



# ●Electrical characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions	
Gate-source leakage	Igss	-	_	±10	μΑ	Vgs=±12V, Vps=0V	
Drain-source breakdown voltage	V <sub>(BR) DSS</sub>	-20	_	_	V	I <sub>D</sub> = -1mA, V <sub>GS</sub> =0V	
Zero gate voltage drain current	IDSS	_	_	-1	μΑ	V <sub>DS</sub> = -20V, V <sub>GS</sub> =0V	
Gate threshold voltage	V <sub>GS (th)</sub>	-0.7	_	-2.0	٧	V <sub>DS</sub> = -10V, I <sub>D</sub> = -1mA	
Static drain-source on-state resistance	R <sub>DS (on)</sub> *	-	70	95	mΩ	I <sub>D</sub> = -2.5A, V <sub>GS</sub> = -4.5V	
		_	75	105	mΩ	I <sub>D</sub> = -2.5A, V <sub>G</sub> S= -4.0V	
		-	115	160	mΩ	I <sub>D</sub> = -1.25A, V <sub>G</sub> S= -2.5V	
Forward transfer admittance	Y <sub>fs</sub> *	2.3	_	_	S	V <sub>DS</sub> = -10V, I <sub>D</sub> = -1.2A	
Input capacitance	Ciss	_	630	_	pF	V <sub>DS</sub> = -10V	
Output capacitance	Coss	_	110	_	pF	V <sub>GS</sub> =0V	
Reverse transfer capacitance	Crss	-	75	_	pF	f=1MHz	
Turn-on delay time	<b>t</b> d (on) *	_	12	_	ns	I <sub>D</sub> = -1.25A	
Rise time	tr *	-	18	_	ns	V <sub>DD</sub> = −15V V <sub>GS</sub> = −4.5V R <sub>I</sub> =12Ω	
Turn-off delay time	td (off) *	-	50	_	ns		
Fall time	t <sub>f</sub> *	-	20	_	ns	Rgs=10Ω	
Total gate charge	Qg	-	7	_	nC	V <sub>DD</sub> ≒−15V	
Gate-source charge	Qgs	_	1.5	_	nC	Vgs=-4.5V	
Gate-drain charge	Qgd	-	2.0	_	nC	ID=-2.5A	

\*Pulsed

Body diode characteristics (source-drain characteristics)

# Electrical characteristic curves




Fig.1 Typical Transfer Characteristics




Fig.2 Static Drain-Source On-State Resistance vs. Drain Current




Fig.3 Static Drain-Source On-State Resistance vs. Drain Current




Fig.4 Static Drain-Source On-State Resistance vs. Drain Current




Fig.5 Static Drain-Source On-State Resistance vs. Drain Current




Fig.6 Reverse Drain Current vs.Source-Drain Voltage




Fig.7 Typical Capacitance vs. Drain-Source Voltage




Fig.8 Switching Characteristics




Fig.9 Dynamic Input Characteristics

# ●Measurement circuits




Fig.10 Switching Time Test Circuit




Fig.11 Switching Time Waveforms




Fig.12 Gate Charge Test Circuit




Fig.13 Gate Charge Waveform

# Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any
  means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the
  product described in this document are for reference only. Upon actual use, therefore, please request
  that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard
  use and operation. Please pay careful attention to the peripheral conditions when designing circuits
  and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or
  otherwise dispose of the same, no express or implied right or license to practice or commercially
  exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

# About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.

