







REV.	ECR/N NO./DESCRIPTION	DATE	DRAWN	CHECKED	APPROVE
I	RD140**	08/15'15	XU	Vito	Barney
J	RD140**	10/27'15	XU	Vito	Barney
K	RD140**	01/14'16	MENG	Vito	Barney



SEE DETAIL A

SEE DETAIL B



HOW TO MATE AND UNMATE
MATE: ① → ④
UNMATE: ⑤ → ⑦
SCALE 2:1

GENERAL TOLERANCES UNLESS SPECIFIED		PART NO. SEE TABLE		LOTES		
X ± 0.35	X° ± 3°	APPROVED BY Barney		TITLE SODDR4 8.0H 260 PIN RVS TYPE		
.XX ± 0.25	X° ± 2°	CHECKED BY Vito		DWG NO. AP-ADDR0070		
.XXX ± 0.15	.XX° ± 1°	DRAWN BY XU				
CUSTOMER DRAWING						
SIZE A4	UNITS MM[INCH]					

1.MATERIALS:

HOUSING: LCP,UL 94V-0.

CONTACT: BRASS C2680.

LATCH: STAINLESS STEEL SUS301.

2.FINISH:

1)CONTACT:UNDERPLATED NICKEL 50~150u",
PLATING ON SOLDER AREA:SEE TABLE

GOLD PLATING ON CONTACT AREA:SEE TABLE

2)LATCH:UNDERPLATED NICKEL 50~150u",MATTE TIN 80u" MIN.

3.ELECTRICAL PERFORMANCE

LLCR INITIAL 50mΩ MAX PER CONTACT.

FINAL $\Delta LCR=20\text{m}\Omega$ MAX

4.MECHANICAL PERFORMANCE.

MATING & UNMATING FORCE: 6.1 Kgf MAX.

5.IR REFLOW:

THE PEAK TEMPRATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 250±10°C.

6. DC: XXXXXX

-DATE

- WEEK

-YEAR

7.PRODUCT NUMBER NOTE:ADDR****_*****

- PACKING DIRECTION

- TYPE SERIAL NUMBER

- HALOGEN FREE

-PRODUCT SERIAL NUMBER

-PRODUCT TYPE

-CONNECTOR

8.RoHS COMPLIANT.

HF COMPLIANT.









TABLE:

NO.	PART NO.	COLOR	DESCRIPTION
1	ADDR0070-P004A	BLACK	GOLD G/F ON CONTACT AREA
			MATTE TIN ON SOLDER AREA
2	ADDR0070-P007A	BLACK	GOLD 10u" ON CONTACT AREA
			MATTE TIN ON SOLDER AREA
3	ADDR0070-P005A	BLACK	GOLD 15u" ON CONTACT AREA
			MATTE TIN ON SOLDER AREA
4	ADDR0070-P006A	BLACK	GOLD 30u" ON CONTACT AREA
			MATTE TIN ON SOLDER AREA
5	ADDR0070-P009A	BLACK	GOLD G/F ON CONTACT AREA
			GOLD G/F ON SOLDER AREA
6	ADDR0070-P010A	BLACK	GOLD 10u" ON CONTACT AREA
			GOLD G/F ON SOLDER AREA
7	ADDR0070-P011A	BLACK	GOLD 15u" ON CONTACT AREA
			GOLD G/F ON SOLDER AREA
8	ADDR0070-P012A	BLACK	GOLD 30u" ON CONTACT AREA
			GOLD G/F ON SOLDER AREA
9	ADDR0070-P014A	WHITE	GOLD G/F ON CONTACT AREA
			GOLD G/F ON SOLDER AREA
10	ADDR0070-P015A	WHITE	GOLD 10u" ON CONTACT AREA
			GOLD G/F ON SOLDER AREA
11	ADDR0070-P016A	WHITE	GOLD 15u" ON CONTACT AREA
			GOLD G/F ON SOLDER AREA
12	ADDR0070-P017A	WHITE	GOLD 30u" ON CONTACT AREA
			GOLD G/F ON SOLDER AREA

GENERAL TOLERANCES UNLESS SPECIFIED		PART NO.	LOTES			
X ± 0.35	X.° ± 3°	SEE TABLE				
.XX ± 0.25	X.° ± 2°	APPROVED BY	TITLE SODDR4 8.0H 260 PIN RVS TYPE			
.XXX ± 0.15	.XX° ± 1°	Barney				
CUSTOMER DRAWING		CHECKED BY	DWG NO. AP-ADDR0070			
		Vito				
SIZE	UNITS	DRAWN BY		SHEET	SCALE	REV
A4	MM[INCH]	XU		2 / 5	5 : 4	K





- NOTES:
- MATERIAL :
 - CARRY TAPE: PS
 - COVER TAPE: PET
 - SHIPPING CARTON: CORRUGATED FIBER
 - DIMENSION :
 - REEL: W=88.0, $\phi A=380$
 - SHIPPING CARTON: L=388, W=388, H=317 (INNER)
 - QUANTITY :
 - PRIMARY PACKING: 270 PCS/REEL
 - SECONDARY PACKING: 3 REELS/CARTON(810PCS)
 - PEELING RESISTANCE: 20gf~120gf.
 - PEELING SPEED: 300mm/minutes.

GENERAL TOLERANCES UNLESS SPECIFIED		PART NO. SEE TABLE	LOTES			
X ± 0.35	X° ± 3°					
.XX ± 0.25	X° ± 2°	APPROVED BY Barney	TITLE SODDR4 8.0H 260 PIN RVS TYPE			
.XXX ± 0.15	.XX° ± 1°					
CUSTOMER DRAWING		CHECKED BY Vito	DWG NO. AP-ADDR0070			
SIZE	UNITS					
A4	MM	DRAWN BY XU		SHEET 5 / 5	SCALE N/A	REV K