



LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-15-014342	07OCT2015	NK	RH

1 HARDWARE SUPPLIED WITH THREADED-BUSHING
PARTS ONLY: TE P/N 2213733-1 (NUT) X2
P/N 2213733-2 (LOCKING WASHER) X1




MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	OFF	ON
TERM. COMM.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267079-6

GOLD	ON-OFF-ON	PC THROUGH-HOLE	VERTICAL	1	2	TMS3T3B1M2RE	2267079-6
SILVER	ON-ON	SOLDER LUG	VERTICAL	2	2	TMD1T3B1M1QE	2267079-5
SILVER	ON-OFF-ON	SOLDER LUG	VERTICAL	1	2	TMS3T3B1M1QE	2267079-4
SILVER	ON-ON	SOLDER LUG	VERTICAL	1	2	TMS1T3B1M1QE	2267079-3
SILVER	OFF-ON	SOLDER LUG	VERTICAL	1	2	TMS6T3B1M1QE	2267079-2
GOLD	ON-ON	WIRE WRAP	VERTICAL	1	2	TMS1T3B1M5RE	2267079-1
CONTACT MATERIAL	FUNCTION	TERMINATION	MOUNT ANGLE	POLES	THROWS	DESCRIPTIVE PN	TE PN

SPECIFICATIONS

MECHANICAL LIFE: 30,000 MAKE-AND-BREAK CYCLES.

CONTACT RESISTANCE: 20 mΩ MAX. INITIAL @ 2-4VDC
100mA FOR BOTH SILVER AND GOLD PLATED CONTACTS.



CONTACT RATING: SILVER PLATED: 3A @ 120 VAC OR 28 VDC, 1A @ 250 VAC
GOLD PLATED: 0.4VA MAX @ 20 V MAX (AC OR DC)

INSULATION RESISTANCE: 1,000 MΩ MIN.

DIELECTRIC STRENGTH: 1,000 Vrms MIN.@SEA LEVEL.


OPERATING TEMPERATURE: -30°C TO 85°C.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN NAGALAKSHMI K 11JUL2014	TE Connectivity			
DIMENSIONS: mm [INCHES]			CHK HILL, RYAN 11JUL2014				
			APVD HILL, RYAN 11JUL2014	NAME			
			PRODUCT SPEC	SUBMINIATURE TOGGLE SWITCH			
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APPLICATION SPEC				
MATERIAL			WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-			-	A2	00779	C=2267079	-
FINISH			CUSTOMER DRAWING	SCALE	SHEET	REV	
-				3:1	1 of 6	A1	




MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3,5-6	N/A	2-1,5-4
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267079-5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

11JUL2014

NAGALAKSHMI_K

CHK

11JUL2014

HILL, RYAN

APVD

11JUL2014

HILL, RYAN

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

SUBMINIATURE TOGGLE SWITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=2267079

—

SCALE

3:1

SHEET

2 OF 6



REV

A1


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	-	-	SEE SHEET 1	-	-

MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION






PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267079-3


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014		 TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK HILL, RYAN 11JUL2014							
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD HILL, RYAN 11JUL2014		NAME SUBMINIATURE TOGGLE SWITCH				
	0 PLC ± -		PRODUCT SPEC						
	1 PLC ± 0.38[.015]		—						
	2 PLC ± 0.25[.010]		APPLICATION SPEC						
	3 PLC ± -		—						
MATERIAL —	4 PLC ± -		—		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
	ANGLES ± 5°		WEIGHT —		A2	00779	C=2267079		—
	FINISH —		CUSTOMER DRAWING		SCALE 3:1		SHEET 3 of 6		REV A1



SOLDER LUG

LAYOUT FOR PN 2267079-4

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		—	SEE SHEET 1	—	—	—



MODEL NO.	POS.1	POS.2	POS.3
TMD	OFF	NONE	ON
TERM. COMM.	OPEN	N/A	3-1
SCHEMATIC			

SWITCH FUNCTION

WITHOUT LOCKING RING

WITH STANDARD LOCKING RING






PANEL MOUNTING

LAYOUT FOR PN 2267079-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK HILL, RYAN 11JUL2014				
		APVD HILL, RYAN 11JUL2014	NAME			
		PRODUCT SPEC	SUBMINIATURE TOGGLE SWITCH			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE			
0 PLC ± -		—	CAGE CODE			
1 PLC ± 0.38[.015]		—	DRAWING NO			
2 PLC ± 0.25[.010]		—	RESTRICTED TO			
3 PLC ± -		—	SCALE			
4 PLC ± -		—	SHEET			
ANGLES ± 5°		—	REV			
FINISH		—	A1			
MATERIAL		—	CUSTOMER DRAWING			
—		—	3:1			
—		—	5 OF 6			
—		—	A1			

MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION



SOLDER LUG

PANEL MOUNTING

LAYOUT FOR PN 2267079-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 11JUL2014
NAGALAKSHMI K

CHK 11JUL2014
HILL, RYAN

APVD 11JUL2014
HILL, RYAN

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	—
1 PLC	±	0.38[.015]
2 PLC	±	0.25[.010]
3 PLC	±	—
4 PLC	±	—
ANGLES	±	5°
FINISH	—	—

MATERIAL —

CUSTOMER DRAWING

DWN 11JUL2014
NAGALAKSHMI K

CHK 11JUL2014
HILL, RYAN

APVD 11JUL2014
HILL, RYAN

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT —

TE Connectivity

SUBMINIATURE TOGGLE SWITCH

SCALE 3:1

SIZE A2

CAGE CODE 00779

DRAWING NO C=2267079

SHEET 6 OF 6

REV A1

NAME

RESTRICTED TO —