



RoHS Compliant
Directive 2011/65/EU

REFERENCE SPECIFICATION

Customer: _____

| | |
|-----------------------|----------------|
| Item: | Crystal Unit |
| Type: | NX2520SA |
| Nominal frequency | 16.000 MHz |
| Customer's Spec. No.: | --- |
| NDK Spec. No.: | EXS00A-CS08206 |

For your reference we submit this specification.
Please study and keep in your related document file.

Charge:

| | | |
|----------|--|--|
| Sales | | |
| Engineer | | |

Revision Record

| Rev. | Rev. Date | Items | Contents | Remarks |
|------|-------------|-------|----------|---------|
| --- | 06.Aug.2014 | Issue | --- | --- |
| | | | | |

1. Customer Specifications Number : ---
2. NDK Specification Number : EXS00A-CS08206
3. Type : NX2520SA
4. Electrical Characteristics

| | Electrical Characteristics Items | Symbol | Electrical Characteristics Spec. | | | | Notes |
|----|---|------------------|----------------------------------|-----|-----------------------|----------------------|--|
| | | | MIN | TYP | MAX | Unit | |
| 1 | Nominal frequency | f _{nom} | 16.000 | | | MHz | |
| 2 | Overtone order | - | Fundamental | | | - | |
| 3 | Frequency tolerance | - | -10 | - | +10 | ppm | at +25°C |
| 4 | Frequency versus Temperature Chacteristic | - | -20 | - | +20 | ppm | at -40 to +85°C |
| 5 | Equivalent resistance | - | - | - | 80 | ohm | IECπ-network / Series |
| 6 | Load capacitance | CL | - | 8 | - | pF | IECπ-network |
| 7 | Level of drive | - | - | 10 | 200 | μW | |
| 8 | Insulation resistance | - | 500 | - | - | Mohm | Terminal to terminal insulation resistance also terminal to cover insulation resistance must be 500MΩ (min) when DC100V ±15V is applied. |
| 9 | Operating Temperature range | | -40 | - | +85 | °C | |
| 10 | Storage temperature range | - | -40 | - | +85 | °C | |
| 11 | Air-tightness | - | - | - | 1.1 x10 ⁻⁹ | Pa m ³ /s | Helium leak detector |

5. Examination results document



Since a performance is guaranteed, an examination results document does not submit.

6. Application drawing


- 6.1 External dimension : EXD14B-00420
- 6.2 Taping and reel figure : EXK17B-00161
- 6.3 Holder marking : EXH11B-00317
- 6.4 Reliability assurance Item : EXS30B-00249

7. Notice


- 7.1 Order items are manufactured according to specification. As to conditions, which are not indicated in the specification and unpredictable such as applied condition and oscillation margin, please check them beforehand.
- 7.2 Crystal units will be damaged by ultrasonic welding process due to resonance of crystal wafer itself. NDK does not recommend using ultrasonic welding. If Ultra Sonic welding used, NDK strongly recommend verifying crystal unit damage by ultrasonic weld.
- 7.3 The appearance color has a different case by purchasing it more than 2 suppliers of the component, but characteristic and reliability are guaranteed.



LAND PATTERN (TYPICAL)






[TOP VIEW] PIN CONNECTION




| Date of Revise | | Charge | Approved | Reason | |
|----------------|-------------|----------|--|------------------------------------|----------------|
| Drawn | 30.Oct.2007 | K.Sato | Third Angle Projection Dimension:mm | Tolerance --- | Scale - / - |
| Designed | 30.Oct.2007 | K.Sato | Title NX2520SA Dimension Drawing | Drawing No. EXD14B-00420 | Rev. |
| Checked | --- | --- | | | |
| Approved | 30.Oct.2007 | K.Kubota | | | |

NIHON DEMPA KOGYO CO., LTD.



| | | | | | |
|----------|----------------|--------------|---|------------------------------------|----------|
| | Date of Revise | Charge | Approved | Reason | |
| B | 14. Mar. 2008 | Wada | Kubota | Changed drawing title | |
| | Date | Name | Third Angle Projection | Tolerance | |
| Drawn | 19. Jun. 2003 | H. Yagishita | Dimension: mm | ---- | |
| Designed | 19. Jun. 2003 | H. Yagishita | Title NX2520 Series Taping and Reel Spec. | Drawing No. EXK17B-00161 | |
| Checked | 19. Jun. 2003 | K. Kubota | | | Rev. |
| Approved | 19. Jun. 2003 | T. Ishii | | | B |



NOTE

1. Frequency Code

Marking Frequency is consist of five digits, first five digits of Nominal Frequency

Example

| | |
|-------------------|---------------|
| Nominal Frequency | 28.636363 MHz |
| Frequency Code | 28.636 |

2. Month Code Table

| | | | | | | | | | | | | |
|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|------------|------------|------------|
| Month | 1 Jan. | 2 Feb. | 3 Mar. | 4 Apr. | 5 May. | 6 Jun. | 7 Jul. | 8 Aug. | 9 Sep. | 10 Oct. | 11 Nov. | 12 Dec. |
| Month Code | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | X | Y | Z |

*Marking digits are not include a decimal point and dot mark.

| | | | | | | |
|----------|----------------|------------|-------------------------------|------------------------------------|---------------------|----------|
| | Date of Revise | Charge | Approved | Reason | | |
| D | 19. Jun 2012 | H.Ouchi | M. Kubota | Added terminal number information. | | |
| | Date | Name | Third Angle Projection | Tolerance | Scale | |
| Drawn | 16.Jan.2006 | I.Miyahara | Dimension:mm | | / | |
| Designed | 16.Jan.2006 | I.Miyahara | Title | | Drawing No. | Rev. |
| Checked | 16.Jan.2006 | --- | Crystal Holder Marking | | EXH11B-00317 | D |
| Approved | 16.Jan.2006 | K.Okamoto | | | | |

NIHON DEMPA KOGYO CO., LTD.

Reliability assurance item

(page: 1/1)

| No. | Test Item | Test Methods | Specification Code |
|-----|-----------------------------|--|--------------------|
| 1 | High Temperature Storage *1 | +85±3°C 720h | A |
| 2 | Low Temperature Storage | -40±3°C 500h | A |
| 3 | Temperature Humidity | +60±3°C 90~95%RH 500h | A |
| 4 | Temperature Cycling *1 | -40±3°C / +85±3°C It is 500 cycles using 30 minutes each as 1 cycle. | A |
| 5 | Vibration | Frequency Range : 10~55Hz Amplitude : 1.52mm 1 cycle : 1 minutes Test time : Three mutually perpendicular axes each 2 hours. | A |
| 6 | Shock | Devices are shocked to half sine wave (981m/s ²) three mutually perpendicular axis each 3 times. | A |
| 7 | Drop | Devices are dropped from the height 75cm onto wooden block. (more than 30mm thickness.) Execution 3 times random drops | A |
| 8 | Solderability | Pre-heat temperature : +150±10°C Pre-heat time : 60~120s When the temperature of the specimen is reached at +215±3°C, it shall be left for 30±1sec. Peak temperature 240±5°C Material: Pb-free (Sn-3.0Ag-0.5Cu) Flux : Rosin resin methyl alcohol solvent (1 : 4) | B |
| 9 | Reflow resistance | Pre-heat temperature : +150~180°C Pre-heat time : 90±30s Heat temperature : more than +230°C Heat time : 30s±10s Peak temperature : +260±5°C Peak time : less than 10s | A |

***1. High Temperature Storage and Temperature Cycling**

In case of customer spec on High temperature exceed +85°C, Low temperature exceed -40°C, above test according to customer spec high or low temperature will be perform and guarantee.

| Specification code | Specification |
|--------------------|---|
| A | $\Delta f/f \leq \pm 5 \text{ ppm}$ $\Delta CI/CI \leq \pm 15 \% \text{ or } 5 \Omega \text{ make use larger value}$ |
| B | The electrodes should be covered by a new solder at least 90% of immersed area. |