

Common mode filters High-speed differential signal line(USB2.0, LVDS, etc.) **MCZ-AH** series









MCZ1210AH type













FEATURES

- Ocompact multilayer common mode filter.
- O Has EMC suppression by achieving wide frequency range differential mode transmission while ensuring common mode impedance with virtually no affect on the high-speed differential transmission line signal.
- Operating temperature range: -40 to +85°C

APPLICATION

- O Electronic equipment high-speed interface (LVDS, USB2.0, MHL)
- O Mobile phones, PCs, DSCs, portable game machines, etc.
- O PDP/LCD/DLP/PJ TVs, DVD players, DVCs, mobile audio, etc.
- O Application guides: Smart phones/tablets

PART NUMBER CONSTRUCTION

MCZ		1210		AH		36	360		L2		Т		A0G	
Series na	ame		mensions ×0.5 mm	Product in		•	dance 100MHz	Number	of lines	Packagi	ng style	Interna	ıl code	

CHARACTERISTICS SPECIFICATION TABLE

Common mode impedance		DC resistance	Rated current	Rated voltage	Insulation resistance	Part No.
[100MHz]		[1 line]				
(Ω)	Tolerance	(Ω)max.	(mA)max.	(V)max.	(M Ω)min.	
36	±25%	1.00	200	5	10	MCZ1210AH360L2TA0G
90	±25%	1.75	100	5	10	MCZ1210AH900L2TA0G
200	±25%	4.00	100	5	10	MCZ1210AH201L2TA0G
300	±25%	4.50	100	5	10	MCZ1210AH301L2TA0G

Measurement equipment

Measurement item	Product No.	Manufacturer
Common mode impedance	E4991A+16192A	Keysight Technologies
DC resistance	Type-7561	Yokogawa
Insulation resistance	4339B	Keysight Technologies


^{*} Equivalent measurement equipment may be used.





MCZ1210AH type

IMPEDANCE VS. FREQUENCY CHARACTERISTICS



Measurement equipment


Product No.	Manufacturer
E4991A+16192A	Keysight Technologies

^{*} Equivalent measurement equipment may be used.

(2/4)


MCZ1210AH type

■SHAPE & DIMENSIONS




Dimensions in mm

■ RECOMMENDED LAND PATTERN




Dimensions in mm

CIRCUIT DIAGRAM




No polarity

■ RECOMMENDED REFLOW PROFILE




■ PACKAGING STYLE

REEL DIMENSIONS




Dimensions in mm

TAPE DIMENSIONS



Dimensions in mm

Type	Α	В	K
MCZ1210AH	1.15±0.1	1.4±0.1	1.0max.



Dimensions in mm

□PACKAGE QUANTITY

Package quantity	4,000 pcs/reel

■TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range	Storage temperature range*	Individual weight
–40 to +85 °C	−40 to +85 °C	3.0 mg

^{*} The storage temperature range is for after the assembly.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

⚠ REMINDERS
The storage period is less than 12 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
On not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
 Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
 Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
 Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
 Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.
Use a wrist band to discharge static electricity in your body through the grounding wire.
On not expose the products to magnets or magnetic fields.
On not use for a purpose outside of the contents regulated in the delivery specifications.
The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society,
person or property.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment

set forth in the each catalog, please contact us.

- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions