

»Features

- 60Watts peak pulse power ($t_p = 8/20\mu s$)
- Tiny DFN0603 package
- Bidirectional configurations
- Solid-state silicon-avalanche technology
- Low clamping voltage
- Low leakage current
- Low capacitance ($C_j=0.2pF$ typ.)
- Protection one data/power line
- IEC 61000-4-2 $\pm 15kV$ contact $\pm 20kV$ air
- IEC 61000-4-4 (EFT)40A(5/50ns)
- IEC 61000-4-5 (Lightning)3.0A(8/20 μs)




»Applications

- USB3.0,HDMI2.0,Thunderbolt
- Notebooks, Desktops, and Servers
- Portable Instrumentation

»Mechanical Data

- DFN0603package
- Molding compound flammability rating: UL 94V-0
- Packaging: Tape and Reel
- RoHS/WEEE Compliant

»Schematic & PIN Configuration



DFN0603

»Absolute Maximum Rating


Rating	Symbol	Value	Units
Peak Pulse Power ($t_p=8/20\mu s$)	P_{PP}	60	Watts
Peak Pulse Current ($t_p=8/20\mu s$)(note1)	I_{pp}	3.0	A
ESD per IEC 61000-4-2(Air) ESD per IEC 61000-4-2(Contact)	V_{ESD}	20 15	kV
Lead SolderingTemperature	T_L	260(10seconds)	°C
JunctionTemperature	T_J	-55 to +125	°C
StorageTemperature	T_{stg}	-55 to +125	°C

»Electrical Characteristics

Parameter	Symbol	Conditions	Min	Typical	Max	Units
Reverse Stand-OffVoltage	V_{RWM}				5.0	V
Reverse BreakdownVoltage	V_{BR}	$I_T=1mA$	5.5	8.5		V
Reverse LeakageCurrent	I_R	$V_{RWM}=5V, T=25^{\circ}C$		5	100	nA
Peak PulseCurrent	I_{PP}	$t_p=8/20\mu s$			3.0	A
Clamping Voltage	V_C	$IPP=3.0A, t_p=8/20\mu s$		20	25	V
JunctionCapacitance	C_j	$V_R = 0V, f = 1MHz$		0.2	0.26	pF

»Electrical Parameters (TA = 25°C unless otherwise noted)

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current



Note: .8/20μs pulsed waveform.

»Typical Characteristics

Figure 1: Peak Pulse Power vs. Pulse Time




Figure 2: Power Derating Curve




Figure3: Pulse Waveform






Figure 4: Clamping Voltage vs.Ipp




»Outline Drawing –DFN0603



Symbol	Dimensions in millimeters		
	Min	Nom	Max
A	0.28	0.30	0.32
A1	0.00	0.02	0.05
C	0.05	0.10	0.15
D	0.55	0.60	0.65
E	0.25	0.30	0.35
b	0.14	0.19	0.24
L	0.20	0.25	0.30
h	0	0.05	0.10

»Marking



»Ordering information

Order code	Package	Base qty	Delivery mode
PESD5V0H1BSF-N	DFN0603	10k	Tape and reel