

# AP2318A


## N-Channel Power MOSFET

### Description

The AP2318A uses advanced trench technology to provide excellent  $R_{DS(ON)}$ , low gate charge and operation with gate voltages as low as 2.5V. This device is suitable for use as a load switch or in PWM applications.

### General Features

- $V_{DS(V)} = 20V$   $I_D = 6.0A$
- $R_{DS(ON)} < 12m\Omega$  ( $V_{GS} = 4.5V$ )
- $R_{DS(ON)} < 16m\Omega$  ( $V_{GS} = 2.5V$ )
- High power and current handing capability
- Lead free product is acquired
- Surface mount package



### Application

- PWM applications
- Load switch
- Power management
- Halogen-free

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
RHXYY	AP2318A	SOT-23-3	Ø180mm	8 mm	3000 units

### Maximum ratings ( $T_a=25^\circ C$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	$V_{DS}$	20	V
Gate-Source Voltage	$V_{GS}$	±12	
Continuous Drain Current $t=5s$	$I_D$	6	A
Pulsed Drain Current	$I_{DM}$	24	
Continuous Source-Drain Diode Current	$I_S$	1.64	
Maximum Power Dissipation $t=5s$	$P_D$	1.25	W
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	-	°C/W
Junction Temperature	$T_J$	150	°C
Storage Temperature	$T_{stg}$	-50 ~ +150	

## AP2318A

## N-Channel Power MOSFET







Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
<b>Static</b>						
Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	20			V
Gate-source leakage	$I_{GSS}$	$V_{DS} = 0V, V_{GS} = \pm 10V$			$\pm 100$	nA
Zero gate voltage drain current	$I_{DSS}$	$V_{DS} = 20V, V_{GS} = 0V$			1.0	$\mu A$
Gate-source threshold voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	0.45	0.7	1.0	V
Drain-source on-state resistance <sup>a</sup>	$R_{DS(on)}$	$V_{GS} = 4.5V, I_D = 6.0A$		0.010	0.0130	$\Omega$
		$V_{GS} = 2.5V, I_D = 4.7A$		0.013	0.0180	
Forward transconductance <sup>a</sup>	$g_{fs}$	$V_{DS} = 10V, I_D = 6.0A$		6		S
<b>Dynamic<sup>b</sup></b>						
Input capacitance	$C_{iss}$	$V_{DS} = 10V, V_{GS} = 0V, f = 1MHz$		565		pF
Output capacitance	$C_{oss}$			125		
Reverse transfer capacitance	$C_{rss}$			85		
Gate resistance	$R_g$	$f = 1MHz$	0.5		4.8	$\Omega$
Turn-on delay Time	$t_{d(on)}$	$V_{GEN} = 5V, V_{DD} = 10V,$ $I_D = 4A, R_G = 1\Omega, R_L = 2.2\Omega$		8	16	ns
Rise time	$t_r$			15	30	
Turn-off Delay time	$t_{d(off)}$			33	66	
Fall time	$t_f$			13	26	
<b>Drain-source body diode characteristics</b>						
Forward diode voltage	$V_{SD}$	$V_{GS} = 0V, I_S = 4A$		0.75	1.2	V

**Notes :**

- a. Pulse Test : pulse width  $\leq 300\mu s$ , duty cycle  $\leq 2\%$ .
- b. These parameters have no way to verify.

# AP2318A

## N-Channel Power MOSFET



## AP2318A

## N-Channel Power MOSFET

## SOT-23-3 Package Outline Dimensions

