規格承認書

PECIFICATION FOR APPROVAL

客 戶								
CUSTOMER	:	立创						
項目	_							
ITEM	:	电磁有源一体蜂鸣器(内含驱动电路)						
型號	_							
TYPE	:	GMD12095YF	3-3V2400)				
描述	_							
DESCRIPTION	:	ф 12 x H9.5 mm	2400Hz	DC3V	≥80dB	PPO 材质	P=7.6mm	
客戶料號								
CUSTOMER NO). ;							
規格書號								
SPECIFICATION	N NC). :						
版本								
EDITION NO.	:	V1.0						
日期	•							
DATE	:	2019-12-26						

客戶承認

CUSTOMER CONFIRM AND SIGN

檢查	審核	承認
TESTED BY	CHECKED BY	APPROVED BY

東莞市赢海電子有限公司

DONGUAN INGHAI ELECTRONICS CO.,LTD

製作	審查	確認
ISSUED BY	CHECKED BY	APPROVED BY
周明	刘承成	


地址: 廣東省東莞市長安鎮廈邊元灶頭工業區 16-6 號

網址: HTTP://WWW.INGHAI.COM

DONGGUAN INGHAI ELECTRONICS CO.,LTD

Model NO: GMD12095YB-3V2400

A: DIMEMSIONS: Unit:mm Tolerance: ± 0.2 mm



B: SPECIFICATIONS


Model NO	GMD12095YB	
Rated Voltage	3VDC	
Operating Voltage	2.0~5.0VDC	
Max.Rated Current	Max.30mA	
Sound Pressure level(dB/min)at5DVC/10cm	Min 80dB	
Resonant Frequency	2400±300Hz	
Operating Temperature	-20 °C~+70 °C	
Storage Temperature	-30 °C∼+80°C	
Case material and color	PPO / Black	

Measuring condition


Part shall be measured under a condition (Temperature: $5\sim35^{\circ}$ C, Humidity: $45\%\sim85\%$ R.H., Atmospheric pressure: $860\sim1060$ hPa) unless the standard condition (Temperature: $25\pm3^{\circ}$ C, Humidity: $60\pm10\%$ R.H. Atmospheric pressure: $860\sim1060$ hPa) is regulated to measure.


C: Acoustic Characteristics:

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below



D: Typical Frequency Response Curve:





E: Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

1. Ordinary Temperature Life Test

The part shall be subjected to 96 hours at $25\pm10\,^{\circ}$ C. Input rated voltage Resonant frequency, 1/2 duty Square wave.

2. High Temperature Test

The part shall be capable of with standing a storage temperature of +80 ℃ for 96 hours.

3. Low Temperature Test

The part shall be capable of with standing a storage temperature of -30℃ for 96 hours.

4. Humidity Test

Temperature:+40 $^{\circ}$ C \pm 3 $^{\circ}$ C Relative Humidity:90% \sim 95% Duration: 48 hours and expose to room temperature for 6 hours

5. Temperature Shock Test

Temperature:70°C /1hour \rightarrow 25°C/3hours \rightarrow -30°C/1hour \rightarrow 25°C/3hours (1cycle) Total cycle: 10 cycles

6. Drop Test

Standard Packaging From 120mm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

7. Vibration Test

Vibration: 1000cycles /min. Amplitude: 1.5mm, Duration: 1 hour in each 3 axes

Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.