

Page: <u>1</u>

1. 安全认证: <u>Safety Standard:</u>

C-UL

- 2. 接点规格: <u>Contact Specification:</u>
 - 2.1 接点间隙:
 最小 0.15 mm。

 Contact Gap:
 0.15mm Minimum.
 - 2.2 接点阻抗: 初始值最大 100mΩ;
 Contact Resistance 流通电流 1A、开路测试电压: 6VDC;
 使用电压下降法量测。
 Maximum 100mΩ at initial value.
 Test Current: 1A, Open Circuit Test Voltage: 6VDC.
 By using Voltage Drop Method.
 - 2.3 接点容量:
 120VAC Cosφ =1,可通过电流为 2 安培。

 Contact Capacity:
 24VDC ,可通过电流为 2 安培。

 2 Amps at 120VAC Cosφ =1.
 2 Amps at 24VDC .

3. 摄氏 20 度之线圈规格: <u>Coil Specification at</u> <u>20 °C:</u>

3.1	额定电压: Rated Voltage:	3VDC.	5VDC.	6VDC.	9VDC.	12VDC.	24VDC.
3.2		50/67/120	29.9 /40/72	25/33.3/60	16.7/22.5/40	12.5/16.7/30	6.25/8.3/15
3.3	额定消耗功率: (± 10%.) Rated Power Consumption:			0.15	W/0.2W0.36V	V	
	线圈阻抗: (Ω± 10%.) Resistance:	60/45/25	167/125/70	240/180/100	540/400/220	960/720/400	3840/2880/1600
3.5	感动电压: Pull In Voltage:	 ≤ (当电压渐渐施加于继电器时接点之动作电压,为额定电压之 80%) V DC ≦ (Contact operating voltage when voltage is gradually applied. It is 80% of the Rated Voltage) V DC 					
3.6	开放电压: Drop Out Voltage:	 ≧ (当额定电压渐渐的减少时接点放开之电压,为额定电压之 10%) VDC ≧ (Contact breaking voltage when rated voltage is gradually reduced. It is 10% of the Rated Voltage) VDC 					
3.7	最大应加电压: Max. Allowable Voltage:	•	已压之 130%) ⁻ the Rated \) V DC /oltage) V DC	;		

中国浙江宁波市鄞州区姜山镇新塘沿工业开发区 宁波汇科新纪元电器有限公司 Jiangshan Town Yinzhou Ningbo Zhejiang China Ningbo Huike New Era Electrical Appliances Co.,Ltd TEL: (0574) 88457918 88457948 FAX: (0574) 88457928



Page: 2

3.8	动作时间: Operate Time:	在施加额定电压时最大为 5 milliseconds。 5 milliseconds Maximum when rated Voltage is applied.
3.9	开放时间 Release Time:	在额定电压突然消失时最大为 5 milliseconds.。 5 milliseconds Maximum when rated Voltage is suddenly cut off.
3.10	D 线圈温升: Coil Temperature Rise:	在空载时线圈施加最大可允许电压, 待温度稳定后量测的温度不可超过 40℃。(不 包含环境温度) 40℃ Maximum. Maximum Allowable Voltage is applied to Coil while no load should be applied to Contacts, then the temperature should be measured when the value is stabilized. Environment temperature should not be included in.
Ele	气特性: <u>ctrical</u> aracteristics:	
4.1	使用寿命: Life Expectancy:	
	4.1.1 电气寿命: Electrical Life:	2A/120VAC Cosφ =1, 施加额定电压时,有 100,000 次以上之电气寿命。 2A/24VDC ,施加额定电压时,有 100,000 次以上之电气寿命。 100,000 operations Minimum at 2A/120VAC Cosφ =1. 100,000 operations Minimum at2A/24VDC Rated Voltage is applied.
	4.1.2 机械寿命: Mechanical Life:	在无负载的情况下有 10,000,000 次以上之机械寿命。 10,000,000 operations Minimum at No Load condition.
	4.1.3最大操作频率 Maximum Operating Frequency:	电气: 每分钟 30 次。 机械: 每分钟 300 次。 Electrical: 30 operations/minute. Mechanical: 300 operations/minute.
4.2	绝缘耐压: Dielectric Strength:	
	4.2.1 接点对接点间: Between Contacts:	400VAC,50/60 Hz,漏电流小于 1mA,持续一分钟。 400VAC at Test Frequency 50/60 Hz, Leakage Current: 5mA for 1 minute.
	4.2.2 线圈对接点间: Between Coil & Contact:	1,000VAC,50/60 Hz,漏电流小于 1mA,持续一分钟。 1,000VAC at Test Frequency 50/60 Hz, Leakage Current: 5mA for 1 minute.

中国浙江宁波市鄞州区姜山镇新塘沿工业开发区 宁波汇科新纪元电器有限公司 Jiangshan Town Yinzhou Ningbo Zhejiang China Ningbo Huike New Era Electrical Appliances Co.,Ltd TEL: (0574) 88457918 88457948 FAX: (0574) 88457928



Page: 3

在施加 500VDC 绝缘阻抗之量测值需 ≧ 100 MΩ。 4.3 绝缘阻抗: Insulation \geq 100 M Ω Minimum. Resistance: A Voltage of 500VDC should be applied after which measurement shall be made. 4.4 震动测试: Vibration 4.4.1 耐震性 I: 在无激磁状态下双振幅宽度为 1.5mm, 震动频率在一分钟内由 Endurance I: 10HZ~55HZ~10HZ。XYZ 各方向各进行 2 小时,共六小时,实验后外观构造不 可异常,且电气功能需符合规格之要求。 The Coil shall be maintained under not energized condition, double amplitude 1.5 mm, the entire frequency range changes from 10 to 55 Hz then returns to 10 Hz shall be made in 1 minute. This motion shall be applied for a period of 2 hours in each of 3 mutually perpendicular axis (a total of 6 hours) There should not be any deformations in construction and in appearance, while the Electrical Specifications should be fulfilled after the test. 4.4.2 耐震性 II (误动 在激磁状态下双振幅宽度是 1.5mm, 震动频率在一分钟内由 10HZ~55HZ~10HZ。 作): XYZ 各方向进行 5 分钟,实验中不得有误(接点断开时间不可超过 1 mS)。实验后 Endurance II 外观,构造不可异常,且电气功能需符合规格之要求。 (Error The Coil shall be maintained under energized condition, double amplitude 1.5 Operation): mm, the entire frequency range changes from 10 to 55 Hz then returns to 10 Hz shall be made in 1 minute. This motion shall be applied for a period of 5 minutes in 3 mutually perpendicular axis. Malfunction is not allowed during the test (contact breaking time should be less than 1 millisecond) In addition, there should not be any deformations in construction and in appearance while the Electrical Specifications should be fulfilled after the test. 4.5 冲击测试: Shock: 在无激磁状态加速度 1000m/s² 冲击情况下,XYZ 各方向进行 5 次,实验后外观, 4.5.1 耐冲击性 I: 构造不可异常,且电气功能需符合规格之要求。 Endurance I: Peak Acceleration: 1000m/s² The Coil shall be maintained under not energized condition, 5 successive shocks shall be applied in 3 mutually perpendicular axis. There should not be any deformations in construction and in appearance while the Electrical Specifications should be fulfilled after the test. 在激磁状态加速度 100m/s² 冲击情况下, XYZ 各方向进行 2 次, 实验中不得有误 4.5.2 耐冲击性 || (误 动作): (接点断开时间不可超过1mS),实验后外观,构造不可异常,且电气功能需符合 规格之要求。 Endurance II (Error Peak Acceleration: 100m/s² Operation): The Coil should be maintained under energized condition, 2 successive shocks shall be applied in 3 mutually perpendicular axis. Malfunction is not allowed during the test (contact breaking time should be less than 1 millisecond) In addition, there should not be any deformations in construction and in appearance while the Electrical Specifications should be fulfilled after the test.

中国浙江宁波市鄞州区姜山镇新塘沿工业开发区宁波汇科新纪元电器有限公司Jiangshan Town Yinzhou Ningbo Zhejiang ChinaNingbo Huike New Era Electrical Appliances Co.,LtdTEL: (0574) 88457918 88457948FAX: (0574) 88457928



5. 环境特性: Environmental **Characteristics:**

5.1 温度范围: Temperature Range:

35~85% RH.

5.1.1 使用温度范围: Operating Temperature Range:	-30 to + 70°C。 使用温度范围是代表继电器在线圈之动作电压范围内可以持续动作的温度范围 (在低温时无水滴凝结现象) Operating temperature range is the range of ambient temperature of which the Relay can be operated continuously within operative voltage range of coil (no condensation of water drops under low temperature condition)
5.1.2 储存温度范围: Storage Temperature Range:	-30 to + 70°C. 储存温度范围是代表继电器在没有损伤的情况下可以被储存的温度范围(在低温 时无水滴凝结现象)。储存的情况在本 SPEC 其它地方所示。 Storage temperature range is the range of ambient temperature of which the Relay can be stored without damages (no condensation of water drops under low temperature condition). Conditions are as specified elsewhere in these specifications.

HK23F

Page: 4

- 5.2 湿度范围: Humidity Range:
- 5.3 耐寒性: Cold Resistance:

5.3.1 使用耐寒性: 继电器不给予电压或电流状态下,在恒温箱以-30 ± 2°C 的温度连续保持 2 小时。 Cold Resistance 保持原状态操作回路上给予定格电压实验时继电器动作要正常。(在低温时无水滴 in Use: 凝结现象) Relay should be kept in temperature chamber at -30 ± 2°C for two hours that no current or voltage shall be supplied to Relay. Such condition shall be maintained while the rated voltage is supplied to Relay, then the Relay shall operate normally. (No condensation of water drops under low temperature condition) 5.3.2 储存耐寒性: 继电器在恒温箱以-30 ± 2°C 的温度连续保持 72 小时。接着,于常温常湿中消除 Storage Cold 水滴1至2小时以后,进行构造,动作,及绝缘阻抗,耐压的测试,结果需要符 Resistance: 合 SPEC。(在低温时无水滴凝结现象)

Relay should be kept in temperature chamber at -40 \pm 2°C for 72 hours. Then the Relays shall be maintained at standard atmospheric condition for 1 to 2 hours after which measurement shall be made. Construction, Relay operation, Insulation Resistance and Dielectric Strength shall satisfy the specification requirements. (No condensation of water drops under low temperature condition)

5.4 耐热性:

Heat Resistance:

中国浙江宁波市鄞州区姜山镇新塘沿工业开发区 宁波汇科新纪元电器有限公司 Jiangshan Town Yinzhou Ningbo Zhejiang China Ningbo Huike New Era Electrical Appliances Co., Ltd TEL: (0574) 88457918 88457948 FAX: (0574) 88457928



Page: 5

5.4.1 使用耐热性: 继电器操作回路提供定格电压,在接点部份提供定格电流的状态下,在恒温箱以 70 ± 2℃ 的温度连续保持 2 小时后,保持原状态进行继电器动作之测试,结果必 Heat Resistance in Use: 须符合 SPEC。 Relay should be kept in temperature chamber at 70 ± 2°C for two hours that rated Voltage should be supplied to Coil while rated Current should be supplied to Contacts. Such condition shall be maintained while the rated voltage is supplied to Relay, then Relay shall operate normally. 5.4.2 储存耐热性: 继电器在恒温箱以 70 ± 2℃ 的温度连续保持 16 小时,在常温,常湿状态下,放 Storage Heat 置 1-2 小时后, 进行构造, 动作, 及绝缘阻抗, 耐压的测试, 结果需要符合 SPEC。 Resistance Relay should be kept in temperature chamber at $70 \pm 2^{\circ}$ C for 16 hours. Then the Relays shall be maintained at standard atmospheric condition for 1 to 2 hours after which measurement shall be made. Construction, Relay operation, Insulation Resistance and Dielectric Strength shall satisfy the specification requirements. 继电器以温度 40 ± 2℃ 相对温度在 90~95%环境下连续保持 48 小时,接着,于 5.5 耐湿性: Moisture Resistance: 常温常湿放置 1-2 小时后,进行构造,动作,及绝缘阻抗,耐压的测试,结果需 要符合 SPEC。 Relay should be kept in temperature chamber at 40 ± 2°C (90~95% RH) for 48 hours. Then the Relays shall be maintained at standard atmospheric condition for 1 to 2 hours after which measurement shall be made. Construction, Relay operation, Insulation Resistance, Dielectric Strength shall satisfy the specification requirements. 6. 端脚特性: Terminal **Characteristics:** 6.1 端脚强度: 在水平方向负重300 克持续1分钟,测试完成后端脚不能有任何的松脱或是弯曲。 A load of 300g should be applied to the Terminal for one minute in horizontal Terminal Strength: direction. There should not be any looseness or bending of Terminals. 6.2 沾锡测试: 温度 230 ± 5℃,时间 3 ± 0.5 秒,浸渍端子前端 3mm,须沾锡面积需达 90%以 Soldering Dip Test: 上。 The front 3 mm of Terminal should be immersed for 3 ± 0.5 seconds at 230 ± 5°C. Soldered area must be minimum 90% of the soldering surface. 当端脚浸到 350℃ 的锡炉内 3 秒钟时, 继电器必须能符合所有的电气与机械规格 6.3 沾锡耐热性: Soldering Heat 之要求,且外观不会有改变。 Resistance: When the Terminal are immersed into soldering bath at 350 °C for 3 seconds, the Relay shall satisfy all electrical and mechanical specifications and must not have excessive change in outside appearance. 7. 重量: 约3.5克 Weight: Approx.3.5g GB2828-2000 抽样标准中,以一般检查水准 II级 AQL - 0.4 为依据。 8. 抽样检查标准: Sample Test Method: GB2828-2000 Level - General II, AQL 0.4.



HK23F	
_	

Page: <u>6</u>

产品编号方式: Ordering Information: HK23F -DC 12V -S D A	XX		
		特殊标记	G:环保产品
		Special Request Code	G: RoHS
		安装方式	无:PCB
		Mounting Termination	NIL:PCB
		触点转换形式	无:1FormC
		Contact Form	NIL:1FormC
		线圈功耗	无:0.36WH:0.2W D:0.15W
		Coil Power	NIL: 0.36W H: 0.2W D:0.15W
		封装方式	无: 半密封型 S: 密封型
		Type Of Sealing	Nil:Flow Solder Type
			S:Plastic Sealed Type
		线圈电压	$3 V \cdot 5 V \cdot 6V \cdot 9V \cdot 12V \cdot 24V$
		Coil Voltag	$3 V \cdot 5 V \cdot 6V \cdot 9V \cdot 12V \cdot 24V$
		线圈性质	DC:直流
		CoilType	DC
		产品型号	HK23F
		Туре	HK23F

外型尺寸 (mm) Dimensin (mm)

H U IK E

Page: 7



Tolerance : ± 0.3

中国浙江宁波市鄞州区姜山镇新塘沿工业开发区 宁波汇科新纪元电器有限公司 Jiangshan Town Yinzhou Ningbo Zhejiang China Ningbo Huike New Era Electrical Appliances Co.,Ltd TEL: (0574) 88457918 88457948 FAX: (0574) 88457928