

# POWER RELAY 1 POLE - 16A 80A Inrush type

# FTR-K1 Series

### **■ FEATURES**

Peak 80A inrush current (1 form A type)

• Low profile (height: 15.7mm)

• HIGH INSULATION

Insulation distance (between coil and contacts): 10mm min.

Dielectric strength: 5KV Surge strength: 10KV

· Class F coil wire

• Low coil power (400mW)

· Cadmium free contacts

SAFETY STANDARDS
 UL, CSA, VDE, SEMKO approved
 UL, CSA TV-5 rating approved (1 form A type)

• Flux proof, RTII

RoHS compliant

Please see page 6 for more information



#### ■ PARTNUMBER INFORMATION

 $[Example] \qquad \frac{FTR\text{-K1}}{\text{(a)}} \quad \frac{C}{\text{(b)}} \quad \frac{K}{\text{(c)}} \quad \frac{012}{\text{(d)}} \quad \frac{W}{\text{(e)}} - \frac{BG}{\text{(f)}}$ 

(a)	Relay type	FTR-K1: FTR-K1 Series		
(b)	Contact configuration	A C	: 1 form A (SPST-NO) : 1 form C (SPDT) (standard type "K" only)	
(c)	Coil type	К	: Standard type (400mW / Flux proof)	
(d)	Coil rated voltage	012	: 5110VDC Coil rating table at page 3	
(e)	Contact material / TV type	W T	: AgSnO <sub>2</sub> (1 form C contact type only) : AgSnO <sub>2</sub> / TV-5 rated (1 form A / TV-5 contact type only)	
(f)	Special type	Nil BG	: Standard type (without gold plate) : Gold plated 3µm	

Actual marking does not carry the type name : "FTR"

E.g.: Ordering code: FTR-K1CK012W Actual marking: K1CK012W

1

### ■ SPECIFICATION

Item			FTR-K1 AK ( ) T Standard	FTR-K1 CK ( ) W Standard	
Contact	Configuration		1 form A	1 form C	
Data	Construction		Single		
	Material		AgSnO <sub>2</sub>		
	Resistance (initial)		Max. 100mOhm at 1A, 6VDC		
	Contact rating (resistive	e)	16A, 250VAC / 24VDC		
	Max. carrying current *	1	20A		
	Max. inrush current		80A (20ms) 250VAC (only make contact)		
	Max. switching voltage		440VAC / 300VDC		
	Max. switching power		4,000VA / 384W		
	Min. switching load *2		100mA, 5VDC		
Life	Mechanical		Min. 20 x 10 <sup>6</sup> operations		
		AC contact rating	Min. 100 x 10 <sup>3</sup> operations	Min. 50 x 10 <sup>3</sup> operations	
	Electrical	DC contact rating	Min. 100 x 10 <sup>3</sup> operations	Min. 30 x 10 <sup>3</sup> operations	
		Peak Inrush (80A)	Min. 10 x 10 <sup>3</sup> operations (only make contact)		
		Lamp load (UL TV-5)	Min. 25 x 10 <sup>3</sup> operations	Min. 25 x 10 <sup>3</sup> operations (only make contact)	
Coil Data	Rated power (20 °C)		400mW (430mW at 48V coil)		
	Operate power (20 °C)		200mW (210mW at 48V coil)		
	Operating temperature	range	-40 °C to +85 °C (no frost)		
Timing Data	Operate (at nominal vo	ltage)	Max. 15ms (without bounce)		
	Release (at nominal vo	ltage)	Max. 5ms (without bounce, no diode)		
Insulation	Resistance (initial)		Min. 1,000MOhm at 500VDC		
	Dielectric strength	Open contacts	ntacts 1,000VAC (50/60Hz) 1min		
		Contacts to coil	5,000VAC (50/60Hz) 1min		
	Surge strength	Coil to contacts	10,000V / 1.2 x 50µs standard wave		
	Clearance		10mm		
	Creepage		10mm		
	EN61810-1, VDE0435	Voltage	250V		
		Pollution degree	3		
	Material group		III a		
	Category		C / 250V (Reference voltage) (VDE0110b)		
Other	Vibration resistance Misoperation≥1us		•		
	. ISTATION TOOLUTIO	Endurance	10 to 55Hz double amplitude 1.5mm		
	Shock Misoperation≥1u Endurance				
			1,000m/s² (6 ± 1ms)		
	Weight		Approximately 13g		
	Sealing		Flux proof, RTII		

<sup>\* 1:</sup> Need to consider the heat from PCB when max. current is more than 10A.

<sup>\* 2:</sup> Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental contions

### **■ COIL RATING**

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance +/- 10% (Ohm)	Must Operate Voltage (VDC) *	Must Release- Voltage (VDC) *	Max. Coil Voltage (VDC)	Rated Power (mW)
005	5	62	3.5	0.5	12.2	
006	6	90	4.2	0.6	14.7	
009	9	202	6.3	0.9	22	
012	12	360	8.4	1.2	29.4	400
018	18	810	12.6	1.8	44.1	
022	22	1,210	15.4	2.2	53.9	
024	24	1,440	16.8	2.4	58.8	
028	28	1,960	19.6	2.8	68.6	
048	48	5,360	33.6	4.8	117.6	430
060	60	8,570	42.0	6.0	147.0	400
110	110	28,800	77.0	11.0	269.5	420

Note: All values in the table are valid for 20°C and zero contact current.


### ■ SAFETY STANDARDS


Туре	Compliance	Contact rating		
UL	UL 508	FTR-K1CK()W	FTR-K1AK()T	
	E63614	Flammability: UL 94-V0 (plastics)		
CSA	C22.2 No. 14 LR 40304	- 16A, 277VAC/24VDC (resistive) 20A, 277VAC (resistive) 1 HP, 277VAC 1/2 HP, 125VAC 1/8 HP, 125VAC TV-5, 120VAC, 25,000 cycles (only make contact) Pilot duty: B300	16A, 24VAC (resistive) 16A, 277VAC (resistive) 20A, 277VAC (resistive) 1 HP, 277VAC 1/2 HP, 125VAC TV-5, 120VAC 25,000 cycles Pilot duty: A300	
VDE	0435, 0631, 0700, 0860, 40013848	16A, 250VAC (cosφ=1), 85°C 3.5A, 250VAC (cosφ=0.4), 85°C 16 A 24VDC (0ms), 85°C 5A/80A, 250VAC 10,000 times, 85°C (only make contact)		
SEMKO	EN 61058-1:1992 and A1 EN 61095:1993 and A1+A11	250VAC, 16 (3)A 40T85 5A/80A 250VAC 40T85 (only make contact)		


Complies with NEMKO, DEMKO, FIMKO


<sup>\*</sup> Specified operate values are valid for pulse wave voltage.


### ■ CHARACTERISTIC DATA






















### **■** DIMENSIONS


#### Dimensions

FTR-K1AK()T






### • Schematics (BOTTOM VIEW)





#### • PC board mounting hole layout (BOTTOM VIEW)




### • Dimensions

### FTR-K1CK()W






# • Schematics (BOTTOM VIEW)



### PC board mounting hole layout (BOTTOM VIEW)



### **RoHS Compliance and Lead Free Information**

### 1. General Information

- All signal and power relays produced by Fujitsu Components are compliant with RoHS directive 2002/95EC including amendments.
- Cadmium as used in electrical contacts is exempted from the RoHS directives on October 21st, 2005.
   (Amendment to Directive 2002/95/EC)
- All of our signal and power relays are lead-free. Please refer to Lead-Free Status Info for older date codes at: http://www.fujitsu.com/us/downloads/MICRO/fcai/relays/lead-free-letter.pdf
- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified. This material has been verified to be compatible with PbSn assembly process.

### 2. Recommended Lead Free Solder Profile

Recommended solder Sn-3.0Ag-0.5Cu.

### Flow Solder condition:

Pre-heating: maximum 120°C dip within 5 sec. at 260°C solder bath

### Solder by Soldering Iron:

Soldering Iron

Temperature: maximum 360°C Duration: maximum 3 sec.

We highly recommend that you confirm your actual solder conditions

### 3. Moisture Sensitivity

• Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated.

### 4. Tin Whiskers

• Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

### **Fujitsu Components International Headquarter Offices**

#### Japan

Fujitsu Component Limited Gotanda-Chuo Building 3-5, Higashigotanda 2-chome, Shinagawa-ku Tokyo 141, Japan Tel: (81-3) 5449-7010 Fax: (81-3) 5449-2626

Email: promothq@ft.ed.fujitsu.com Web: www.fcl.fujitsu.com

### North and South America

Fujitsu Components America, Inc. 250 E. Caribbean Drive Sunnyvale, CA 94089 U.S.A. Tel: (1-408) 745-4900 Fax: (1-408) 745-4970

Email: components@us.fujitsu.com

Web: http://us.fujitsu.com/components

#### Europe

Fujitsu Components Europe B.V. Diamantlaan 25 2132 WV Hoofddorp Netherlands Tel: (31-23) 5560910 Fax: (31-23) 5560950 Email: info@fceu.fujitsu.com

Web: emea.fujitsu.com/components/

#### Asia Pacific

Fujitsu Components Asia Ltd. 102E Pasir Panjang Road #01-01 Citilink Warehouse Complex Singapore 118529 Tel: (65) 6375-8560

Fax: (65) 6273-3021 Email: fcal@fcal.fujitsu.com

Web: http://www.fujitsu.com/sg/services/micro/components/

©2010 Fujitsu Components Europe B.V. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

The contents, data and information in this datasheet are provided by Fujitsu Component Ltd. as a service only to its user and only for general information purposes.

The use of the contents, data and information provided in this datasheet is at the users' own risk.

Fujitsu has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

Fujitsu Components Europe B.V. and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Nor do Fujitsu Components Europe B.V. and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability for any representation or warrant of any kind, express or implied, including warranties of any kind for merchantability or fitness for particular use, with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. July 28, 2010