

ISO9001: 2015

ISO14001: 2015

## APPROVAL SPECIFICATIONS

Title. TACT SWITCH

Product Model. KAN0656-0701C1-C15

Customer's Part NO. \_\_\_\_\_

Customer's Model: \_\_\_\_\_

Customer's Approval Requested.

Please return this copy as a certification of your approval.

Checked by: \_\_\_\_\_ Date: \_\_\_\_\_

Approved by: \_\_\_\_\_ Date: \_\_\_\_\_

温州港源电子有限公司

Wenzhou Gangyuan Electronics Co.,Ltd

Address: No.2 Yonghe Yi Road, Chengdong  
Street, Yueqing City, Zhejiang Province, China.

Tel: 0577-06571538

Fax: 0577-62573066

Website: <http://www.gangyuan.com>





GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		2/12

## 变更履历表:



GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		3/12

**1、概述****GENERAL****1.1 适用范围****APPLICATION**

此规格书适用于机械式轻触开关的相关要求

This specification is applied to the requirements for tactile switch (mechanical contact)

**1.2 工作温度范围****Operating Temperature Range**

-30℃~80℃(在标准大气压、标准湿度条件下)

-30℃~80℃(Normal humidity, normal air pressure)

**1.3 贮藏温度范围****Storage Temperature Range**

-40℃~90℃(在标准大气压、标准湿度条件下)

-40℃~90℃(Normal humidity, normal air pressure)

**1.4 测试条件****Test Conditions**

在没有其它特定的条件下，应该在以下的条件下进行测试和测量：

Unless otherwise specified, tests and measurement shall be made in the following standard conditions:

常温.....5℃~35℃

Normal temperature.....5℃~35℃

标准湿度.....相对湿度 25%~85%

Normal humidity.....relative humidity 25%~85%

标准大气压.....86Kpa~106Kpa

Normal air pressure.....86Kpa~106Kpa

在制造过程中，测试和测量应该在以下的条件下进行：

If any doubt arise from the judgment, tests shall be conducted at the following conditions:

温度.....20℃±2℃

Temperature.....20℃±2℃

相对湿度.....65%±5%

Relative humidity.....65%±5%

环境气压.....86Kpa~106Kpa

Air pressure.....86Kpa~106Kpa

**1.5 保质期****Quality guarantee**

产品出货后在温度-5℃~35℃、湿度 25%~85%条件下，确保未开封状态保质期为 3 个月；

保管时尤其应注意避开高湿高温和有腐蚀性气体的环境

Stored at a condition of temperature -5℃~35℃,humidity 25%~85% and ensure that it be unsealed after delivery, it can be stored for 3 months.

Should especially avoid the environment of high humidity and corrosive gases



GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		4/12

**2. 详细说明**

## Detailed specification

2.1 外观: 应无影响、降低产品性能的缺陷;

Appearance: There should be no defects that affect the serviceability of product.

2.2 结构尺寸和安装尺寸: 应符合装配图要求;

Style and dimension: shall conform to the assemble drawings.

2.3 操作形式: 有触觉反应的操作

Type of actuating: Tactile feedback.

2.4 开关结构: 单回路单输出(具体的触点结构在装配图中已绘出);

Contact arrangement: 1 pole, 1 throw

(Details of contact arrangement are given in the assembly drawings.)

2.5 开关工作额定值: DC 12V 50mA (最大值) DC 1V 10μA (最小值)

Ratings: DC 12V 50mA (Max) DC 1V 10μA (Min)

**3. 电气性能:**



## ELECTRICAL SPECIFICATION

项 目 ITEM	试 验 条 件 TEST CONDITIONS	要 求 REQUIREMENTS
3.1 接触电阻 Contact Resistance	在以 5V 10mA 的直流电源或不低于1KHz的交流电源的电路中, 以一个等于 2 倍按力的静负荷施加于手柄中心  Applying a static load of 2 times operating force to the center of the stem, measurements shall be made by 5V DC 10mA or more than 1KHz AC small-current contact resistance meter.	$\leq 100m\Omega$
3.2 绝缘电阻 Insulation Resistance	在端子之间施加 DC 100V /min 的条件下, 测量端子之间底座、盖板的电阻值  Measurement shall be made following application of 100V DC potential, across terminals, and across terminals and cover, for one minute.	$\geq 100M\Omega$
3.3 介质耐压 Dielectric voltage proof	在端子之间施加 250V AC(50Hz 或 60Hz)/min 250V AC (50Hz or 60Hz) shall be applied across terminals, for one minute.	无击穿、无飞弧 There should be no breakdown and flashover



GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		5/12
ITEM	TEST CONDITIONS			REQUIREMENTS
3.4 触点抖动 Bounce	<p>按照正常使用时的力度轻按手柄中心（每秒 3~4 次），在导通和断开过程中测试开关抖动 Lightly striking the center of the stem at a rate encountered in normal use (3 to 4 times per second), and bounce shall be tested at "ON" and "OFF"</p>  <p>示波器</p>  <p><math>t</math> 为触点抖动时间</p>		ON-3ms max OFF-8ms max	

## 4. 机械性能:

## MECHANICAL SPECIFICATION


4.1 按力 Operating Force	<p>开关垂直于操作方向放置，在开关驱动件顶端中心逐渐施力，测量开关导通所需的最大力度。 Placing the switch such that the direction of switch operation is vertical and then gradually increasing the load applied to the center of the stem, the maximum load required for the switch to come to a stop shall be measured.</p>	260±50gf
4.2 最大行程 Full Travel	<p>开关垂直于操作方向放置，以一个等于 2 倍按力的静负荷施加在开关驱动件顶端中心，测量顶端移动的距离。 Placing the switch such that the direction of switch operation is vertical and then applying static load of 2times operating force to the center of the stem; the travel distance for the switch to come to a stop shall be measured.</p>	0.30±0.1mm



GANGYUAN

## APPROVAL SPECIFICATIONS

Product name		P/N	Version	Document No.	Page
Tact switch		KAN0656-0701C1-C15	A/00		6/12
项目 ITEM		试验条件 TEST CONDITIONS			要求 REQUIREMENTS
4.3	回弹力 Return Force	开关垂直于操作方向放置，在开关驱动件顶端中心下降至全行程后，测量顶端向自由位置转换的力度。 The sample switch is installed such that the direction of switch operation is vertical and upon depressing the stem in its center to the whole travel distance, the force of the stem to return to its free position shall be measured.			20gf Min
4.4	停止强度 Stop Strength	开关垂直于操作方向放置，从操作方向向驱动件施加 30N 的静负荷持续 1min。 Placing the switch such that the direction of switch operation is vertical, and then a static load of 30N shall be applied in the direction of stem operation for a period of 1 min.			无机械和电气损坏 There shall be no sign of damage mechanically and electrically.
4.5	手柄拔出 强度 Stem Strength	开关垂直于操作方向放置，反方向实施最大操作力，并测量手柄的行程范围。 Placing the switch such that the direction of switch operation is vertical, and then the maximum force to withstand a pull applied opposite to the direction of stem operation shall be measured.			20N min.
4.6	振动 Vibration	根据以下给定条件进行测试： Measurement shall be made following the test set forth below: (1) 振动频率范围: 10~55~10Hz Vibration frequency range: 10 to 55 to 10Hz (2) 振幅(峰—峰) : 1.5mm Amplitude: 1.5mm (3) 振动方向: 包括手柄行程方向在内的三个相互垂直的方向 Direction of vibration: Three mutually perpendicular direction including the direction of stem travel (4) 测试时间: 每次 2 小时 Duration: Each 2 hours.			Item 3 Item4.1 Item4.2 Item4.3
4.7	冲击 Shock	根据下列条件进行冲击试验 Test by following conditions (1) 安装方法: 正常安装 (1) installation method: normal (2) 加速度: 784m/s <sup>2</sup> (2) Acceleration: 784m/s <sup>2</sup> (3) 作用时间: 11ms (3) Acting time: 11ms (4) 测试方向: 6 个方向 (4) Test direction: 6 directions 冲击次数: 每个方向 3 次, 共计 18 次 (4) Times: 3 times/direction ,total 18 times			Item3 Item4.1 Item4.2 Item4.3





GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		7/12

## 5、环境耐久性:

## ENVIRONMENTAL SPECIFICATION

项目 ITEM	试验条件 TEST CONDITIONS	要求 REQUIREMENTS
5.1 低温测试 Resistance to low temperature	<p>样品应按照以下实验条件进行测试，实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试：  Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 h before measurements are made:</p> <p>(1) 温度: <math>-40 \pm 2^\circ\text{C}</math>  Temperature : <math>-40 \pm 2^\circ\text{C}</math></p> <p>(2) 时间: 96h  Time: 96h</p>	Item3 Item4.1 Item4.2 Item4.3
5.2 高温测试 Heat resistance	<p>样品应按照以下实验条件进行测试，实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试：  Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 h before measurements are made:</p> <p>(1) 温度: <math>90 \pm 2^\circ\text{C}</math>  temperature:<math>90 \pm 2^\circ\text{C}</math></p> <p>(2) 时间: 96h  time: 96h</p>	Item3 Item4.1 Item4.2 Item4.3
5.3 温度周期性测试 Change of temperature	<p>根据下面的测试要求进行 5 次循环的温度周期性测试，实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试。测试期间样品应保持干燥。  After 5 cycles of following conditions, the sample shall be allowed to stand under normal temperature and humidity conditions for 1 h. and measurements shall be made. During the test water drops shall be removed.</p> <p>A: <math>+90 \pm 2^\circ\text{C}</math>  B: <math>-40 \pm 2^\circ\text{C}</math>  C: 2小时  D: 1小时  E: 2小时  F: 1小时</p>	Item3 Item4.1 Item4.2 Item4.3
5.4 湿温测试 Moisture resistance	<p>样品应按照以下实验条件进行测试，实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试：  Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 h before measurements are made:</p> <p>(1) 温度: <math>60 \pm 2^\circ\text{C}</math>  temperature: <math>60 \pm 2^\circ\text{C}</math></p> <p>(2) 相对湿度: 90%~95%  relative humidity:90% to 95%</p> <p>(3) 时间: 96h  time: 96h</p>	接触电阻: $\leq 200\text{m}\Omega$ Contact resistance $\leq 200\text{m}\Omega$ 绝缘电阻: $\geq 10\text{M}\Omega$ Insulation Resistance $\geq 10\text{M}\Omega$ Item3.3 Item3.4 Item4.1 Item4.2 Item4.3



GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		8/12
项目 ITEM	试验 条件 TEST CONDITIONS			要求 REQUIREMENTS
5.5 硫化试验 Sulfuration resistance	<p>样品应按照以下实验条件进行测试，实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试：</p> <p>Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 h before measurements are made:</p> <ul style="list-style-type: none"> <li>(1) H<sub>2</sub>S 气体浓度: 3ppm±1ppm H<sub>2</sub>S gas concentration: 3ppm±1ppm</li> <li>(2) 时间: 96h Time: 96h</li> <li>(3) 温度: 40±2°C (90~95%RH) temperature: 40±2°C (90~95%RH)</li> </ul>		<p>接触电阻: ≤200mΩ Contact resistance≤200mΩ</p> <p>Item3.3 Item3.4 Item4.1 Item4.2 Item4.3</p>	
5.6 盐雾试验 Salt Mist	<p>在以下设定条件下进行测量:</p> <p>The switch shall be checked after following test:</p> <ul style="list-style-type: none"> <li>(1) 温度: 35°C±2°C temperature: 35°C±2°C</li> <li>(2) 盐溶液浓度: 5±1% (质量百分比) salt solution : 5±1%(solids by mass)</li> <li>(3) 时间: 48±1h Time: 48±1h</li> </ul> <p>实验后的盐沉积物后水冲掉 After test, salt deposit shall be removed by running water.</p>		<p>金属件上没有腐蚀斑点 No remarkable corrosion shall be recognized in metal part.</p>	
5.7 动作寿命 Operation life	<p>根据下面的测试要求进行测试:</p> <p>Measurement shall be made following the test set forth below:</p> <ul style="list-style-type: none"> <li>(1) DC 12V, 50mA 带负载 DC 12V, 50 mA resistive load</li> <li>(2) 按动速率: 2 次/秒 Rate of operation: 2 times/s</li> <li>(3) 按力: 按力的 1.5 倍 Operating Force: 1.5 times as much as Operating Force</li> <li>(4) 无故障寿命: 100,000 次 fault-free life:100,000 cycles</li> </ul>		<p>接触电阻≤1Ω Contact resistance≤1Ω</p> <p>绝缘电阻≥10MΩ Insulation Resistance≥10MΩ</p> <p>触点抖动 ON-20ms max Bounce OFF-20ms max</p> <p>按力: 初值的±30% Operating Force: initial value±30%</p> <p>Item3.3 Item4.2</p>	



GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		9/12
项目 ITEM	试验条件 TEST CONDITIONS			要求 REQUIREMENTS
5.8	可焊性 Solderability	<p>在以下设定条件下进行测量: Measurements shall be made following the test set forth below:</p> <p>(1) 焊接温度: <math>245 \pm 5^\circ\text{C}</math> Solder temperature : <math>245 \pm 5^\circ\text{C}</math></p> <p>(2) 浸入时间: <math>3s \pm 0.5s</math> Immersion time: <math>3s \pm 0.5s</math></p>		
5.9	防水等级 Waterproof grade	<p>1、IP6X:产品需抽负压，放置沙尘箱中 1 、 IP6X:Products to be placed in the negative pressure pumping, dust box</p> <p>2、IPX7: 短时间浸水，浸入规定压力的水中经规定的时间后外壳浸水量不至于达到有害程度,放置于一个潜水箱中，一般深度1米，试验时间为30min;</p> <p>2、IPX7 : Short time immersion in water, the provisions of the pressure of the shell by the prescribed time after water content not reach harmful levels, placed on adive in the water tank, the general depth of 1 meters, the testing time is 30min;</p>		
<b>6. 焊接条件:</b> <b>SOLDERING CONDITIONS:</b>				
6.1	手工焊接 Hand soldering	<p>请按以下条件进行焊接:</p> <p>(1) 焊锡温度: <math>\leq 350^\circ\text{C}</math></p> <p>(2) 连续焊接时间: <math>\leq 3</math> s</p> <p>Please practice according to below conditions:</p> <p>(1) Soldering temperature: <math>\leq 350^\circ\text{C}</math></p> <p>(2) Continuous soldering time: <math>\leq 3</math> s</p>		



GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		10/12
ITEM	推荐条件 Recommended conditions			
6.2 自动浸焊 Conditions for Auto-dip	项目 Items	条件 Condition		
	助焊剂附着量 Flux built-up	不附着于零部件贴装面的程度 Mounting surface should not be coated with flux		
	预热温度 Preheating temperature	印刷电路板焊接面的周围温度 100°C max. Ambient temperature of the soldered surface of PC board. 100°C max.		
	预热温度时间 Preheating time	60s max.		
	焊接温度 Soldering temperature	260°C max.		
	焊接浸渍时间 Continuous dipping time	5s max.		
	焊接次数 Number of soldering	最多两次 2 times max.		

**注意事项(Notes):**

a、印刷基板的焊盘尺寸参见产品图。

The pad size of the printed substrate is shown in the product diagram.

b、在使用烙铁的情况下，焊锡温度应在 350°C 以下、3 秒以内。

In the case of using soldering iron, soldering conditions shall be 350°C max and 3 sec.max.

c、防止助焊剂从开关的顶端渗入

Prevent flux penetration from the top of the switch

d、开关浸焊后，注意不要用溶剂或类似品清洗开关。

After switches were soldered,please be careful not to clean switches with solvent or other similar products.

e、浸焊后，注意不要在顶部施加负荷。

Right after switches were soldered;please be careful not to load to on the knobs of switches.

f、注意不要施加超负荷的压力或晃动开关。

Please be cautions not to give excessive static load or shock to switches.

g、开关浸焊后，印刷基板注意不要叠放。



Please be careful not to pile up P.W.B.after switches were soldered




GANGYUAN

## APPROVAL SPECIFICATIONS

Product name	P/N	Version	Document No.	Page
Tact switch	KAN0656-0701C1-C15	A/00		11/12

General tolerance:  $\pm 0.2\text{mm}$  H=7.0

NO.	NAME	MATERIAL	QTY.	FINISHING
1	TERMINAL	Brass	1	Silver plating
2	CASE	PA66	1	Black
3	CONTACT	SUS	1	Ag plating
4	Waterproof membrane	PI	1	Yellow
5	Rubber pad	SILICONE RUBBER	1	Black
6	COVER	PA66	1	Black
7	STEM	PA66	1	Black



## 技术要求:

1. 成品包装数量每盒000只。
2. 纸带编好后前端空5个孔，约70mm左右，后端也空5个孔，约70mm左右。

环保要求: 符合公司WGY/EM431.001-2005标准

序号	部件名称	图号	材料	产品包装带						
				材料	HRC	图样标记	重量	比例	标记处数	更改文件号
9	胶带									
8	防水膜									
7	模校垫									
6	手柄	ARAa7.870.070	增强尼龙	PAG6-G30	1	黑色	设计	会	图样标记	材料
5	盖板	ARAa8.010.010	PEI	F•Ag/C5210-EH-TA	1	镀银	绘图	审	重量	HRC
4	簧片	8WCY-557.001	覆银轴销		1	镀银	批准		比例	
3	底座	ARAa3.604.036	增强尼龙	PAG6-G30	1	黑色				
2	接线片	ARAa7.750.017	高精铜	H65Y t=0.3mm	1	镀银				
1			材料规格及牌号		数量	备注	共1页	第1页		
			日期							