



SPECIFICATION OF PRODUCT

承认书

CUSTOMER:		
DESCRIPTION: _	Piezo Buzzer	
FUSHENG P/N:	FSD-2312	
CUSTOMER P/N:		
DATE:	2018-8-28	

CUSTOMER	APPROVER	CHECKER
1/3	Yunqing Wu	Bing Yan

泰州福声电子科技有限公司

泰州福声电子科技有限公司-----电声产品专业制造商 FUSHENG ELECTRONICS-----Acoustic Components Professional Manufacturer

地址:江苏省泰州市海陵区凤凰西路 168 号

电话: 0086-523-86219066 传真: 0086-523-81601108

邮箱: sales@electronic-tech.cn


网址: www.tzfsdz.com



1.SPECIFICATION 规格

No.	Item	Unit	Specification	Condition
1	Oscillation Frequency	Hz	2900±500	
2	Operating Voltage	VDC	3~24	
3	Rated Voltage	VDC	12	2
4	Current Consumption	mA	MAX. 10	at Rated Voltage
5	Sound Pressure Level	dB	MIN. 85	at 10cm at Rated Voltage
6	Operating Temperature	$^{\circ}$	-20 ~ +70	
7	Storage Temperature	$^{\circ}$	-30 ~ +85	
8	Dimension	mm	Ф23.0 х Н12	See appearance drawing
9	Weight (MAX)	gram	4	
10	Housing Material		ABS(Black)	
11	Leading Pin		Wire Type	See appearance drawing
12	Environmental Protection Regulation		RoHS	

2. APPEARANCE DRAWING 尺寸图




3.TESTING METHOD 测量方式

Standard Measurement conditions


Temperature:25±2°C Humidity:45-65%

Acoustic Characteristics:


The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below



In the measuring test, buzzer is placed as follows:



4. VOLTAGE / CURRENT / SOUND PRESSURE CHARACTERISTICS



5. RELIABILITY TEST 可靠性测试

NO.	ITEM	TEST CONDITION AND REQUIREMENT		
1	High Temperature Test (Storage)	After being placed in a chamber with 80 2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: 10dB.		
2	Low Temperature Test (Storage)	After being Placed in a chamber with -30 2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: 10dB.		
3	Humidity Test	After being Placed in a chamber with 90-95% R.H. at 40 2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: 10dB.		
4	Temperature Cycle Test	The part shall be subjected to 5 cycles. One cycle shall be consist of: +70°C +25°C +25°C +25°C -20°C 3hours Allowable variation of SPL after test: 10dB.		
5	Drop Test	Drop on a hard wood board of 4cm thick, any directions ,6 times, at the height of 75cm. Allowable variation of SPL after test: 10dB.		

泰州福声电子科技有限公司-----电声产品专业制造商

FUSHENG ELECTRONICS-----Acoustic Components Professional Manufacturer

6	Vibration Test	After being applied vibration of amplitude of 1.5mm with 10 to 55 Hz band of vibration frequency to each of 3 perpendicular directions for 2 hours. Allowable variation of SPL after test: 10dB.
7	Solderability Test	Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of +300 5°C for 3 1 seconds. 90% min. lead terminals shall be wet with solder (Except the edge of terminals).
8	Terminal Strength Pulling Test	The force of 9.8N(1.0kg) is applied to each terminal in axial direction for 10 seconds. No visible damage and cutting off.

TEST CONDITION.

Standard Test Condition : a) Temperature: $+5 \sim +35^{\circ}$ b) Humidity: 45-85% c) Pressure: 860-1060mbar a) 温度: $+5 \sim +35^{\circ}$ b) 湿度: 45-85% c) 气压: 860-1060mbar c) 气压: 860-1060mbar a) Temperature: $+25\pm 2^{\circ}$ b) Humidity: 60-70% c) Pressure: 860-1060mbar c) 气压: 860-1060mbar c)