



SPECIFICATION OF PRODUCT

承认书

CUSTOMER:		
DESCRIPTION: _	Piezo Buzzer	
FUSHENG P/N: _	FUET-1580-12	
CUSTOMER P/N:		
DATE:	2018-8-28	

CUSTOMER	APPROVER	CHECKER
	Yunqing Wu	Bing Yan

泰州福声电子科技有限公司

泰州福声电子科技有限公司-----电声产品专业制造商

FUSHENG ELECTRONICS-----Acoustic Components Professional Manufacturer

地址:江苏省泰州市海陵区凤凰西路 168 号

电话: 0086-523-86219066 传真: 0086-523-81601108


邮箱: sales@electronic-tech.cn

网址: www.tzfsdz.com

1.SPECIFICATION 规格

No.	Item	Unit	Specification	Condition
1	Oscillation Frequency	Hz	4000	
2	Operating Voltage	VDC	3-16	
3	Rated Voltage	VDC	12	
4	Current Consumption	mA	MAX. 100	at Rated Voltage
5	Sound Pressure Level	dB	MIN. 80	at 10cm at Rated Voltage
6	Operating Temperature	$^{\circ}$	-20 ~ +70	
7	Storage Temperature	$^{\circ}$	-30 ~ +80	
8	Dimension	mm	14.8x 14.8x H 7.4	See appearance drawing
9	Weight (MAX)	gram	2	
10	Housing Material		PPS(Gray)	
11	Leading Pin		Tin Plated Brass(Sn)	See appearance drawing
12	Environmental Protection Regulation		RoHS	

2. APPEARANCE DRAWING 尺寸图



Tol: ± 0.5 Unit: mm


3.TESTING METHOD 测量方式

Standard Measurement conditions


Temperature:25±2°C Humidity:45-65%

Acoustic Characteristics:


The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below




In the measuring test, buzzer is placed as follows:




4. VOLTAGE/CURRENT/SOUND PRESSURE CHARACTERISTICS





5. Recommend Driving Circuit




The base current Ib should high enough so that it saturates the collector current of the transistor with the CB load.

6. Soldering Condition

(1)Recommendable reflow soldering condition is as follows (Reflow soldering is twice)

Note: It is requested that reflow soldering should be executed after heat of product goes down to normal.



Heat resistant line

(Used when heat resistant reliability test is performed)

(2)Manual soldering

Manual soldering temperature 350 °C within 5 sec.

7. RELIABILITY TEST 可靠性测试

NO.	ITEM	TEST CONDITION AND REQUIREMENT	
1	High Temperature Test (Storage)	After being placed in a chamber with 80 2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: 10dB.	
2	Low Temperature Test (Storage)	After being Placed in a chamber with -30 2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: 10dB.	
3	Humidity Test	After being Placed in a chamber with 90-95% R.H. at 40 2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: 10dB.	
4	Temperature Cycle Test	The part shall be subjected to 5 cycles. One cycle shall be consist of: +70°C +25°C +25°C -20°C -20°C 3hours Allowable variation of SPL after test: 10dB.	
5	Drop Test	Drop on a hard wood board of 4cm thick, any directions ,6 times, at the height of 75cm. Allowable variation of SPL after test: 10dB.	
6	Vibration Test	After being applied vibration of amplitude of 1.5mm with 10 to 55 Hz band of vibration frequency to each of 3 perpendicular directions for 2 hours. Allowable variation of SPL after test: 10dB.	
7	Solderability Test	Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of +300 5°C for 3 1 seconds. 90% min. lead terminals shall be wet with solder (Except the edge of terminals).	
8	Terminal Strength Pulling Test	The force of 9.8N(1.0kg) is applied to each terminal in axial direction for 10 seconds. No visible damage and cutting off.	

TEST CONDITION.

 Standard Test Condition
 : a) Temperature: +5~+35℃
 b) Humidity: 45-85%
 c) Pressure: 860-1060mbar

 一般测试条件
 : a) 温度: +5~+35℃
 b) 湿度: 45-85%
 c) 气压: 860-1060mbar

 Judgment Test Condition
 : a) Temperature: +25±2℃
 b) Humidity: 60-70%
 c) Pressure: 860-1060mbar

 争议时测试条件
 : a) 温度: +25±2℃
 b) 湿度: 60-70%
 c) 气压: 860-1060mbar

8. PACKING STANDARD 包装

