

MAPX	MODIFICATION	DATE

NOTES:

- 1. HOUSING: SEE NOTES, UL94V-0 .
- TERMINAL: SEE NOTES.
- SHELL: SEE NOTES.



SPECIFICATION:

- 1. ELECTRICAL CHARACTERISTIC:
 - CONTACT RESISTANCE: 30MΩ MAX
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1MIN
 - INSULATION RESISTANCE: 1000MΩ MIN
- 2. MECHANICAL CHARACTERISTIC:
 - INSERTION FORCE: 35N(3.57KGF) MAX
 - EXTRACTION FORCE: 10~35N(1.02~3.57KGF)MIN
 - DURABILITY: 1500 CYCLES EXTRACTION FORCE:10~35N
5000 CYCLES MIN
5000 CYCLES EXTRACTION FORCE:3~35N

- 3. ENVIRONMENTAL:
 - OPERATING TEMPERATURE: -55°C+85°C

4. Contact finish:

- 01:Selective Gold Flash
- 02:Selective Gold 3U"
- 03:Selective Gold 5U"
- 04:Selective Gold 15U"
- 05:Selective Gold 30U"



RBCOMMENDBD P. C. B PATTBRN LAY OUT

产品图 PRODUCT CHART DWG				深圳市精拓金电子有限公司						
公差一览表 TOLERANCE UNLESS OTHERWISE				单位	MM	制图	尹先华	制图料号	907-411A1026P10200	
X.	±0.25	X.	±5.°	UNITS		DRAWING		PRODUCT PART NO.		
.X	±0.20	.X	±2.°	比例	1:1	审核	郭治富	产品名称	AF90度双层17.0沉板鱼叉脚有边铁壳PBT	
.XX	±0.15	.XX	±1.°	SCALE		CHKD		PRODUCT NO.	黑胶24H	
.XXX	±0.10	.XXX	±0.5°	日期	2021-04-13	核准	黄国荣	角法	版本	AO
				DATE		APPD		VIEW	VER	

