


Features

- DFN2510 package
- Protects up to 4-Lines operating at 3.3V
- R2R + Zener technology
- Low clamping voltage
- Low leakage current
- Ultra low capacitance (0.15pF typical I/O to I/O)
- ESD Protection for high-speed data lines to:
 - IEC 61000-4-2 ±10KV contact ±15KV air
- RoHS compliant


Applications

- USB 3.0/3.1
- HDMI 1.4/2.0, Display Port 1.3, eSATA
- Unified Display Interface (UDI)
- Digital Visual Interface (DVI)
- High speed serial interfaces

SESUC3V3D2510-10U



DFN2510



Schematic Diagram

Absolute Maximum Ratings

(T_A=25°C, Unless otherwise specified.)

Parameter	Symbol	Value	Unit
Junction Temperature	T _J	-55 to +125	°C
Storage Temperature	T _{STG}	-55 to +150	°C
Lead Soldering Temperature	T _L	260 (10sec.)	°C
Peak Pulse Current (t _P = 8/20μS)	I _{PP}	3	A
IEC 61000-4-2 Contact (ESD)	VESD	±10	kV
IEC 61000-4-2 Air (ESD)	VESD	±15	kV

Electrical Characteristics

(T_A=25°C, Unless otherwise specified.)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Reverse stand-off Voltage	V _{RWM}				3.3	V
Reverse Breakdown Voltage	V _{BR}	I _T =1mA	5	6		V
Reverse Leakage Current	I _R	V _R =3.3V		0.01	1	μA
Clamping Voltage (IEC 61000-4-5)	V _C	I _{PP} =3A, T _P =8/20μS		10		V
Trigger Voltage (IEC 61000-4-2)	V _T	V _{ESD} =8kV		135		V
Clamping Voltage (IEC 61000-4-2)	V _C	V _{ESD} =8kV		20		V
Junction Capacitance	C _J	V _R =0V, f=1MHz, I/O to I/O		0.15		pF
	C _J	V _R =0V, f=1MHz, I/O to GND		0.35		pF

Typical Characteristic Curves

Fig.1 Pulse Waveform-ESD(IEC61000-4-2)




Fig.2 IEC61000-4-2 +8kV Contact ESD Clamping Waveform




Fig.3 Eye Diagram - USB3.1 at 10Gbps per channel (with SESUC3V3D2510-10U)





Fig.4 Insertion Loss S21 - I/O to I/O



Order Information

Device	Package	Carrier	Quantity	HSF Status
SESUC3V3D2510-10U	DFN2510	Tape & Reel (7")	3000pcs / Reel	RoHS Compliant

Revision history


Date	Revision	Description of changes
26-January-2016	A0	First issue

CAUTION / WARNING

- Information in this document is believed to be accurate and reliable. However, SEMITEL does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.
- Users should independently evaluate the suitability of and test each product selected for their own applications, and SEMITEL assumes no liability whatsoever relating to the choice, selection or use of the SEMITEL products and services described herein.
- SEMITEL reserves the right to change or update, without notice, any information contained in this publication; to change, without notice, the design, construction, processing, or specification of any product; and to discontinue or limit production or distribution of any product.
- Information in this document supersedes and replaces all information previously supplied.
- Products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an SEMITEL product can reasonably be expected to result in personal injury, death or severe property or environmental damage. SEMITEL accepts no liability for inclusion and/or use of SEMITEL products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.
- This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.
- Resale of SEMITEL products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by SEMITEL for the SEMITEL product or service described herein and shall not create or extend in any manner whatsoever, any liability of SEMITEL.
- SEMITEL expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. SEMITEL only obligations are those in the SEMITEL Standard Terms and Conditions of Sale and in no case will SEMITEL be liable for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of its products.

Specifications are subject to change without notice

© Copyright 2005, Semitel Electronics

 . ® is a registered trademark of Semitel Electronics

All rights reserved