






REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE



PCB LAYOUT


NOTES1:  
 UL Standard  
 1. Rated Voltage/Current : 300V / 8A  
 2. Withstanding Voltage : AC1600V/1Min.  
 VDE Standard  
 1.

Pollution Degree	2
Overtoltage Category	II
Rate Impulse Voltage(KV)	2.5KV
Rate Voltage(V)	250V
Rate Current(A)	7A

NOTES2:  
 1. Dimension shall be interpreted per ASME Y14.5-2009  
 2. Pitch : 3.50mm, Poles : N=2~22P  
 3. Operating temperature: -40°C~+105°C  
 4. Undimensioned Tolerances:

Pitch Range In mm	Nominal Dimension Range In mm				0.1/10		
	Over 6 TO 10	Over 10 TO 24	Over 30 TO 60	Over 60 TO 150			
±0.15	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±2*

5. RoHS Compliance



ITEM	NAME OF PART	MATERIAL	NOTES
3	SCREW CAP	BRASS	
2	PIN	BRASS	Sn Plated
1	HOUSING	PA66	UL94V-0

PART NO.: /

APPD: *Aaron/olya*

CHKD: *Xm19/15*

DRFT: Yz 10/13/15"

DEGSON® NINGBO DEGSON ELECTRICAL CO., LTD

NAME: 15EDGVM-3.5-XXP-1Y-00A(H)

TITLE: CUSTOMER DRAWING

DRAWING NO.: 15EDGVM-3.5-C01

THIRD ANGLE PROJECTION

REV	T0
SHEET	1/1
SCALE	1:1