

HXB Series

• 105°C 1,000~2,000Hrs assured.

- Non-solvent proof.
- Low Impedance, Long Life.
- Height 7mm.
- For LED TV PSU, DVD Driver.
- RoHS compliant.
- Halogen-free capacitors are also available.

HXA

HXB

Low Imp. Long Life


**SPECIFICATIONS**

Item	Characteristics																										
Rated Voltage Range	6.3 ~ 50 V _{DC}																										
Operating Temperature Range	-40 ~ +105°C																										
Capacitance Tolerance	$\pm 20\%$ (M) (at 20°C, 120Hz)																										
Leakage Current	I = 0.01CV(μA) or 3μA, whichever is greater. Where, I:Max. Leakage current(μA), C:Nominal capacitance(μF), V:Rated voltage(V _{DC}) (at 20°C, 2 minutes)																										
Dissipation Factor(Tanδ)	<table border="1"> <tr> <td>Rated voltage(V_{DC})</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr> <tr> <td>Tanδ(Max.)</td><td>0.22</td><td>0.19</td><td>0.16</td><td>0.14</td><td>0.12</td><td>0.10</td></tr> </table> (at 20°C, 120Hz)						Rated voltage(V _{DC})	6.3	10	16	25	35	50	Tanδ(Max.)	0.22	0.19	0.16	0.14	0.12	0.10							
Rated voltage(V _{DC})	6.3	10	16	25	35	50																					
Tanδ(Max.)	0.22	0.19	0.16	0.14	0.12	0.10																					
Temperature Characteristics (Max. Impedance ratio)	<table border="1"> <tr> <td>Rated voltage(V_{DC})</td><td>6.3</td><td>10</td><td>16</td><td>25~50</td><td></td><td></td></tr> <tr> <td>Z(-25°C)/Z(20°C)</td><td>2</td><td>2</td><td>2</td><td>2</td><td></td><td></td></tr> <tr> <td>Z(-40°C)/Z(20°C)</td><td>6</td><td>4</td><td>3</td><td>3</td><td></td><td></td></tr> </table> (at 120Hz)						Rated voltage(V _{DC})	6.3	10	16	25~50			Z(-25°C)/Z(20°C)	2	2	2	2			Z(-40°C)/Z(20°C)	6	4	3	3		
Rated voltage(V _{DC})	6.3	10	16	25~50																							
Z(-25°C)/Z(20°C)	2	2	2	2																							
Z(-40°C)/Z(20°C)	6	4	3	3																							
Load Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage is applied for 2,000 hours at 105°C. (where 1,000 hours for Ø4) Capacitance change $\leq \pm 25\%$ of the initial value Tan δ $\leq 200\%$ of the initial specified value Leakage current \leq The initial specified value																										
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied. The rated voltage shall be applied to the capacitors for a minimum of 30 minutes, at least 24 hours and not more than 48 hours before the measurements. Capacitance change $\leq \pm 25\%$ of the initial value Tan δ $\leq 200\%$ of the initial specified value Leakage current \leq The initial specified value																										
Others	Satisfied characteristics KS C IEC 60384-4																										

RATINGS OF HXB Series

V _{DC} μF	6.3	10	16	25	35	50
1						
2.2						
4.7						
10						
22						
33	4X7 1.50 130	4X7 1.50 130			5X7 0.70 165	6.3X7 0.35 260
	5X7 0.70 165	5X7 0.70 165	5X7 0.70 165	5X7 0.70 165	6.3X7 0.35 260	6.3X7 0.35 260
47	5X7 0.70 165	5X7 0.70 165	5X7 0.70 165	6.3X7 0.35 260	8X7 0.17 450	8X7 0.17 450
68	6.3X7 0.35 260	6.3X7 0.35 260	6.3X7 0.35 260	6.3X7 0.35 260	8X7 0.17 450	8X9 0.15 500
100	6.3X7 0.35 260	6.3X7 0.35 260	6.3X7 0.35 260	8X7 0.17 450	8X9 0.15 500	
150	6.3X7 0.35 260	6.3X7 0.35 260	8X7 0.17 450	8X9 0.15 500		
220	8X7 0.17 450	8X7 0.17 450	8X9 0.15 500			
330	8X7 0.17 450	8X9 0.15 500				
390	8X9 0.15 500					

↑↑
 Rated Ripple Current (mArms/105°C, 100kHz)
 Impedance (Ω max./20°C, 100kHz)
 Case Size Ø D × L (mm)

DIMENSIONS OF HXB Series Unit(mm)

Marking : DARK BROWN SLEEVE, SILVER INK

Ø D	4	5	6.3	8
Ø d			0.45	
F	1.5	2.0	2.5	3.5
Ø D'			Ø D + 0.5 max.	
L'			L + 1.0 max.	

※ Ø 8 x 9 L, Ø d=0.60

RATED RIPPLE CURRENT MULTIPLIERS

Frequency Multipliers

Cap.(μF)	Freq.(Hz)	120	1k	10k	50k	100k
1 ~ 150		0.40	0.75	0.90	0.95	1.00
220 ~ 330		0.50	0.85	0.94	0.97	1.00