

1	2	3	4	5	6																																																															
<table border="1"> <thead> <tr> <th colspan="2">part no.</th> <th rowspan="2">ØD</th> <th colspan="2">wire gauge</th> <th rowspan="2">stripping length</th> <th rowspan="2">Recommended Hand Crimp Tool</th> <th rowspan="2">Note</th> </tr> <tr> <th>silver plated</th> <th>gold plated</th> <th>mm²</th> <th>AWG</th> </tr> </thead> <tbody> <tr> <td>09 15 000 6107*</td> <td>09 15 000 6127*</td> <td>0,90</td> <td>0,14-0,37</td> <td>26-22</td> <td rowspan="6">8</td> <td>09 99 000 0888 09 99 000 0001</td> <td>*only for four indent crimping tool adjusting Ø0,1</td> </tr> <tr> <td>09 15 000 6104</td> <td>09 15 000 6124</td> <td>0,90</td> <td>0,14-0,37</td> <td>26-22</td> <td>09 99 000 0110 09 99 000 0021</td> <td></td> </tr> <tr> <td>09 15 000 6103</td> <td>09 15 000 6123</td> <td>1,10</td> <td>0,5</td> <td>20</td> <td>09 99 000 0888</td> <td></td> </tr> <tr> <td>09 15 000 6105</td> <td>09 15 000 6125</td> <td>1,30</td> <td>0,75</td> <td>18</td> <td>09 99 000 0001</td> <td></td> </tr> <tr> <td>09 15 000 6102</td> <td>09 15 000 6122</td> <td>1,45</td> <td>1</td> <td>18</td> <td>09 99 000 0110</td> <td></td> </tr> <tr> <td>09 15 000 6101</td> <td>09 15 000 6121</td> <td>1,75</td> <td>1,5</td> <td>16</td> <td>09 99 000 0021</td> <td></td> </tr> <tr> <td>09 15 000 6106</td> <td>09 15 000 6126</td> <td>2,25</td> <td>2,5</td> <td>14</td> <td>6</td> <td>09 99 000 0888 09 99 000 0001</td> <td></td> </tr> </tbody> </table>						part no.		ØD	wire gauge		stripping length	Recommended Hand Crimp Tool	Note	silver plated	gold plated	mm²	AWG	09 15 000 6107*	09 15 000 6127*	0,90	0,14-0,37	26-22	8	09 99 000 0888 09 99 000 0001	*only for four indent crimping tool adjusting Ø0,1	09 15 000 6104	09 15 000 6124	0,90	0,14-0,37	26-22	09 99 000 0110 09 99 000 0021		09 15 000 6103	09 15 000 6123	1,10	0,5	20	09 99 000 0888		09 15 000 6105	09 15 000 6125	1,30	0,75	18	09 99 000 0001		09 15 000 6102	09 15 000 6122	1,45	1	18	09 99 000 0110		09 15 000 6101	09 15 000 6121	1,75	1,5	16	09 99 000 0021		09 15 000 6106	09 15 000 6126	2,25	2,5	14	6	09 99 000 0888 09 99 000 0001	
part no.		ØD	wire gauge		stripping length	Recommended Hand Crimp Tool	Note																																																													
silver plated	gold plated		mm²	AWG																																																																
09 15 000 6107*	09 15 000 6127*	0,90	0,14-0,37	26-22	8	09 99 000 0888 09 99 000 0001	*only for four indent crimping tool adjusting Ø0,1																																																													
09 15 000 6104	09 15 000 6124	0,90	0,14-0,37	26-22		09 99 000 0110 09 99 000 0021																																																														
09 15 000 6103	09 15 000 6123	1,10	0,5	20		09 99 000 0888																																																														
09 15 000 6105	09 15 000 6125	1,30	0,75	18		09 99 000 0001																																																														
09 15 000 6102	09 15 000 6122	1,45	1	18		09 99 000 0110																																																														
09 15 000 6101	09 15 000 6121	1,75	1,5	16		09 99 000 0021																																																														
09 15 000 6106	09 15 000 6126	2,25	2,5	14	6	09 99 000 0888 09 99 000 0001																																																														
<table border="1"> <tr> <td rowspan="2"> </td> <td colspan="2">All Dimensions in mm Original Size DIN A4</td> <td>Scale 2:1</td> <td colspan="2">Free size tol.</td> <td colspan="2">Ref.</td> </tr> <tr> <td colspan="2"></td> <td></td> <td colspan="2"></td> <td colspan="2">Sub.</td> </tr> </table>							All Dimensions in mm Original Size DIN A4		Scale 2:1	Free size tol.		Ref.							Sub.																																																	
	All Dimensions in mm Original Size DIN A4		Scale 2:1	Free size tol.			Ref.																																																													
						Sub.																																																														
<table border="1"> <tr> <td rowspan="2"> </td> <td colspan="2">All rights reserved</td> <td>Created by RULLKOETTER</td> <td>Inspected by SCHNIEDER</td> <td>Standardisation RUETERA</td> <td>Date 2018-05-29</td> <td>State Final Release</td> </tr> <tr> <td colspan="2">Department EL PD - DE</td> <td colspan="4">Title Han D crimp contacts male</td> <td>Doc-Key / ECM-Nr. 100086611/UGD/006/B 500000135752</td> </tr> </table>							All rights reserved		Created by RULLKOETTER	Inspected by SCHNIEDER	Standardisation RUETERA	Date 2018-05-29	State Final Release	Department EL PD - DE		Title Han D crimp contacts male				Doc-Key / ECM-Nr. 100086611/UGD/006/B 500000135752																																																
	All rights reserved		Created by RULLKOETTER	Inspected by SCHNIEDER	Standardisation RUETERA		Date 2018-05-29	State Final Release																																																												
	Department EL PD - DE		Title Han D crimp contacts male				Doc-Key / ECM-Nr. 100086611/UGD/006/B 500000135752																																																													
<table border="1"> <tr> <td colspan="3">HARTING Electric GmbH & Co. KG D-32339 Espelkamp</td> <td>Type TB</td> <td colspan="2">Number 09 15 000 61XX</td> <td>Rev. B</td> <td>Page 1/1</td> </tr> </table>						HARTING Electric GmbH & Co. KG D-32339 Espelkamp			Type TB	Number 09 15 000 61XX		Rev. B	Page 1/1																																																							
HARTING Electric GmbH & Co. KG D-32339 Espelkamp			Type TB	Number 09 15 000 61XX		Rev. B	Page 1/1																																																													