




HIGH-VOLTAGE HIGH-CURRENT DARLINGTON TRANSISTOR ARRAYS

The HT2003A are monolithic high-voltage, high-current Darlington transistor arrays. Each consists of seven n-p-n Darlington pairs that feature high-voltage outputs with common-cathode clamp diodes for switching inductive loads. The collector-current rating of a single Darlington pair is 500 mA. The Darlington pairs may be paralleled for higher current capability. Applications include relay drivers, hammer drivers, lamp drivers, display drivers (LED and gas discharge), line drivers, and logic buffers.

The HT2003A has a 2.7-k Ω series base resistor for each Darlington pair for operation directly with TTL or 5-V CMOS devices.




ORDERING INFORMATION

HT2003ANZ DIP
HT2003ARZ SOP


- 500-mA Rated Collector Current (Single Output)
- High-Voltage Outputs . . . 50 V
- Output Clamp Diodes
- Inputs Compatible With Various Types of Logic
- Relay Driver Applications
- Ordering Information

Operation Temperature	PKG Type	Ordering part number
-40°C ~ 85°C	DIP - 16	HT2003ANZ
	SOP - 16	HT2003ARZ

LOGIC SYMBOL




LOGIC DIAGRAM



SCHEMATICS (each Darlington Pair)

All resistor values shown are nominal.

$$\text{HT2003A: } R_B = 2.7 \text{ k}\Omega$$



**Absolute Maximum Ratings (Ta =25°C)**

Parameter	Symbol	Limit Values		Unit
		min.	max.	
Output Sustaining Voltage	V _{CE(SUS)}	-0.5	50	V
Output Current	I _{OUT}	500		mA/ch
Input Voltage	V _{IN}	-0.5	30	V
Clamp Diode Reverse Voltage	V _R	50		V
Clamp Diode Forward Current	I _F	500		mA
Power Dissipation	DIP	1.15		W
	SOP	0.95		
Operating Temperature	T _{opr}	-40	85	°C
Storage Temperature	T _{stg}	-55	150	°C

* Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

Recommended Operating Conditions
(Ta=-40~85°C)

Parameter	Symbol	Test Condition	Limit Value			Unit
			Min	Typ	Max	
Output Sustaining Voltage	V _{CE(SUS)}		0	-	50	V
Output Current	DIP	T _{pw} =25ms,Duty=10%, 7 Circuits	0	-	370	mA/ch
		T _{pw} =25ms,Duty=30%, 7 Circuits	0	-	200	
	SOP	T _{pw} =25ms,Duty=10%, 7 Circuits	0	-	290	
		T _{pw} =25ms,Duty=30%, 7 Circuits	0	-	150	
Input Voltage	V _{IN}		0	-	30	V
Clamp Diode Reverse Voltage	V _R		-	-	50	V
Clamp Diode Forward Current	I _F		-	-	400	mA
Power Dissipation	DIP		-	-	0.52	W
	SOP		-	-	0.4	

Electrical characteristics, $T_A = 25^\circ\text{C}$ (unless otherwise noted)


Parameter	Test Fig.	Test Conditions		Min	Typ	Max	Unit
$V_{I(on)}$ On-state Input Voltage	6	$V_{CE}=2\text{V}$	$I_C=125\text{mA}$				V
			$I_C=200\text{mA}$			2.4	
			$I_C=250\text{mA}$			2.7	
			$I_C=275\text{mA}$				
			$I_C=300\text{mA}$			3	
			$I_C=350\text{mA}$				
$V_{CE(sat)}$ Collector-emitter saturation voltage	5	$I_I=250\text{\mu A}$	$I_C=100\text{mA}$		0.9	1.1	V
		$I_I=350\text{\mu A}$	$I_C=200\text{mA}$		1	1.3	
		$I_I=500\text{\mu A}$	$I_C=350\text{mA}$		1.2	1.6	
I_{CEX} Collector outoff current	1	$V_{CE}=50\text{V}$	$I_I=0$			50	uA
	2	$V_{CE}=50\text{V}, T_A=85^\circ\text{C}$	$I_I=0$			100	
h_{FE} DC Current Transfer Ratio	5	$V_{CE}=2\text{V}, I_{OUT}=350\text{mA}$		1000	-	-	
V_F Clamp forward voltage	8	$I_F=350\text{mA}$			1.7	2	V
$I_{I(off)}$ Off-state input current	3	$V_{CE}=50\text{V}$ $T_A=85^\circ\text{C}$	$I_C=500\text{\mu A}$	50	65		uA
I_I Input current	4	$V_I=2.4\text{V}$			0.4	0.7	mA
		$V_I=5\text{V}$					
		$V_I=12\text{V}$					
I_R Clamp reverse current	7	$V_R=50\text{V}$				50	uA
		$V_R=50\text{V}$	$T_A=85^\circ\text{C}$			100	
C_I Input capacitance		$V_I=0$	$f=1\text{MHz}$		15	25	pF

Switching Characteristics, $T_A=25^\circ\text{C}$

Parameter	Test Conditions	Min	Typ	Max	Unit
t_{PLH} Propagation delay time, low-to-high-level output	See Figure 9		0.25	1	us
t_{PHL} Propagation delay time, high -to- low -level output			0.25	1	us
V_{OH} High-level output voltage after switching	$V_S=50\text{V}, I_O=300\text{mA},$ See Figure 10	V_S-20			mV

* EOS (Electrical Over Stress) Immunity Level

Test Circuit








Test conditions	
V_{CC}	12V
Power on time	5000ms
Current max	1.0A
IN	pin4
OUT	pin13

t_E (Endurance time) : time until IC damage / Criterion : IC should survive EOS


EOS Immunity Level: More than 5000ms



PARAMETER MEASUREMENT INFORMATION

Figure 1. I_{CEX} Test CircuitFigure 2. I_{CEX} Test CircuitFigure 3. $I_{I(off)}$ Test CircuitFigure 4. I_I Test Circuit

NOTE: I_I is fixed for measuring $V_{CE(sat)}$, variable for measuring h_{FE} .

Figure 5. h_{FE} , $V_{CE(sat)}$ Test CircuitFigure 6. $V_{I(on)}$ Test Circuit





Figure 7. I_R Test CircuitFigure 8. V_F Test Circuit

Figure 9. Propagation Delay-Time Waveforms



NOTES: A. The pulse generator has the following characteristics: PRR = 12.5 kHz, $Z_0 = 50 \Omega$.

B. C_L includes probe and jig capacitance.

C. $V_{IH} = 3$ V;



TYPICAL CHARACTERISTICS

COLLECTOR-EMITTER
SATURATION VOLTAGE
vs
COLLECTOR CURRENT
(ONE DARLINGTON)




Figure 11

COLLECTOR-EMITTER
SATURATION VOLTAGE
vs
TOTAL COLLECTOR CURRENT
(TWO DARLINGTONS PARALLELED)




Figure 12

COLLECTOR CURRENT
vs



INPUT CURRENT




Figure 13

THERMAL INFORMATION




Figure 14





Figure 15

POWER DISSIPATION



APPLICATION INFORMATION




Figure 16. TTL to Load





Figure 17. Use of Pullup Resistors to Increase Drive Current


DIP-16



SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	3.60	3.80	4.00
A1	0.51	—	—
A2	3.10	3.30	3.50
A3	1.42	1.52	1.62
b	0.44	—	0.53
b1	0.43	0.46	0.48
B1	1.52BSC		
c	0.25	—	0.31
c1	0.24	0.25	0.26
D	18.90	19.10	19.30
E1	6.15	6.35	6.55
e	2.54BSC		
eA	7.62BSC		
eB	7.62	—	9.50
eC	0	—	0.94
L	3.00	—	—
80*80			
L/F载体尺寸 (Mil)			
110*140			
140*170			



SOP-16



SECTION B-B
WITH PLATING
BASE METAL

SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	—	—	1.75
A1	0.10	—	0.25
A2	1.35	1.40	1.45
A3	0.60	0.65	0.70
b	0.39	—	0.48
b1	0.38	0.41	0.43
c	0.21	—	0.26
c1	0.19	0.20	0.21
D	9.70	9.90	10.10
E	5.80	6.00	6.20
E1	3.70	3.90	4.10
e	1.27BSC		
L	0.50	—	0.80
L1	1.05BSC		
θ	0	—	8°
L/F载体尺寸 (mil)	75*75		
	90*110		
	90*180		