PRECISION 2.5 VOLT MICROPOWER VOLTAGE REFERENCE

ISSUE 4 - JANUARY 2003

DEVICE DESCRIPTION

The ZR4040-2.5 uses a bandgap circuit design to achieve a precision micropower voltage reference of 2.5 volts. The device is available in a small outline surface mount package, ideal for applications where space saving is important, as well as packages for through hole requirements.

The ZR4040-2.5 design provides a stable voltage without an external capacitor and is stable with capacitive loads. The ZR4040-2.5 is recommended for operation between $60\mu A$ and 15mA and so is ideally suited to low power and battery powered applications.

Excellent performance is maintained to an absolute maximum of 25mA, however the rugged design and 20 volt processing allows the reference to withstand transient effects and currents up to 200mA. Superior switching capability allows the device to reach stable operating conditions in only a few microseconds.

SCHEMETIC DIAGRAM

FEATURES

- Small outline SOT23 package
- TO92 style package
- No stabilising capacitor required
- Typical T_C 30ppm/°C
- Typical slope resistance 0.4Ω
- 2% 1% and 0.5 % tolerance
- Industrial temperature range
- Operating current 60µA to 15mA
- $\bullet~$ Transient response, stable in less than $10 \mu s$

APPLICATIONS

- Battery powered and portable equipment.
- Metering and measurement systems.
- Instrumentation.
- Test equipment.
- Data acquisition systems.
- Precision power supplies.



ZR4040-2.5

ZR4040-2.5

Forward Current

ABSOLUTE MAXIMUM RATING Reverse Current

25mA 25mA -40 to 85°C -55 to 125°C Power Dissipation (Tamb=25°C) SOT23 E-Line, 3 pin (TO92)

330mW 500mW

Operating Temperature Storage Temperature

ELECTRICAL CHARACTERISTICS TEST CONDITIONS (Unless otherwise stated) T_{amb}=25°C

SYMBOL	PARAMETER	CONDITIONS	LIMITS			TOL. %	UNITS
			MIN	TYP	MAX		
V _R	Reverse Breakdown Voltage	I _R =150μΑ	2.4875 2.475 2.45	2.5 2.5 2.5	2.5125 2.525 2.55	0.5 1 2	~
I _{MIN}	Minimum Operating Current			25	60		μA
I _R	Recommended Operating Current		0.06		15		mA
T _C †	Average Reverse Breakdown Voltage Temp. Co.	I _{R(min)} to I _{R(max)}		30	100		ppm/°C
R _S §	Slope Resistance			0.4	2		Ω
Z _R	Reverse Dynamic Impedance	I _R = 1mA f = 100Hz I _{AC} =0.1 I _R		0.3	0.8		Ω
E _N	Wideband Noise Voltage	I _R = 1mA f = 10Hz to 10kHz		45			μV (rms)



ZR4040-2.5



ZR4040-2.5

CONNECTION DIAGRAMS



ORDERING INFORMATION

Part Number	Tol%	Package	Partmark	
ZR40402F25	2	SOT23	25L	
ZR40401F25	1	SOT23	25M	
ZR404005F25	0.5	SOT23	25V	
ZR40402R25	2	E-Line *	ZR4040225	
ZR40401R25	1	E-Line *	ZR4040125	
ZR404005R25	0.5	E-Line *	ZR4040525	

* E-Line, 3 pin Reversed