

## N-Channel Enhancement Mode Power MOSFET

### Description


The GT080N10 uses advanced trench technology to provide excellent  $R_{DS(ON)}$ , low gate charge. It can be used in a wide variety of applications.

### General Features


- $V_{DS}$  100V
- $I_D$  (at  $V_{GS} = 10V$ ) 75A
- $R_{DS(ON)}$  (at  $V_{GS} = 10V$ ) < 8mΩ
- $R_{DS(ON)}$  (at  $V_{GS} = 4.5V$ ) < 12mΩ
- 100% Avalanche Tested
- RoHS Compliant

### Application

- Synchronous Rectification in SMPS or LED Driver
- UPS
- Motor Control
- BMS
- High Frequency Circuit



Schematic Diagram



TO-252



TO-220



DFN5\*6

Device	Package	Marking	Packaging
GT080N10T	TO-220	GT080N10	50pcs/Tube
GT080N10M	TO-263	GT080N10	50pcs/Tube
GT080N10D5	DFN5*6	GT080N10	2500pcs/Reel

### Absolute Maximum Ratings $T_C = 25^\circ\text{C}$ , unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage	$V_{DS}$	100	V
Continuous Drain Current	$I_D$	75	A
Pulsed Drain Current (note1)	$I_{DM}$	300	A
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Power Dissipation	$P_D$	100	W
Operating Junction and Storage Temperature Range	$T_J, T_{stg}$	-55 To 150	$^\circ\text{C}$

### Thermal Resistance




Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	$R_{thJC}$	1.5	$^\circ\text{C/W}$

**Specifications**  $T_J = 25^\circ\text{C}$ , unless otherwise noted

Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
<b>Static Parameters</b>						
Drain-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{GS} = 0V, I_D = 250\mu\text{A}$	100	--	--	V
Zero Gate Voltage Drain Current	$I_{\text{DSS}}$	$V_{DS} = 100V, V_{GS} = 0V$	--	--	1	$\mu\text{A}$
Gate-Source Leakage	$I_{\text{GSS}}$	$V_{GS} = \pm 20V$	--	--	$\pm 100$	nA
Gate-Source Threshold Voltage	$V_{GS(\text{th})}$	$V_{DS} = V_{GS}, I_D = 250\mu\text{A}$	1	2.2	3	V
Drain-Source On-Resistance	$R_{DS(\text{on})}$	$V_{GS} = 10V, I_D = 50\text{A}$	--	6	8	$\text{m}\Omega$
		$V_{GS} = 4.5V, I_D = 50\text{A}$		10	12	
Forward Transconductance	$g_{\text{FS}}$	$V_{DS}=5V, I_D=50\text{A}$	--	60	--	S
<b>Dynamic Parameters</b>						
Input Capacitance	$C_{\text{iss}}$	$V_{GS} = 0V,$ $V_{DS} = 50V,$ $f = 1.0\text{MHz}$	--	3650	--	pF
Output Capacitance	$C_{\text{oss}}$		--	315	--	
Reverse Transfer Capacitance	$C_{\text{rss}}$		--	22	--	
Total Gate Charge	$Q_g$	$V_{DD} = 50V,$ $I_D = 40A,$ $V_{GS} = 10V$	--	70	--	nC
Gate-Source Charge	$Q_{gs}$		--	14.5	--	
Gate-Drain Charge	$Q_{gd}$		--	17	--	
Turn-on Delay Time	$t_{d(\text{on})}$	$V_{DD} = 50V,$ $I_D = 40A,$ $R_G = 1.6\Omega$	--	16	--	ns
Turn-on Rise Time	$t_r$		--	11	--	
Turn-off Delay Time	$t_{d(\text{off})}$		--	35	--	
Turn-off Fall Time	$t_f$		--	9	--	
<b>Drain-Source Body Diode Characteristics</b>						
Continuous Body Diode Current	$I_S$	$T_C = 25^\circ\text{C}$	--	--	75	A
Body Diode Voltage	$V_{SD}$	$T_J = 25^\circ\text{C}, I_{SD} = 25A, V_{GS} = 0V$	--	--	1.2	V
Reverse Recovery Time	trr	$I_S = 40A, V_{GS} = 0V$ $di/dt=100A/\mu\text{s}$	--	60	--	nS


**Notes**

- Repetitive Rating: Pulse width limited by maximum junction temperature
- $I_{AS} = 20A, V_{DD} = 50V, R_G = 25\Omega$ , Starting  $T_J = 25^\circ\text{C}$
- Identical low side and high side switch with identical  $R_G$


**Gate Charge Test Circuit****EAS Test Circuit****Switch Time Test Circuit**

**Typical Characteristics**  $T_J = 25^\circ\text{C}$ , unless otherwise noted


**Figure 1. Output Characteristics**




**Figure 2. Transfer Characteristics**




**Figure 3. Gate Charge**




**Figure 4. Drain Source On Resistance**



**Figure 5. Capacitance vs Vds**




**Figure 6. Source-Drain Diode Forward**




**Typical Characteristics**  $T_J = 25^{\circ}\text{C}$ , unless otherwise noted


**Figure 7. Drain-Source On-Resistance**






**Figure 8. Safe Operation Area**



**Figure 9. Normalized Maximum Transient Thermal Impedance**




## DFN5×6-8L Package Information




SYMBOL	COMMON			
	MM		INCH	
	MIN	MAX	MIN	MAX
A	1.03	1.17	0.0406	0.0461
b	0.34	0.48	0.0134	0.0189
c	0.824	0.970	0.0324	0.0382
D	4.80	5.40	0.1890	0.2126
D1	4.11	4.31	0.1618	0.1697
D2	4.80	5.00	0.1890	0.1969
E	5.59	6.15	0.2343	0.2421
E1	5.65	5.85	0.2224	0.2303
E2	1.60	-	0.0630	-
e	1.27	BSC	0.05	BSC
L	0.05	0.25	0.0020	0.0098
L1	0.38	0.50	0.0150	0.0197
L2	0.38	0.50	0.0150	0.0197
H	3.30	3.50	0.1299	0.1378
I	-	0.18	-	0.0070

## TO-220 Package Information



Symbol	Dimensions in Millimeters		
	MIN.	NOM.	MAX.
A	4.37	4.57	4.7
A1	1.25	1.3	1.4
A2	2.2	2.4	2.6
b	0.7	0.8	0.95
b2	1.7	1.27	1.47
c	0.45	0.5	0.6
D	15.1	15.6	16.1
D1	8.8	9.1	9.4
D2	5.5		
E	9.7	10	10.3
e	2.54BSC		
e1	5.08BSC		
H1	6.25	6.5	6.85
L	12.75	13.5	13.8
L1		3.1	3.4
ØP	3.4	3.6	3.8
Q	2.6	2.8	3

## TO-263 Package Information



COMMON DIMENSIONS

SYMBOL	mm		
	MIN	NOM	MAX
A	4.52	4.57	4.62
A1	9.95	10.00	10.05
A2	6.30	6.40	6.50
b	1.30	1.50	1.70
b2	1.17	1.27	1.37
c	14.80	15.00	15.20
D	9.05	9.10	9.15
D1	1.90	2.10	2.30
D2	-	2.54	-
E	-	0.80	-
E3	-	4.57	-
e	-	1.30	-
e0	-	1.30	-
e1	1.73	3	-
H1	-	2.40	-
L	-	2.50	-
L1	-	0.50	-
φP	-	1.50	-
R	-	0.50	-
Q1	0.10	-	0.15
Q2	0	-	0.02