



1 2 3 4 5 6 7 8 9 10

|      |              |      |
|------|--------------|------|
| MAPX | MODIFICATION | DATE |
|      |              |      |

A  
B  
C  
D  
E  
F  
G





A  
B  
C  
D  
E  
F  
G



TOLERANCE: ±0.05,  
RECOMMENDED PCB LAYOUT  
(TOP VIEW)

NOTES:

- 1.MATERIAL:  
 1.1 HOUSING: HIGH TEMPERATURE THERAL PLASTIC.  
 1.2 SPRING CONTACT: COPPER ALLOY.  
 1.3 FLAT CONTACT;COPPER ALLOY  
 1.4 SHELL :COPPER ALLOY.  
 1.5 COVER:HIGH TEMPERATURE THERAL PLASTIC.
- 2.FINISH:  
 2.1 CONTACT: (SEE P/N.),[50μ"] MIN. NICKEL UNDERPLATING OVER ALL.  
 2.2 SHELL: [50μ"] MIN.SOLDERABILITY NICKEL UNDERPLATING OVER ALL.



|            |                      |       |       |       |
|------------|----------------------|-------|-------|-------|
| PIN NO.    | PIN 1                | PIN 2 | PIN 3 | PIN 4 |
| SLGNL NAME | V BUS                | D-    | D+    | GND   |
| REMARK     | USB 2.0 CONTACT PINS |       |       |       |

|            |                      |            |           |            |            |
|------------|----------------------|------------|-----------|------------|------------|
| PIN NO.    | PIN 5                | PIN 6      | PIN 7     | PIN 8      | PIN 9      |
| SLGNL NAME | STDA_SSRX-           | STDA_SSRX+ | GND_DRAIN | STDA_SSTX- | STDA_SSTX+ |
| REMARK     | USB 3.0 CONTACT PINS |            |           |            |            |

|   |            |               |       |                          |                           |    |       |    |      |     |       |     |      |      |       |      |       |                     |  |  |  |  |  |
|---|------------|---------------|-------|--------------------------|---------------------------|----|-------|----|------|-----|-------|-----|------|------|-------|------|-------|---------------------|--|--|--|--|--|
| <p>产品图<br/>PRODUCT CHART DWG</p> <p>公差一览表<br/>TOLERANCE UNLESS OTHERWISE</p> <table border="1"> <tr> <td>X.</td> <td>±0.25</td> <td>X.</td> <td>±5.°</td> </tr> <tr> <td>.X</td> <td>±0.20</td> <td>.X</td> <td>±2.°</td> </tr> <tr> <td>.XX</td> <td>±0.15</td> <td>.XX</td> <td>±1.°</td> </tr> <tr> <td>.XXX</td> <td>±0.10</td> <td>.XXX</td> <td>±0.5°</td> </tr> </table> |            | X.            | ±0.25 | X.                       | ±5.°                      | .X | ±0.20 | .X | ±2.° | .XX | ±0.15 | .XX | ±1.° | .XXX | ±0.10 | .XXX | ±0.5° | <p>深圳市精拓金电子有限公司</p> |  |  |  |  |  |
| X.  | ±0.25      | X.            | ±5.°  |                          |                           |    |       |    |      |     |       |     |      |      |       |      |       |                     |  |  |  |  |  |
| .X  | ±0.20      | .X            | ±2.°  |                          |                           |    |       |    |      |     |       |     |      |      |       |      |       |                     |  |  |  |  |  |
| .XX   | ±0.15      | .XX           | ±1.°  |                          |                           |    |       |    |      |     |       |     |      |      |       |      |       |                     |  |  |  |  |  |
| .XXX  | ±0.10      | .XXX          | ±0.5° |                          |                           |    |       |    |      |     |       |     |      |      |       |      |       |                     |  |  |  |  |  |
| 单位<br>UNITS   | MM         | 制图<br>DRAWING | 尹先华   | 制图料号<br>PRODUCT PART NO. | 916-152A2058Y20200        |    |       |    |      |     |       |     |      |      |       |      |       |                     |  |  |  |  |  |
| 比例<br>SCALE   | 1:1        | 审核<br>CHKD    | 郭治富   | 产品名称<br>PRODUCT NO.      | AF3.0 180度15.0弯脚有边铜壳LCP蓝胶 |    |       |    |      |     |       |     |      |      |       |      |       |                     |  |  |  |  |  |
| 日期<br>DATE  | 2021-04-14 | 核准<br>APPD    | 黄国荣   | 角法<br>VIEW               | 版本<br>VER                 | AO |       |    |      |     |       |     |      |      |       |      |       |                     |  |  |  |  |  |

1 2 3 4 5 6 7 8 9 10