




REV	MARK	DESCRIPTION	DRAFTED. BY	DATE
-----	------	-------------	-------------	------



CHARACTERISTICS	
OPERATING FORCE (OF) :	130gf Max.
RELEASE FORCE (RF) :	13gf Min.
OPERATING POSITION:	3.05 ± 0.20 mm.
PRE TRAVEL:	0.8mm Max.
DIFFERENTIAL TRAVEL:	0.2mm Max.
OVER TRAVEL:	0.8mm Min.

ELECTRICAL DATA	
RATING	OPERATING LIFE
3A 12VDC	100,000 CYCLES
0.1A 48VDC 125/250VAC	100,000 CYCLES
MECHANICAL LIFE	500,000 CYCLES
GAP TYPE	MICRO
OPERATING TEMP.	-40°C ~ +85°C
WATERPROOF	IP67

OUTLINE DRAWING		TOLERANCE UNLESS OTHERWISE SPECIFIED						
TITLE	ITEM	≤3	1~3	3~10	10~30	30~100	100~200	ANGLE
MODEL	H3-E1	±0.2	±0.3	±0.4	±0.6	±1.0	±1.5	±3.0°
PART NO.	H3-E1-1B00T2							SCALE
DRAFTED BY	Bing Wang	DATE	2020-7-21					UNIT mm
CHECKED BY	Hua Bai	DATE	2020-7-21					VERSION REV A1
APPROVED BY	Hong Chen	DATE	2020-7-21					

KINGHOR
SWITCHES AND CONTROL EXPERT