


## Precision Wide Bandwidth LanSwitch Quad 2:1 Mux/DeMux

### Features

- Single 3.3V/5V supply operation
- Rail-To-Rail Operation
- Very Low Distortion: 2%
- Replaces mechanical relays
- High-performance, low-cost solution for switching between different LAN signals
- Low crosstalk: -70dB @ 30 Mbps
- Low insertion loss and On-Resistance: 6-ohms typical
- Off isolation: -55dB @ 30 Mbps
- Wide bandwidth data rates >135 Mbps
- Low Quiescent Supply Current (100nA typical)
- Packaging (Pb-free & Green available):
  - 16-pin 150-mil wide plastic SOIC (W)
  - 16-pin 150-mil wide plastic QSOP (Q)
  - 16-pin 173-mil wide plastic TSSOP (L)

### Block Diagram



### Truth Table<sup>(1)</sup>

| $\bar{E}$ | S | YA   | YB   | YC   | YD   | Function |
|-----------|---|------|------|------|------|----------|
| H         | X | Hi-Z | Hi-Z | Hi-Z | Hi-Z | Disable  |
| L         | L | IA0  | IB0  | IC0  | ID0  | $S = 0$  |
| L         | H | IA1  | IB1  | IC1  | ID1  | $S = 1$  |

#### Note:

1. H = High Voltage Level

L = Low Voltage Level

Switches are shown with logic "0" input (Select and Enable)

### Description


Pericom Semiconductor's PI5L200 is a Rail-to-Rail Quad 2:1 multiplexer/demultiplexer LanSwitch with 3-state outputs. The On-Resistance typically varies from 5 ohms to 7 ohms with data inputs of 0V to 5V. Generally, this part can be used to replace mechanical relays in low voltage (3.3V/5V systems) LAN applications.

With a wide bandwidth of 135 MHz, the PI5L200 can switch Fast Ethernet and ATM25 signals. Into 100-ohm UTP cables, the switch distortion is typically less than two percent. Crosstalk @30 MHz is -70dB. The PI5L200 operates from a single 3.3V/5V supply and interface to TTL logic.

### Applications

- 10/100 Base-TX/T4
- 100VG-AnyLAN
- Token Ring 4/16 Mbps
- ATM25
- NIC Adapter and Hubs
- SONET OCI 51.8Mbps
- T1/E1

### Pin Configuration



### Pin Description

| Pin Name        | Description   |
|-----------------|---------------|
| IAn-IDn         | Data Inputs   |
| S               | Select Inputs |
| $\bar{E}$       | Enable        |
| YA-YD           | Data Outputs  |
| GND             | Ground        |
| V <sub>CC</sub> | Power         |

## Maximum Ratings

(Above which the useful life may be impaired. For user guidelines, not tested.)

|  |                                |
|--|--------------------------------|
| Storage Temperature .....                    | -65°C to +150°C                |
| Ambient Temperature with Power Applied ..... | -40°C to +85°C                 |
| Supply Voltage to Ground Potential .....     | -0.5V to +7.0V                 |
| DC Input Voltage .....                       | -0.5V to V <sub>CC</sub> +0.5V |
| DC Output Current .....                      | 120mA                          |
| Power Dissipation .....                      | 0.5W                           |

### Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

## Single 5.0V Supply

### DC Electrical Characteristics (Over the Operating Range, T<sub>A</sub>=-40°C to +85°C, V<sub>CC</sub>=5V±10%, GND=0V)

| Parameters                                 | Description              | Test Conditions <sup>(1)</sup>                                      | Min. | Typ. <sup>(2)</sup> | Max.            | Units |
|--|--------------------------|---|------|---------------------|-----------------|-------|
| V <sub>ANALOG</sub>                        | Analog Signal Range      |   | 0    | —                   | V <sub>CC</sub> | V     |
| R <sub>ON</sub>                            | ON-Resistance            | I <sub>ON</sub> = 10mA to 30mA                                      | —    | 6                   | 12              | Ω     |
| ΔR <sub>ON</sub>                           | Match Between Channels   |   | —    | 0.4                 | 2               |       |
| R <sub>FLAT(ON)</sub>                      | R <sub>ON</sub> Flatness | I <sub>ON</sub> = 1mA, V <sub>NO</sub> , V <sub>NC</sub> = 0V to 5V | —    | 3                   | 5               |       |
| I <sub>NO(OFF)</sub> , I <sub>NO(ON)</sub> | On/Off Leakage Current   | V <sub>NO</sub> , V <sub>NC</sub> = 4.5V                            | -100 | —                   | 100             | nA    |
| I <sub>CC</sub>                            | Quiescent Supply Current | V <sub>CC</sub> = 5.5V, V <sub>IN</sub> = 0V or V <sub>CC</sub>     | —    | —                   | 1               | μA    |
| I <sub>O</sub>                             | Output Current           | V <sub>NO</sub> , V <sub>NC</sub> or V <sub>COM</sub> = 0V to 5V    | 100  | —                   | —               | mA    |
| V <sub>IH</sub>                            | Input HIGH Voltage       | Guaranteed Logic HIGH Level   | 2.0  | —                   | —               | V     |
| V <sub>IL</sub>                            | Input LOW Voltage        | Guaranteed Logic LOW Level  | -0.5 | —                   | 0.8             |       |
| I <sub>IH</sub>                            | Input HIGH Current       | V <sub>CC</sub> = Max., V <sub>IN</sub> = V <sub>CC</sub>           | —    | —                   | ±1              | μA    |
| I <sub>IL</sub>                            | Input LOW Current        | V <sub>CC</sub> = Max., V <sub>IN</sub> = GND                       | —    | —                   | ±1              |       |

### Dynamic Electrical Characteristics (Over the Operating Range, T<sub>A</sub>=-40°C to +85°C, V<sub>CC</sub>=5V±10%, GND=0V)

| Parameters         | Description                     | Test Conditions <sup>(1)</sup>                          | Min. | Typ. <sup>(2)</sup> | Max. | Units |
|--------------------|---------------------------------|---|------|---------------------|------|-------|
| t <sub>ON</sub>    | Turn-on Time                    | V <sub>NO</sub> or V <sub>NC</sub> = 3.0V, see Figure 2 | —    | 10                  | 20   | ns    |
| t <sub>OFF</sub>   | Turn-off Time                   | V <sub>NO</sub> or V <sub>NC</sub> = 3.0V, see Figure 2 | —    | 5                   | 10   |       |
| X <sub>TALK</sub>  | Crosstalk                       | R <sub>L</sub> = 100 ohms, f = 30 MHz, see Figure 4     | —    | -70                 | —    | dB    |
| C <sub>(OFF)</sub> | NC or NO Capacitance            | f = 1kHz  | —    | 13                  | —    | pF    |
| O <sub>IRR</sub>   | Off Isolation                   | R <sub>L</sub> = 100 ohms, f = 30 MHz, see Figure 5     | —    | -55                 | —    | dB    |
| BW                 | Bandwidth -3 dB                 | R <sub>L</sub> = 100 ohms, see Figure 3                 | —    | 137                 | —    | MHz   |
| D                  | Distortion DR <sub>ON</sub> /RL | R <sub>L</sub> = 100 ohms                               | —    | 2                   | —    | %     |

### Notes:

- For Max. or Min. conditions, use appropriate value specified under Electrical Characteristics for applicable device type.
- Guaranteed by design.

### Single 3.3V Supply

#### DC Electrical Characteristics (Over the Operating Range, $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_{CC} = 3.3\text{V} \pm 10\%$ , GND = 0V)

| Parameters                   | Description            | Test Conditions <sup>(1)</sup>   | Min. | Typ. <sup>(2)</sup> | Max.     | Units         |
|------------------------------|------------------------|--|------|---------------------|----------|---------------|
| $V_{ANALOG}$                 | Analog Signal Range    |  | 0    | —                   | $V_{CC}$ | V             |
| $R_{ON}$                     | ON-Resistance          | $I_{ON} = 10\text{mA}$ to $30\text{mA}$                                | —    | 15                  | 22       | $\Omega$      |
| $\Delta R_{ON}$              | Match Between Channels |  | —    | 1                   | 3        |               |
| $R_{FLAT(ON)}$               | $R_{ON}$ Flatness      | $I_{ON} = 1\text{mA}$ , $V_{NO}$ , $V_{NC} = 0\text{V}$ to $5\text{V}$ | —    | 7                   | 12       |               |
| $I_{NO(OFF)}$ , $I_{NO(ON)}$ | On/Off Leakage Current | $V_{NO}$ , $V_{NC} = 3.0\text{V}$                                      | -100 | —                   | 100      | nA            |
| $I_{COM(ON)}$                | On Leakage Current     | $V_{NO}$ , $V_{NC} = 3.0\text{V}$                                      | -100 | —                   | 100      | $\mu\text{A}$ |
| $I_O$                        | Output Current         | $V_{NO}$ , $V_{NC}$ or $V_{COM} = 0\text{V}$                           | 80   | —                   | —        | mA            |
| $V_{IH}$                     | Input HIGH Voltage     | Guaranteed Logic HIGH Level  | 2.0  | —                   | —        | V             |
| $V_{IL}$                     | Input LOW Voltage      | Guaranteed Logic LOW Level   | -0.5 | —                   | 0.8      |               |
| $I_{IH}$                     | Input HIGH Current     | $V_{CC} = \text{Max.}$ , $V_{IN} = V_{CC}$                             | —    | —                   | $\pm 1$  | $\mu\text{A}$ |
| $I_{IL}$                     | Input LOW Current      | $V_{CC} = \text{Max.}$ , $V_{IN} = \text{GND}$                         | —    | —                   | $\pm 1$  |               |

#### Dynamic Electrical Characteristics (Over the Operating Range, $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_{CC} = 3.3\text{V} \pm 10\%$ , GND = 0V)

| Parameters     | Description          | Test Conditions <sup>(1)</sup>                    | Min. | Typ. <sup>(2)</sup> | Max. | Units |
|----------------|----------------------|---|------|---------------------|------|-------|
| $t_{ON}$       | Turn-on Time         | $V_{NO}$ or $V_{NC} = 1.5\text{V}$ , see Figure 2 | —    | 28                  | 40   | ns    |
| $t_{OFF}$      | Turn-off Time        | $V_{NO}$ or $V_{NC} = 1.5\text{V}$ , see Figure 2 | —    | 4                   | 20   |       |
| $X_{TALK}$     | Crosstalk            | $R_L = 50$ ohms, $f = 1\text{MHz}$ , see Figure 4 | —    | -75                 | —    | dB    |
| $C_{(OFF)}$    | NC or NO Capacitance | $f = 1\text{kHz}$                                 | —    | 15                  | —    | pF    |
| $C_{COM(OFF)}$ | COM Off Capacitance  | $f = 1\text{kHz}$                                 | —    | 30                  | —    |       |
| $O_{IRR}$      | Off Isolation        | $R_L = 50$ ohms, $f = 1\text{MHz}$ , see Figure 5 | —    | -75                 | —    | dB    |
| BW             | Bandwidth -3 dB      | $R_L = 50$ ohms, see Figure 3                     | —    | 110                 | —    | MHz   |
| D              | Distortion           | $R_L = 100$ ohms                                  | —    | 4                   | —    | %     |

#### DC Electrical Characteristics (Over the Operating Range, $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_{CC} = 3.3\text{V} \pm 10\%$ , GND = 0V)

| Parameters | Description                             | Test Conditions <sup>(1)</sup>   | Min. | Typ. <sup>(2)</sup> | Max. | Units         |
|------------|---|--|------|---------------------|------|---------------|
| $I_{CC}$   | Quiescent Positive Power Supply Current | $V_{CC} = 3.6\text{V}$ , $V_{IN} = 0\text{V}$ or $V_{CC}$ All Channels On or OFF | —    | —                   | 1    | $\mu\text{A}$ |

#### Notes:

- For Max. or Min. conditions, use appropriate value specified under Electrical Characteristics for applicable device type.
- Guaranteed by design.




Figure 1a. Full Duplex Transceiver




Figure 1b. Loop Back




Figure 1c. Line Termination







Figure 1d. Line Clamp

## Test Circuits



\*Note: This is a 1.5V for 3.3V supply.

**Figure 2. Switching Time**



**Figure 3. Bandwidth**

## Typical Operating Characteristics




Figure 4. Crosstalk




Figure 5. Off Isolation




Figure 6. On-Resistance vs. Input Voltage




Figure 7. Insertion Loss vs. Frequency




Figure 8. Off Isolation vs. Frequency







Figure 9. Crosstalk vs. Frequency

**Packaging Mechanical: 16-Pin SOIC (W)**

**Packaging Mechanical: 16-Pin QSOP (Q)**


### Packaging Mechanical: 16-Pin TSSOP (L)



### Ordering Information

| Ordering Code | Package Code | Package Type                  |
|---------------|--------------|-------------------------------|
| PI5L200L      | L            | 16-pin TSSOP                  |
| PI5L200LE     | L            | Pb-free & Green, 16-pin TSSOP |
| PI5L200Q      | Q            | 16-pin QSOP                   |
| PI5L200QE     | Q            | Pb-free & Green, 16-pin QSOP  |
| PI5L200W      | W            | 16-pin SOIC                   |
| PI5L200WE     | W            | Pb-free & Green, 16-pin SOIC  |

#### Notes:

- Thermal characteristics can be found on the company web site at [www.pericom.com/packaging/](http://www.pericom.com/packaging/)