






SECTION A-A
SCALE 1:1



RECOMMENDED P.C.B. PATTERN LAYOUT



RECOMMENDED FPC/FFC DIMENSION

Note:

1. Material:

- 1.1 Housing: thermoplastic high temp.UL94V-0; Color: natural.
- 1.2 Latch: thermoplastic high temp.UL94V-0; Color: black.
- 1.3 Terminal: copper alloy.
- 1.4 Fitting Nail: copper alloy.

2. Finish:

2.1 Terminal:

- 50u"Min Nickel Under plating overall;
- 1:1u" Gold on Contact and Solder
- N:10u" Gold on Contact and Gold flash on Solder;

2.2 Fitting Nail:

- 50u"Min Nickel Under plating overall;
- 90u"Min matte tin plating overall.

3. Product must comply HF RoHS specification.

4. Product No:

- AFC64-S ** F * * - **
- CKTS CONTACTS TYPE F:Lower
- PLATING I:1u" Gold on Contact and solder
N:10u" Gold on Contact and Gold flash on solder
- PACKING A:Tape&Reel
C:Tube
- REMARKS HF:Halogen free

CKTS	DIM A	DIM B	DIM C	DIM D
4	1.50	6.17	2.57	6.80
5	2.00	6.67	3.07	7.30
6	2.50	7.17	3.57	7.80
7	3.00	7.67	4.07	8.30
8	3.50	8.17	4.57	8.80
9	4.00	8.67	5.07	9.30
10	4.50	9.17	5.57	9.80
11	5.00	9.67	6.07	10.30
12	5.50	10.17	6.57	10.80
13	6.00	10.67	7.07	11.30
14	6.50	11.17	7.57	11.80
15	7.00	11.67	8.07	12.30
16	7.50	12.17	8.57	12.80
17	8.00	12.67	9.07	13.30
18	8.50	13.17	9.57	13.80
19	9.00	13.67	10.07	14.30
20	9.50	14.17	10.57	14.80
21	10.00	14.67	11.07	15.30
22	10.50	15.17	11.57	15.80
23	11.00	15.67	12.07	16.30
24	11.50	16.17	12.57	16.80
25	12.00	16.67	13.07	17.30
26	12.50	17.17	13.57	17.80
27	13.00	17.67	14.07	18.30
28	13.50	18.17	14.57	18.80
29	14.00	18.67	15.07	19.30
30	14.50	19.17	15.57	19.80
31	15.00	19.67	16.07	20.30
32	15.50	20.17	16.57	20.80
33	16.00	20.67	17.07	21.30
34	16.50	21.17	17.57	21.80
35	17.00	21.67	18.07	22.30
36	17.50	22.17	18.57	22.80
37	18.00	22.67	19.07	23.30
38	18.50	23.17	19.57	23.80
39	19.00	23.67	20.07	24.30
40	19.50	24.17	20.57	24.80
41	20.00	24.67	21.07	25.30
42	20.50	25.17	21.57	25.80
43	21.00	25.67	22.07	26.30
44	21.50	26.17	22.57	26.80
45	22.00	26.67	23.07	27.30
46	22.50	27.17	23.57	27.80
47	23.00	27.67	24.07	28.30
48	23.50	28.17	24.57	28.80
49	24.00	28.67	25.07	29.30
50	24.50	29.17	25.57	29.80
51	25.00	29.67	26.07	30.30
52	25.50	30.17	26.57	30.80
53	26.00	30.67	27.07	31.30
54	26.50	31.17	27.57	31.80
55	27.00	31.67	28.07	32.30
56	27.50	32.17	28.57	32.80
57	28.00	32.67	29.07	33.30
58	28.50	33.17	29.57	33.80
59	29.00	33.67	30.07	34.30
60	29.50	34.17	30.57	34.80

CUSTOMER DRAWING

Tolerance Unspecified (未注公差)	Size(图幅): A4
0.0 ±0.15 0° ±5°	Unit(单位): MM
0.00 ±0.10 0° ±3°	Scale(比例): 1:1
0.000 ±0.05 0° ±1°	Page(页数): 1 OF 1
Project View (投影视角)	Rev(版本): A

深圳市钜硕电子有限公司
SHENZHEN JUSHUO ELECTRONIC CO.,LTD

Product Name(产品名称):
0.5Pitch H=2.0 FPC/FFC Easy-on R/A Type5 SMT CONN






Product No(产品料号):
AFC64-S**F**

Designer(设计):
Allan

Checked(审核):



Approved(核准):

Rev 版本	初版发行 变更内容	2017/04/10 日期	Allan 制/修订人
-----------	--------------	------------------	----------------



NOTES:

1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE.±0.20mm
2. CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
3. ALL DIMENSIONS MEET EIA-481-D REQUIREMENTS.
4. MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
5. THICKNESS: 0.30 ± 0.05 mm.
6. PACKING LENGTH PER 13" REEL: 24.60METERS.
7. COMPONENT LOAD PER 13" REEL: 2000PCS
8. PEELING OFF FORCE OF TOP TAPE 0.1N~0.7N(10.2gf~71.4gf).



CKTS	B0±0.10	W	W1	F	S0±0.10
4	7.10	16±0.3/-0	16.4	7.5±0.10	单边孔
5	7.60				
6	8.10				
7	8.60				
8	9.10				
9	9.60	24±0.3/-0	24.4	11.5±0.10	单边孔
10	10.10				
11	10.60				
12	11.10				
13	11.60				
14	12.10	32±0.30	32.4	14.2±0.10	28.4
15	12.60				
16	13.10				
17	13.60				
18	14.10				
19	14.60	44±0.30	44.4	20.2±0.15	40.4
20	15.10				
21	15.60				
22	16.10				
23	16.60				
24	17.10	56±0.30	56.4	26.2±0.15	52.4
25	17.60				
26	18.10				
27	18.60				
28	19.10				
29	19.60	68±0.30	68.4	32.2±0.15	64.4
30	20.10				
31	20.60				
32	21.10				
33	21.60				
34	22.10	80±0.30	80.4	38.2±0.15	76.4
35	22.60				
36	23.10				
37	23.60				
38	24.10				
39	24.60	92±0.30	92.4	44.2±0.15	88.4
40	25.10				
41	25.60				
42	26.10				
43	26.60				
44	27.10	104±0.30	104.4	50.2±0.15	96.4
45	27.60				
46	28.10				
47	28.60				
48	29.10				
49	29.60	116±0.30	116.4	56.2±0.15	112.4
50	30.10				
51	30.60				
52	31.10				
53	31.60				
54	32.10	128±0.30	128.4	62.2±0.15	124.4
55	32.60				
56	33.10				
57	33.60				
58	34.10				
59	34.60	140±0.30	140.4	68.2±0.15	136.4
60	35.10				

CLASSIFICATION DIMENSION(尺寸类别):			
FAT(首次检验): ☉To ☉			
■ MARK IS MAJOR DIM(重点尺寸标示)			
⊙ MARK IS CRITICAL DIM(Cpk&Cp标示)			
Tolerance Unspecified (未注公差)			Size(图幅): A4
0.0 ±0.10 0° ±3°			Unit(单位): MM
0.00 ±0.05 0° 0 ±2°			Scale(比例): 1:1
0.000 ±0.02 0° 00 ±1°			Page(页数): 1 OF 1
Project View (投影视角)			Rev(版本): 1.0
			

深圳市钜硕电子有限公司
SHENZHEN JUSHUO ELECTRONIC CO.,LTD

Product Name (产品名称):			
0.5Pitch H=2.0 FPC 掀盖卧式5代SMT型.载带			
Product No (产品料号):			
AFC64-S**F**-**			
Drawing No (图面编号):		Date (日期):	
DNE00126-1		2017/04/10	
Designer (设计):		Checked (审核):	
Allan		Approved (核准):	

1.0	初版发行	2017/04/10	Allan
Rev	Change Description	Date	Revisor
版本	变更内容	日期	制/修订人