





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
HB	00	E	ECR-09-027847	03FEB2010	JS GK
		F	CHANGE TE LOGO, ECO-12-005755	24AUG2012	HL.C BH.Y



HOLE CHART
 A- Ø .043±.003 [1.09±0.08]
 B- Ø .081 [2.06]




ELECTRICAL CHARACTERISTICS

NOMINAL VOLTAGE: 24 VDC
 OPERATE VOLTAGE: 18 VDC
 DROPOUT VOLTAGE: 2.4 VDC MIN.
 COIL RESISTANCE: 547 OHMS, ±5%
 CONTACT ARRANGEMENT: 1 FORM A (SPST)
 CONTACT MATERIAL: SILVER CADMIUM OXIDE
 CONTACT RATING: 25A @ 240 VAC, NO CONTACT

BREAKDOWN: 1554V RMS 60Hz ACROSS OPEN CONTACTS
 2500V RMS 60Hz BETWEEN CONTACTS AND COIL
 6KV SURGE USING 1.2 MICROSEC. / 50 MICROSEC. IMPULSE WAVE OR
 .5 MICROSEC. -100KHz RING WAVE BETWEEN CONTACTS AND COIL.

STORAGE TEMPERATURE RANGE: -55°C TO +130°C
 OPERATE TEMPERATURE RANGE: -55°C TO +105°C**



TE PART NO.
 3-1423091-5

PC BOARD LAYOUT (BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SLIKE 03FEB2010	STE TE Connectivity	
DIMENSIONS: INCH [mm]		CHK G. KOPPENHEFFER 03FEB2010		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. KOPPENHEFFER 03FEB2010	NAME RELAY, PC, SEALED	
0 PLC ±-		PRODUCT SPEC -	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
1 PLC ±-		APPLICATION SPEC -	A300779 C-T9AS1H22-24	
2 PLC ±.01[0.25]		WEIGHT -	SCALE 2:1 SHEET 1 OF 1 REV F	
3 PLC ±.005[0.13]		Customer Drawing		
4 PLC ±-				
ANGLES ±-				
MATERIAL -				
FINISH -				