

HXC SERIES

105°C High Ripple, Snap-in Terminal Type

◆ FEATURES

- Load Life : 105°C 2000 hours.
- Higher ripple current endurance than MXC series.
- RoHS compliance.



◆ SPECIFICATIONS

Items	Characteristics								
Category Temperature Range	-25~+105℃								
Rated Voltage Range	200, 400, 450V.DC								
Capacitance Tolerance	± 20%(20℃,120Hz)								
Leakage Current(MAX)	I= 3√CV (After 5 minutes application of rated voltage) I= (μA) V= (V) C= (μF) Leakage Current Rated Voltage Rated Capacitance								
Dissipation Factor(MAX) (tanδ)	<table><tr><td>(V) Rated Voltage</td><td>200~400</td><td>450</td></tr><tr><td>tan δ</td><td>0.15</td><td>0.20</td></tr></table> (20℃,120Hz)			(V) Rated Voltage	200~400	450	tan δ	0.15	0.20
(V) Rated Voltage	200~400	450							
tan δ	0.15	0.20							
Impedance Ratio(MAX)	<table><tr><td>(V) Rated Voltage</td><td>200</td><td>400~450</td></tr><tr><td>Z(-25℃)/Z(20℃)</td><td>3</td><td>8</td></tr></table> (120Hz)			(V) Rated Voltage	200	400~450	Z(-25℃)/Z(20℃)	3	8
(V) Rated Voltage	200	400~450							
Z(-25℃)/Z(20℃)	3	8							
Endurance	After applying rated voltage with rated ripple current for 2000hrs at 105℃, the capacitors shall meet the following requirements. <table><tr><td>Capacitance Change</td><td>Within ±20% of the initial value.</td></tr><tr><td>Dissipation Factor</td><td>Not more than 200% of the specified value.</td></tr><tr><td>Leakage Current</td><td>Not more than the specified value.</td></tr></table>			Capacitance Change	Within ±20% of the initial value.	Dissipation Factor	Not more than 200% of the specified value.	Leakage Current	Not more than the specified value.
Capacitance Change	Within ±20% of the initial value.								
Dissipation Factor	Not more than 200% of the specified value.								
Leakage Current	Not more than the specified value.								

◆ MULTIPLIER FOR RIPPLE CURRENT

Frequency coefficient

(Hz) Frequency		60(50)	120	500	1k	10k≤
Coefficient	200WV	0.80	1.00	1.20	1.30	1.50
	400~450WV	0.80	1.00	1.20	1.25	1.40

◆ PART NUMBER


	HXC				SN	DxL
Rated Voltage	Series	Rated Capacitance	Capacitance Tolerance	Option	Terminal Code	Case Size

◆ Option

	Code
PET Sleeve without plate	EFC
PVC Sleeve without plate	OOE
PVC Sleeve with plate	Blank

◆ DIMENSIONS

(mm)



◆ STANDARD SIZE

Cap (μ F)	ϕ D	200							
		ϕ 22		ϕ 25		ϕ 30		ϕ 35	
270		22×25	1.64						
330		22×30	1.89						
390		22×35	2.14	25×25	1.99				
470		22×40	2.41	25×30	2.32	30×25	2.27		
560		22×45	2.71	25×35	2.63	30×25	2.43		
680		22×50	3.06	25×35	2.81	30×30	2.82		
820				25×45	3.32	30×30	2.94	35×25	2.56
1000				25×50	3.72	30×35	3.36	35×30	3.07
1200						30×40	3.78	35×35	3.57
1500						30×50	4.48	35×40	4.01
1800								35×45	4.44
2200								35×50	4.90

Cap (μ F)	ϕ D	400							
		ϕ 22		ϕ 25		ϕ 30		ϕ 35	
82		22×30	0.81						
100		22×35	0.99	25×25	0.99				
120		22×40	1.19	25×30	1.19				
150		22×45	1.43	25×35	1.43	30×25	1.41		
180		22×50	1.60	25×40	1.61	30×30	1.61		
220				25×45	1.83	30×35	1.84		
270				25×50	2.06	30×40	2.10	35×30	2.00
330						30×45	2.36	35×35	2.29
390						30×50	2.62	35×40	2.56
470								35×45	2.86
560								35×50	3.15

Cap (μ F)	ϕ D	450							
		ϕ 22		ϕ 25		ϕ 30		ϕ 35	
68		22×30	0.67						
82		22×35	0.81	25×25	0.81				
100		22×40	0.99	25×30	0.99				
120		22×45	1.19	25×35	1.19	30×25	1.19		
150				25×40	1.49	30×30	1.49	35×25	1.49
180				25×45	1.68	30×35	1.70	35×25	1.61
220				25×50	1.89	30×40	1.92	35×30	1.85
270						30×45	2.18	35×35	2.12
330						30×50	2.45	35×40	2.41
390								35×45	2.67
470								35×50	2.97

↑ Ripple Current (A r.m.s./120Hz, 105°C)

 Case Size ϕ D×L(mm)