#### PAN1326C *Bluetooth*® Classic and Bluetooth 4.2 Low Energy RF Module Host Controlled Interface (HCI) Bluetooth RF Module Brings TI's CC2564C To An Easy-To-Use Module Format!



Panasonic's New PAN1326C Series Host Controlled Interface (HCI) Bluetooth RF Module brings Texas Instrument's seventh generation Bluetooth core integrated circuit, the CC2564C, to an easy-to -use Module format. The New PAN1326C is Bluetooth 4.2 compliant and offers best-in-class RF performance. Panasonic's tiny footprint technology has produced a Module of only 85.5mm<sup>2</sup>. The PAN1326C is designed to accommodate PCBs pad pitch of 1.3mm and as little as two layers for easy implementation and manufacturing. This Module has been designed to be 100% pin compatible with previous generations of Texas Instruments based Bluetooth HCI modules.

## **General Features and Benefits:**

- Bluetooth 4.2 Compliant Up To The HCI Layer
- Best-In-Class Bluetooth RF Performance (Tx, Rx Sensitivity, Blocking)
- Fully Qualified Bluetooth
- FCC And IC Listed, CE Compliant
- Dimensions: 9.0 Mm x 9.5 Mm x 1.8 Mm (Width x Length x Height)
- Operating Temperature Range: -45°C To +85°C
- Supply Voltage Range: 1.7 4.8 V
- Based Upon TI's CC2564C
- RoHS and REACH Compliant

## **Bluetooth Features:**

- Basic Rate Scatternet: Up To Three Piconets Simultaneously, One As Master And Two As Slaves
- Provide Assisted Mode For HFP 1.6 Wideband Speech (WBS) Profile Or A2DP Profile
- BLE Concurrent Peripheral And Central, Support Up To 10 Devices
- Integration Of Bluetooth 4.2 Low Energy Secure Connections

# **Applications:**

- Heart Rate Monitors
- Blood Glucose Meters
- Industrial Sensors
- Entertainment Devices
- Mobile Accessories
- Toys

# **Part Number Information:**

| Part Number   | Description  | Series Number |
|---------------|--|---------------|
| ENW-89823A4KF | Bluetooth HCl Module,<br>CC2564C, Integrated Antenna | PAN1325C      |

### **Block Diagram:**



## **Technical**

### **Characteristics:**

| Parameter             | Value          | Condition/Note           |
|-----------------------|----------------|--------------------------|
| Receiver Sensitivity  | -93 dbm        |                          |
| Output Power          | 10 dbm         | Maximum Setting          |
| Power Supply          | 1.7V — 4.8V    | Single Operation Voltage |
| Transmit Mode         | 40mA           | ACL, DH1                 |
| Receive Mode          | 20 mA          | ACL, DH1                 |
| Operating Temperature | -45°C to +85°C | Industrial Range         |