

Features


- P-Channel, -5V Logic Level Control
- Fast Switching
- Enhancement mode
- 100% Avalanche Tested
- Pb-free lead plating; RoHS compliant




Part ID	Package Type	Marking	Tape and reel information
VS6522AD	TO-252	6522AD	2500PCS/Reel

V_{DS}	-60	V
$R_{DS(on),TYP@ V_{GS}=-10V}$	69	mΩ
$R_{DS(on),TYP@ V_{GS}=-4.5V}$	119	mΩ
I_D	-18	A

TO-252



Drain Pin 2



Maximum ratings, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Symbol	Parameter	Rating	Unit
$V_{(BR)DSS}$	Drain-Source breakdown voltage	-60	V
I_S	Diode continuous forward current	$T_C = 25^\circ\text{C}$ -18	A
I_D	Continuous drain current @ $V_{GS} = -10V$	$T_C = 25^\circ\text{C}$ -18	A
		$T_C = 100^\circ\text{C}$ -12	A
I_{DM}	Pulse drain current tested ①	$T_C = 25^\circ\text{C}$ -72	A
EAS	Avalanche energy, single pulsed ②	33	mJ
P_D	Maximum power dissipation	$T_C = 25^\circ\text{C}$ 43	W
V_{GS}	Gate-Source voltage	± 20	V
$T_{STG} T_J$	Storage and operating temperature range	-55 to 175	$^\circ\text{C}$
Thermal Characteristics			
$R_{\theta JC}$	Thermal Resistance-Junction to Case	3.5	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance-Junction to Ambient	100	$^\circ\text{C/W}$

Symbol	Parameter	Condition	Min.	Typ.	Max.	Unit
Static Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
V _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =-250μA	-60	--	--	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =-60V,V _{GS} =0V	--	--	-1	μA
	Zero Gate Voltage Drain Current(T _J =125°C)	V _{DS} =-60V,V _{GS} =0V	--	--	-100	μA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±20V,V _{DS} =0V	--	--	±100	nA
V _{GS(TH)}	Gate Threshold Voltage	V _{DS} =V _{GS} ,I _D =-250μA	-1.3	-2	-2.4	V
R _{DS(ON)}	Drain-Source On-State Resistance ③	V _{GS} =-10V, I _D =-15A	--	69	81	mΩ
R _{DS(ON)}	Drain-Source On-State Resistance ③	V _{GS} =-4.5V, I _D =-10A	--	119	134	mΩ
Dynamic Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
C _{iss}	Input Capacitance	V _{DS} =-30V,V _{GS} =0V, f=1MHz	800	890	1000	pF
C _{oss}	Output Capacitance		30	55	80	pF
C _{rss}	Reverse Transfer Capacitance		20	40	60	pF
R _g	Gate Resistance	f=1MHz		12		Ω
Q _g	Total Gate Charge	V _{DS} =-30V,I _D =-15A, V _{GS} =-10V	--	18	--	nC
Q _{gs}	Gate-Source Charge		--	4.5	--	nC
Q _{gd}	Gate-Drain Charge		--	5.2	--	nC
Switching Characteristics						
t _{d(on)}	Turn-on Delay Time	V _{DD} =-30V, I _D =-15A, R _G =3.0Ω, V _{GS} =-10V	--	10	--	nS
t _r	Turn-on Rise Time		--	5.8	--	nS
t _{d(off)}	Turn-Off Delay Time		--	33.5	--	nS
t _f	Turn-Off Fall Time		--	9.5	--	nS
Source- Drain Diode Characteristics@ T _J = 25°C (unless otherwise stated)						
V _{SD}	Forward on voltage	I _{SD} =-15A,V _{GS} =0V	--	-1.0	-1.2	V
t _{rr}	Reverse Recovery Time	T _J =25 °C,I _{sd} =-15A, V _{GS} =0V	--	29	--	nS
Q _{rr}	Reverse Recovery Charge	di/dt=-100A/μs		34		nC







NOTE:

① Repetitive rating; pulse width limited by max. junction temperature.

② Limited by T_{Jmax}, starting T_J = 25°C, L = 0.5mH, R_G = 25Ω, I_{AS} = -9A, V_{GS} = -10V. Part not recommended for use above this value

③ Pulse width ≤ 300μs; duty cycles ≤ 2%.

Typical Characteristics



Typical Characteristics




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage




Fig9. Normalized Maximum Transient Thermal Impedance




Fig10. Unclamped Inductive Test Circuit and Waveforms





Fig11. Switching Time Test Circuit and waveforms

TO-252 Package Outline Data



Symbol	Dimensions (unit: mm)		
	Min	Typ	Max
A	2.20	2.30	2.38
A₁	0.46	0.50	0.63
b	0.64	0.76	0.89
b₁	0.77	0.85	1.14
b₂	5.00	5.33	5.46
c	0.458	0.508	0.558
D₁	5.98	6.10	6.223
D₂	5.21	--	--
E	6.40	6.60	6.731
E₁	4.40	--	--
e	2.286 BSC		
e₁	--	4.57	--
H_D	9.40	10.00	10.40
L	2.743 REF		
L₁	1.40	1.52	1.77
L₂	0.50	0.80	1.01
w	--	0.20	--
y	--	--	0.20

Notes:

1. Refer to JEDEC TO-252 variation AA
2. Dimension "E" does NOT include mold flash, protrusions or gate burrs. Mold flash, protrusions or gate burrs shall not exceed 0.1524mm per side.
3. Dimension "D1" does NOT include interlead flash or protrusion. Interlead flash or protrusion shall not exceed 0.1524mm per end.