


REL-MR-...21

Miniature Relays With PDT for Loads up to 6 A



INTERFACE

Data Sheet

© PHOENIX CONTACT - 10/2005

Description

With the REL-MR-...21 plug-in miniature relay, the high end of the latest relay developments are made available to the innovative PLC range. Despite its compact dimensions, the device is rugged and equipped with features which are not normally found in plug-in relays:

- 5 mm wide
- High level of operational safety
- Cadmium-free, environmentally friendly power contacts up to 250 V AC/6 A
- Available with gold plating for low power switching levels (mA) as an option
- 4 kV_{rms} electrical isolation between input and output
- Safe isolation according to EN 50178
- High degree of protection, up to IP67 depending on the type

The miniature relays are not just designed to be used as components for the PLC range, but can also be used as PCB relays in industrial products of any kind, such as:

- Interface technology, timer relays
- Measuring and control technology
- PLC and bus I/O modules



Make sure you always use the latest documentation.

It can be downloaded at www.download.phoenixcontact.com.

A conversion table is available on the Internet at

http://www.download.phoenixcontact.com/general/7000 en 00.pdf.



This data sheet is valid for the following products:

Ordering Data

Plug-In Miniature Relays With Power Contact

Description	Туре	Order No.	Pcs./Pkt.
Plug-in miniature relays with power contact, 4.5 V DC input voltage	REL-MR- 4,5DC/21	29 61 36 7	10
Plug-in miniature relays with power contact, 12 V DC input voltage	REL-MR- 12DC/21	29 61 15 0	10
Plug-in miniature relays with power contact, 18 V DC input voltage	REL-MR- 18DC/21	29 61 38 3	10
Plug-in miniature relays with power contact, 24 V DC input voltage	REL-MR- 24DC/21	29 61 10 5	10
Plug-in miniature relays with power contact, 60 V DC input voltage	REL-MR- 60DC/21	29 61 11 8	10

Plug-In Miniature Relays With Multi-Layer Contact

Description	Туре	Order No.	Pcs./Pkt.
Plug-in miniature relays with multi-layer contact, 4.5 V DC input voltage	REL-MR- 4,5DC/21AU	29 61 37 0	10
Plug-in miniature relays with multi-layer contact, 12 V DC input voltage	REL-MR- 12DC/21AU	29 61 16 3	10
Plug-in miniature relays with multi-layer contact, 18 V DC input voltage	REL-MR- 18DC/21AU	29 61 49 3	10
Plug-in miniature relays with multi-layer contact, 24 V DC input voltage	REL-MR- 24DC/21AU	29 61 12 1	10
Plug-in miniature relays with multi-layer contact, 60 V DC input voltage	REL-MR- 60DC/21AU	29 61 13 4	10

Technical Data

Coil Side	4,5VDC	12VDC	18VDC	24VDC	60VDC
Nominal input voltage U _N	4.5 V DC	12 V DC	18 V DC	24 V DC	60 V DC
Permissible range (with reference to U _N)	See	See "Permissible Operating Voltage Range" on page 4			
Typical input current at U _N	38 mA	14 mA	9 mA	7 mA	3 mA
Typical response time at U _N	5 ms	5 ms	5 ms	5 ms	5 ms
Typical release time at U _N	2.5 ms	2.5 ms	2.5 ms	2.5 ms	2.5 ms
Coil resistance at 20°C	119 Ω ±10%	848 Ω ±10%	1906 Ω ±10%	3390 Ω ±10%	20500 Ω ±15%

Contact Side		REL-MR21	REL-MR	R21AU
Contact type		Single contact, 1 PDT	Single contact, 1 PDT	
Contact material		AgSnO	Ag alloy, hard gold-plated ¹	
Maximum switching voltage		250 V AC/DC	30 V AC/36 V DC	(250 V AC/DC)
Minimum switching voltage		12 V AC/DC	100 mV	(12 V AC/DC)
Limiting continuous current		6 A	50 mA	(6 A)
Maximum inrush current		On request	50 mA	
Minimum switching current		10 mA	1 mA	(10 mA)
Maximum shutdown power (ohmic load), (see "Shutdown Power" on page 4)	24 V DC	140 W	1.2 W	(140 W)
	48 V DC	20 W	-	(20 W)
	60 V DC	18 W	_	(18 W)
	110 V DC	23 W	_	(23 W)
	220 V DC	40 W	_	(40 W)
	250 V AC	1500 VA	_	(1500 VA)
Minimum switching power		120 mW	100 μW	(120 mW)

¹ If the specified maximum values are exceeded, the gold coating will be damaged. In subsequent operation, the maximum values given in brackets will apply. This can then result in reduced service life compared to simple power contacts.

101810_01_en PHOENIX CONTACT 2

General Data	
Test voltage: Winding/contact	4 kV, 50 Hz, 1 minute
Ambient operating temperature range	-40°C to +85°C
Nominal operating mode	100% operating factor
Mechanical service life	2 x 10 ⁷ cycles
Electrical service life	See "Service Life Reduction Factor" on page 4
Standards/specifications	IEC 60255/DIN VDE 0435 (in relevant parts) DIN EN 50178/VDE 0160 (in relevant parts) EN 60730/DIN VDE 0631 IEC 60664/IEC 60064 A/DIN VDE 0110 Pollution degree 3, surge voltage category III, DIN EN 50178/VDE 0160, increased isolation I/O
Approvals	(i) And (ii) 1
Mounting position/mounting	Any/can be mounted without spacing

¹ Instead of **¾** and **⑥**: ₀**¾** us is also possible.

Dimensions




Figure 1 Dimensions (in mm)

Pin Assignment





Figure 2 Pin assignment (view of the connections)

101810_01_en PHOENIX CONTACT 3

Diagrams


Permissible Operating Voltage Range




- **A** Maximum permissible continuous voltage U_{max} with limiting continuous current on the contact side
- $\begin{tabular}{ll} \bf B & {\it Minimum permissible relay operate voltage U_{op}} \\ & {\it following pre-excitation} \\ \end{tabular}$

Service Life Reduction Factor

(with varying $\cos \varphi$)




Electrical Service Life



- A 250 V AC, ohmic load
- **B** 250 V AC, $\cos \varphi = 0.4$
- C 24 V DC, ohmic load

Shutdown Power



- A AC, ohmic load
- B DC, ohmic load

© PHOENIX CONTACT 10/2005

101810_01_en PHOENIX CONTACT 4