



Features

- 80V/90A
- RDS(ON)=6.5mΩ (typ.) @ VGS=10V
- Lead free and Green Device Available
- Low Rds-on to Minimize Conductive Loss
- High avalanche Current
- 100% Avalanche Tested



Application

- Power Supply
- DC-DC Converters
- UPS
- Battery Management



Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Maximum	Unit	
V_{DSS}	Drain-to-Source Voltage	80	V	
V_{GSS}	Gate-to-Source	± 25	V	
I_D^3	Continuous Drain Current	$T_c=100^\circ\text{C}$	90	A
		$T_c=100^\circ\text{C}$	63	
I_{DM}^4	Pulsed Drain Current	360	A	
EAS ⁵	Avalanche energy	313	mJ	
PD	Maximum Power Dissipation	$T_c=25^\circ\text{C}$	180	W
T_J, T_{STG}	Junction & Storage Temperature Range		-55~175 °C	

Thermal Characteristics

Symbol	Parameter	Typical	Unit
$R\theta_{jc}$	Thermal Resistance-Junction to Case	0.63	°C/W
$R\theta_{ja}$	Thermal Resistance-Junction to Ambient	62.5	

Electrical Characteristics (TA=25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min.	Typ	Max.	Unit
Static Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250uA	80	—	—	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =80V, V _{GS} =0V	—	—	1	uA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250uA	2	3	4	V
I _{GSS}	Gate Leakage Current	V _{GS} =±25V, V _{DS} =0V	—	—	±100	nA
R _{DS(on)} ¹	Drain-Source On-Resistance	V _{GS} =10V, I _D =40A	—	6.5	8.5	mΩ
			—	—	—	
Diode Characteristics						
V _{SD} ¹	Diode Forward Voltage	I _{SD} =50A, V _{GS} =0V	—	0.9	1.3	V
I _S ³	Diode Continuous Forward Current		—	—	97	A
t _{rr}	Reverse Recovery Time	I _S =50A,	—	45	—	nS
Q _{rr}	Reverse Recovery Charge	dI/dt=100A/us	—	65	—	nC
Dynamic Characteristics ²						
C _{iss}	Input Capacitance	V _{GS} =0V, V _{DS} =50V Frequency=1MHz	—	3175	—	pF
C _{oss}	Output Capacitance		—	440	—	
C _{rss}	Reverse Transfer Capacitance		—	268	—	
t _{d(on)}	Turn-On Delay Time	V _{DS} =40V, I _D =50A, V _{GS} =10V,(Note1,4)	—	49	—	nS
t _r	Rise Time		—	64	—	
t _{d(off)}	Turn-Off Delay Time		—	139	—	
t _f	Fall Time		—	48	—	
Gate Charge Characteristics ²						
Q _g	Total Gate Charge	V _{DS} =64V, I _D =50A, V _{GS} =10V,(Note1,4)	—	76	—	nC
Q _{gs}	Gate-to-Source Charge		—	21	—	
Q _{gd}	Gate-to-Drain Charge		—	24	—	

Note: 1: Pulse test; pulse width \leq 300us, duty cycle \leq 2%.

2: Guaranteed by design, not subject to production testing.

3: Package limitation current is 100A.Calculated continuous current based on maximum allowable junction temperature.

4: Repetitive rating, pulse width limited by max junction temperature.

5: Starting TJ = 25°C,L = 1mH,IAS = 25A.

Typical Characteristics




Figure 1. On Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On Resistance Variation vs. Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage Variation with Source Current and Temperature




Figure 5. Capacitance Characteristics






Figure 6. Gate Charge Characteristics

Typical Characteristics (continued)



**Figure 7. Breakdown Voltage Variation
vs Temperature**



**Figure 8. On-Resistance Variation
vs Temperature**





Figure 9. Maximum Safe Operating Area



**Figure 10. Maximum Drain Current
vs Case Temperature**






Figure 11. Transient Thermal Response Curve

Test Circuit

1) E_{AS} test Circuit



2) Gate charge test Circuit



3) Switch Time Test Circuit

