

## 3MHz, Rail-to-Rail I/O CMOS Op Amps

### Feature

- Stable 3MHz GBWP with Low  $I_Q$  of Only 480 $\mu$ A Typical per Amplifier
- Offset Voltage: +/-2mV Maximum
- High Slew Rate: 3.7V/ $\mu$ s
- Input Bias Current: 1pA Typical
- CMRR/PSRR:100dB/100dB
- Settling time to 0.1% with 2V Step: 0.46us
- Beyond the Rails Input Common-Mode Range
- Output Swing to within 10mV Typical of each Rail
- No Phase Reversal for Overdriven Inputs
- Supply Voltage Range: 2.1V to 5.5V
- -40°C to 125°C Operation Range
- Green, Popular Type Package

### General Description

The HT2358A is CMOS dual op-amps with low offset, stable high frequency response, low power, low supply voltage, and rail-to-rail inputs and outputs. HT2358A has a high gain-bandwidth product of 3MHz, 3.7V/ $\mu$ s slew rate while consuming only 480 $\mu$ A of supply current per amplifier. The maximum input offset voltage is 2mV for HT2358A. Beyond the rail input and rail-to-rail output characteristics allow the full power-supply voltage to be used for signal range. operating range is from 2.5V to 5.5V.

This combination of features makes the HT2358A superior among rail-to-rail input/output CMOS op amps in its power class. It is specified over the extended industrial temperature range -40 °C to +125°C.

The HT2358A can be used as cost-effective plug replacements for many commercially available op amps to reduce power and improve input/output range and performance.

### Applications

- Active Filters, ASIC Input or Output Amplifier
- Sensor Interface
- Smoke/Gas/Environment Sensors
- Portable Instruments and Mobile Device
- Audio Output
- PCMCIA Cards
- Battery or Solar Power Systems
- Medical Equipment
- Piezo Electrical Transducer Amplifier

## Absolute Maximum Ratings

(If out of these ratings, the filter may be fail or damaged)

Table 1

Symbol	parameter	rating	units
VDD	Power supply	6	V
T <sub>A</sub>	Operating ambient Temperature Range	-40~+125	°C
T <sub>STG</sub>	Storage Temperature	-65~+150	°C

## Recommended Operating Conditions

Table 2

Symbol	parameter	rating	units
VDD	Power supply	2.5~5.5	V
T <sub>A</sub>	Operating ambient Temperature Range	-40~+125	°C




## Electrical Characteristics

Specifications are at  $T_A=+27^\circ\text{C}$ ,  $VDD=5\text{V}$ ,  $V_{CM}=V_{OUT}=VDD/2$ ,  $RL=10\text{Kohm}$ ,  $CL=100\text{pF}$

Symbol	Parameter	Spec			Units
		Min	Typ	Max	
VCC	Operating Supply Voltage	2.5	5	5.5	V
Vos	Input Offset Voltage	-2	+/-0.6	+2	mV
Vos_TC	Input Offset voltage Temp Drift		1.6		$\mu\text{V}/^\circ\text{C}$
en	Input Voltage Noise Density: f=1KHz		25		nV/VHz
CIN	Input Capacitance	Differential	1.5		pF
		Common Mode	3.0		
RIN	Input Resistance	>100			GΩ
IQ	Quiescent Current per Amplifier		480	790	uA
Iout	Output Current		50		mA
Vin_cm	Common mode Input voltage	0		VDD-0.1	V
Vol	Output Voltage from supply Swing		10		mV
CMRR	Common Mode Rejection Ratio		100		dB
Isc	Output short-circuit current		80		mA
PM	Phase Margin		65		°
GM	Gain Margin		-10		dB
GBWP	Gain-Bandwidth Product		3		MHz
PSRR	Power supply rejection ratio: 1Hz 1KHz		100 72		dB
ts	Settling time, 1.5V to 3.5V, Unity Gain: 0.1%		0.46		μs
SR	Slew Rate		3.7		μs

## Typical performance characteristics

At  $T_A=+27^\circ\text{C}$ ,  $V_{dd}=5\text{V}$ ,  $V_{CM}=V_{OUT}=\text{VDD}/2$   $RL=10\text{Kohm}$   $CL=100\text{pF}$



## PAD Definition




Fig 2. Pad definition of HT2358A

Table 7. Pad definition

Name	I/O	Analog/Digital	Description
INP	I	A	Non-Inverting Input of Amplifier. Voltage range of this pin can go from 0 to VDD.
GND	GROUND	GROUND	Ground pin. Connect to the most negative supply, ALL GND pads are connected on die.
INN	I	A	Inverting Input of Amplifier. This pin has same voltage range as INP.
OUT	O	A	Amplifier Output. The voltage range extends to within millivolts of each supply rail.
VDD	POWER	POWER	Power supply (5V) ,connect to positive voltage supply

## Application Circuits







Fig.3 Applications Circuits of HT2358A



**(DIP8)**

**NOTES:**

- Dimensions "A", "B" do not include mold flash or protrusions.

Maximum mold flash or protrusions 0.25 mm (0.010) per side.



	Dimension, mm	
Symbol	MIN	MAX
<b>A</b>	8.51	10.16
<b>B</b>	6.1	7.11
<b>C</b>		5.33
<b>D</b>	0.36	0.56
<b>F</b>	1.14	1.78
<b>G</b>		2.54
<b>H</b>		7.62
<b>J</b>	$0^\circ$	$10^\circ$
<b>K</b>	2.92	3.81
<b>L</b>	7.62	8.26
<b>M</b>	0.2	0.36
<b>N</b>	0.38	

**(SOP8)**


	Dimension, mm	
Symbol	MIN	MAX
<b>A</b>	4.8	5
<b>B</b>	3.8	4
<b>C</b>	1.35	1.75
<b>D</b>	0.33	0.51
<b>F</b>	0.4	1.27
<b>G</b>		1.27
<b>H</b>		5.72
<b>J</b>	$0^\circ$	$8^\circ$
<b>K</b>	0.1	0.25
<b>M</b>	0.19	0.25
<b>P</b>	5.8	6.2
<b>R</b>	0.25	0.5

**NOTES:**

- Dimensions A and B do not include mold flash or protrusion.
- Maximum mold flash or protrusion 0.15 mm (0.006) per side for A; for B - 0.25 mm (0.010) per side.