

## 8CH Darlington Sink Driver

The HT62083A&HT62084A are high-voltage, high-current darlington drivers comprised of eight NPN darlington pairs.


All units feature integral clamp diodes for switching indicative loads.

Application include relay, hammer, lamp and display (LED) drivers.


### Features

- Output current (single output)  
500mA (Max)
- Output clamp diodes
- Inputs compatible with various types of logic

TYPE	INPUT BASE RESISTOR	DESIGNATION
HT62083AN/ARW	2.7kΩ	TTL, 5V CMOS
HT62084AN/ARW	10.5kΩ	6~15V PMOS, CMOS




**Pin Configuration  
(top view)**




**Block Schematics**

**HT62083A**



**HT62084A**



Note: The input and output parasitic diodes cannot be used as clamp diodes.

## Maximum Ratings

T<sub>a</sub> =25°C

Parameter	Symbol	Limit Values		Unit
		min.	max.	
Output Sustaining Voltage	V <sub>CE(SUS)</sub>	-0.5	50	V
Output Current	I <sub>OUT</sub>	500		mA/ch
Input Voltage	V <sub>IN</sub>	-0.5	30	V
Clamp Diode Reverse Voltage	V <sub>R</sub>	50		V
Clamp Diode Forward Current	I <sub>F</sub>	500		mA
Power Dissipation	HT62083AN	1.47		W
	HT62083ADW	0.96		
Operating Temperature	T <sub>opr</sub>	-40	85	°C
Storage Temperature	T <sub>stg</sub>	-55	150	°C

\* Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## Recommended Operating Conditions

(T<sub>a</sub>=-40~85°C)

Parameter	Symbol	Test Condition	Limit Value			Unit
			Min	Typ	Max	
Output Sustaining Voltage	V <sub>CE(SUS)</sub>		0	-	50	V
Output Current	I <sub>OUT</sub>	N	T <sub>pw</sub> =25ms,Duty=10%, 8 Circuits	0	-	347
			T <sub>pw</sub> =25ms,Duty=50%, 8 Circuits	0	-	123
		DW	T <sub>pw</sub> =25ms,Duty=10%, 8 Circuits	0	-	268
			T <sub>pw</sub> =25ms,Duty=50%, 8 Circuits	0	-	90
Input Voltage	V <sub>IN</sub>		0	-	30	V
Input Voltage (Output On)	HT62083A	V <sub>IN(ON)</sub>		3.5	-	30
				8	-	30
Clamp Diode Reverse Voltage	V <sub>R</sub>		-	-	50	V
Clamp Diode Forward Current	I <sub>F</sub>		-	-	400	mA
Power Dissipation	N	P <sub>D</sub>		-	-	0.52
				-	-	0.4

**Electrical Characteristics**


Ta = 25°C

Parameter		Symbol	Test Circuit	Test Condition		Limit Values			Unit
						Min	Typ	Max	
Output Leakage Current	HT62083A	I <sub>CEx</sub>	1	V <sub>CE</sub> =50V	Ta=25°C	-	-	50	uA
				V <sub>CE</sub> =50V	Ta=85°C	-	-	100	
	HT62084A			V <sub>CE</sub> =50V	V <sub>IN</sub> =1V	-	-	500	
Collector-Emitter Saturation Voltage		V <sub>CE(sat)</sub>	2	I <sub>OUT</sub> =350mA, I <sub>IN</sub> =500um		-	1.3	1.6	V
				I <sub>OUT</sub> =200mA, I <sub>IN</sub> =350um		-	1.1	1.3	
				I <sub>OUT</sub> =100mA, I <sub>IN</sub> =250um		-	0.9	1.1	
Input Current	HT62083A	I <sub>IN(ON)</sub>	2	V <sub>IN</sub> =3.85V		-	0.93	1.35	mA
				V <sub>IN</sub> =5V		-	0.35	0.5	
	HT62084A			V <sub>IN</sub> =12V		-	1.0	1.45	
Input Voltage (Output On)	HT62083A	V <sub>IN(ON)</sub>	5	V <sub>CE</sub> =2V, I <sub>OUT</sub> =200mA		-	-	2.4	V
				V <sub>CE</sub> =2V, I <sub>OUT</sub> =250mA		-	-	2.7	
				V <sub>CE</sub> =2V, I <sub>OUT</sub> =300mA		-	-	3.0	
				V <sub>CE</sub> =2V, I <sub>OUT</sub> =125mA		-	-	5.0	
				V <sub>CE</sub> =2V, I <sub>OUT</sub> =200mA		-	-	6.0	
				V <sub>CE</sub> =2V, I <sub>OUT</sub> =275mA		-	-	7.0	
	HT62084A			V <sub>CE</sub> =2V, I <sub>OUT</sub> =350mA		-	-	8.0	
DC Current Transfer Ratio		h <sub>FE</sub>	2	V <sub>CE</sub> =2V, I <sub>OUT</sub> =350mA		1000	-	-	
Clamp Diode Reverse Current		I <sub>R</sub>	6	Ta=25°C (Note)		-	-	50	uA
				Ta=85°C (Note)		-	-	100	
Clamp Diode Forward Voltage		V <sub>F</sub>	7	I <sub>F</sub> =350mA		-	-	2.0	V
Input Capacitance		C <sub>IN</sub>	-			-	-	15	pF
Turn-On Delay		t <sub>ON</sub>	8	R <sub>L</sub> =125Ω, V <sub>OUT</sub> =50V		-	0.1	-	us
Turn-Off Delay		t <sub>OFF</sub>	8	R <sub>L</sub> =125Ω, V <sub>OUT</sub> =50V		-	0.21	-	us


 Note : V<sub>R</sub>=V<sub>RMAX</sub>

## Test Circuit


1.  $I_{CEX}$




2.  $V_{CE}(\text{sat}), h_{FE}$




3.  $I_{IN}(\text{ON})$




4.  $I_{IN}(\text{OFF})$




5.  $V_{IN}(\text{ON})$





6.  $I_R$



7.  $V_F$



### 8. $t_{ON}$ , $t_{OFF}$



Note 1 : Pulse Width 50us, Duty Cycle 10%  
 Output Impedance  $50\Omega$ ,  $t_r \leq 5\text{ns}$ ,  $t_f \leq 10\text{ns}$   
 Note 2 : See below.





### Input Condition




Type number	R1	$V_{IH}$
HT62083A	$0\Omega$	3V
HT62084A	$0\Omega$	8V

Note 3 :  $C_L$  includes probe and jig capacitance

### Precautions for Using

Utmost care is necessary in the design of output line, COMMON and GND line since IC may be destroyed due to short-circuit between outputs, air contaminaton fault, or fault by improper grounding.


**HT62083AN**
**IIN vs VIN**

**HT62084A**
**IIN vs VIN**

**IOUT vs DUTY CYCLE**

**IOUT vs VCE (sat)**





### Package Dimensions

DIP-18

Unit: mm



**SOP-18**


SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	—	—	2.70
A1	0.10	—	0.28
A2	2.25	2.30	2.35
A3	0.97	1.02	1.07
b	0.35	—	0.44
b1	0.34	0.37	0.39
c	0.26	—	0.31
c1	0.24	0.25	0.26
D	11.25	11.45	11.65
E	10.10	10.30	10.50
E1	7.30	7.50	7.70
e	1.27BSC		
L	0.70	—	1.00
L1	1.40BSC		
θ	0	—	8°
L/F载体尺寸 (mil)	140*160		