All-In-One Single-coil Fan drivers

Since 2000 MELEXIS has been INNOVATING in the fan market offering QUALITIVE and COST EFFECTIVE fandrivers



"With the expansion of its single coil fandriver family Melexis continues to offer its advance design capabilities in hall sensing and motor control to the benefit of the fandriver market."

INNOVATION

- Soft start and soft switching for low acoustic noise
- Integrated reverse polarity protection, avoids the need for protection diode, and allows smaller decoupling capacitor
- All-In-One single coil fandriver with PWM control in straight leads SOIC8 package
- Wettable flanks QFN package allows assembly using standard optical inspection (no XRAY required)

QUALITY

- AECQ-100 compliant
- 100% production tested at two temperatures
- Qualified to automotive standard including Automotive PPAP
- State of the art protection against ESD and EOS

COST

- Single layer pcb, even half size pcb possible.
- Low BOM cost: Minimum discrete components
 - Integrated high sensitive hall sensor,
 - Integrated reverse polarity protection diode.
- One IC fits all:
 - Configurable speed curve
 - High drive strength up to 600mA
 - Standardized pcb / stator design, from 40mm to 120mm fans



Layout example : Half size single layer pcb

Picture :

Melexis straight leads PWM Single coil fandriver on a single layer pcb *(on the left)*.

Compared to a TSSOP16 competitor with external straight leads SOT hall element (on the right). Motor control

Pressure Sensors

Wireless ICs

Hall Effect ICs And Sensors

> Optoelectronii Sensors

InfraRed Sensors

Pressure Sensors

Wireless ICs

Hall Effect ICs And Sensors

oelectronic Sensors

Sensor Interface ICs

InfraRed Sensors



Target Applications



Game consoles



White goods



Automotive: LED headlamp, Battery cooling, VGA

| Quick Reference | MLX90287 | MLX90297 | |
|---------------------|--------------|----------------|--|
| Minimum speed | Configurable | Configurable | |
| Speed curve | Fixed | Configurable | |
| Average Fan current | < 450 mA | < 600 mA | |
| Current limiting | No | Yes | |
| Soft start | Yes | Yes | |
| Soft switching | Yes | Yes | |
| Reverse polarity | Built-in | External diode | |
| Supply voltage | [4.5, 18] | [3.3, 18] | |
| ESD—HBM | 6kV | 9kV | |

| Order code (*) | Grade | Package | FG/RD | Current Limit | |
|--|---------------------|--------------------------|-------|---------------|--|
| MLX90287KZC-AAA000-RX | Industrial/Consumer | ZC: Straight leads SOIC8 | FG | n/a | |
| MLX90287LZC-AAA000-RX | Automotive | ZC: Straight leads SOIC8 | FG | n/a | |
| MLX90287LLD-AAA000-RX | Automotive | DFN10 3*3mm | FG | n/a | |
| MLX90297KZC-AAA008-RX | Industrial/Consumer | ZC: Straight leads SOIC8 | FG | Yes | |
| MLX90297KZC-ABA008-RX | Industrial/Consumer | ZC: Straight leads SOIC8 | RD | Yes | |
| MLX90297KLD-AAA009-RX | Industrial/Consumer | DFN10 3*3mm | FG | Yes | |
| (*) More order code options available. Please contact your sales representative for more information | | | | | |

For additional information email info@melexis.com

or go to our website at: www.melexis.com

(*) More order code options available. Please contact your sales representative for more information.

