



Electric Double Layer Capacitor

(EDLC/Super Capacitor)

EDLC262520 Series

EDLC262520-501-2F-40

500mF

Electric Double Layer Capacitor (EDLC/Super Capacitor)

Product compatible with RoHS directive

Overview of EDLC262520 Series

FEATURES


- ☐ High capacitance and low impedance.
- ☐ Thin small size.
- ☐ Long-life.
- ☐ Clean materials.
- ☐ Safety.

APPLICATION

- ☐ Battery assistance
- ☐ Storage element of energy harvesting
- ☐ Strong LED flash
- ☐ Backup application for instantaneous power failures

Part Number Construction

EDLC	26	25	20	-	501	-	2F	-	40
Series name	Thickness dimensionst	Width dimensions W	Vertical dimensions L (Not including the lead length)		Data capacity (mF)		Number of series and voltage		Impedance
					351 350				




☐ RoHS Directive Compliant Product: See the following for more details. <https://product.tdk.com/info/en/environment/rohs/index.html>


Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use.
Please note that the contents may change without any prior notice due to reasons such as upgrading.

EDLC262520 Series

PRODUCT INDICATION



SHAPE & DIMENSIONS



Dimensions in mm



EDLC262520 Series

ELECTRICAL CHARACTERISTICS

CHARACTERISTICS SPECIFICATION TABLES

Part No.	Nominal capacitance	Nominal impedance [AC 1kHz]	Operating voltage	
	(mF)typ.	(mΩ)typ.	continuous (V)	peak (V)
EDLC262520-501-2F-40	500	35	4.2	5.5

EXAMPLE OF THERMAL CHARACTERISTICS



- The graph of THERMAL CHARACTERISTICS mentioned above shows the typical behavior of the product, and does not show the guarantee values.
- It is a value for standard temperature 25°C.

TEMPERATURE RANGE

Part No.	Temperature range	
	Operating temperature (°C)	Storage temperature (°C)
EDLC262520-501-2F-40	-30 to +70°C	-40 to +85°C