



# **Test Procedure for the NCP161FCT2GEVB Evaluation Board**

There is a collection test procedures for NCP160 demoboards. This paper offers some helpful test configuration for first contact with ONSEMI NCP160 LDO.

## 1. QUIESCENT CURRENT



Figure 1: Test configuration for measurement I<sub>Q</sub>, Quiescent Current

- 1. Connect circuit as shown figure on 1
- 2. Apply voltage at V<sub>Input</sub> Default test V<sub>input</sub> is V<sub>out\_nom</sub>+1 V or 2.5 V whichever is greater
- 3. Value shown  $\mu A$  meter is measured quiescent current.
- 4. Measurement is finished. Disconnect supply voltage.

\**Note – Be carefully if any device is connected on output, because leakage current can affect measurement accuracy.* 

**ON Semiconductor®** 



#### 2. LOAD REGULATION



Figure 2: Test configuration for measurement REG<sub>LOAD</sub>, Load Regulation

- 1. Connect circuit as shown figure on 2
- 2. Apply voltage at V<sub>Input.</sub> Default test V<sub>input</sub> is V<sub>out\_nom</sub>+1 V or 2.5 V whichever is greater
- 3. Set minimal required current  $I_1$ , e.g. 1 mA, and switch load ON.
- 4. Note the value V1 from voltmeter Vo.
- 5. Switch load OFF and set maximal required current I2, e.g. 250 mA and switch load ON.
- 6. Note the value V2 from voltmeter Vo.
- 7. Load regulation is obtained via following formula:  $REG_{LOAD} = (V_1 V_2), [V]$
- 8. Measurement is finished. Disconnect supply voltage.

**ON Semiconductor®** 



### 3. LINE REGULATION



Figure 3: Test configuration for measurement REG<sub>LINE</sub>, Line Regulation

- 1. Connect circuit as shown on figure 3
- 2. Set load to the required current e.g. 10 mA
- 3. Set minimal input voltage  $V_{II}$ ,  $V_{OUT_NOM}$ +1V or 2.5V whichever is greater
- 4. Note the value  $V_{I1}$  and  $V_{O1}$ .
- 5. Set maximal input voltage  $V_{12} = 5.5 \text{ V}$
- 6. Note the value  $V_{I2}$  and  $V_{O2}$ .
- 7. Load regulation is obtained via following formula:  $\text{REG}_{\text{LINE}} = (V_{01} V_{02})/(V_{11} V_{12})$ , [V/V]
- 8. Measurement is finished. Disconnect supply voltage.

**ON Semiconductor®** 



#### 4. ENABLE START-UP



Figure 4: Test configuration for measurement enables response

- 1. Connect circuit as shown on figure 4
- 2. Set generator to SQUARE PULSE,  $0.9 \le \text{AMPLITUDE} \le V_{\text{IN}}$ , FREQUENCY=10Hz, DUTY=10%
- 3. Apply voltage at V<sub>Input.</sub> Default test V<sub>input</sub> is V<sub>out\_nom</sub>+1 V or 2.5 V whichever is greater
- 4. Set required I<sub>OUT</sub>, e.g. 10 mA
- 5. Connect oscilloscope to EN signal and VOUTPUT.
- 6. Watch enable response of the regulator after asserting EN pin.
- 7. Measurement is finished. Disconnect supply voltage.