

KA7552A/KA7553A SMPS Controller

Features

- Built-in drive circuits for direct connection power MOSFET (l_O = ±1.5A)
- Wide operating frequency range (5kHz ~ 600kHz)
- Pulse by pulse over current limiting
- Over load protection
- On/off control by external trigger
- Internal UVLO
- Low standby current (typ. 90uA)
- Soft start circuit

Description

The KA7552A/KA7553A are switching power control IC for wide operating frequency range. The internal circuits include pulse by pulse current limiting, protection, on/off control by external trigger, low standby current, soft start, and high current totempole output for driving a POWER MOSFET. Maximum duty of the KA7552A is 70% and the KA7553A is 46%. When duty is maximum, the input threshold voltage of pin2 & pin8 are not same in KA7552A and KA7553A.





Internal Block Diagram

Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Supply voltage	Vcc	30	V
Output current	lo	±1.5	A
Input voltage at overcurrent detection pin	VIN(IS)	-0.3 to 4	V
Input voltage at FB pin	VIN(FB)	4	V
Input current at CS pin	lin(CS)	2	mA
Total power dissipation (Ta = 25°C)	PD	800	mW
Operating temperature	TOPR	-25 to 85	°C
Storage temperature range	TSTG	-65 to 150	°C
Junction temperature	Tj	+125	°C

Electrical Characteristics

(VCC = 18V, FOSC = 135kHz, TA = 25° C, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit	
OSCILLATOR SECTION		I					
Initial accuracy	Fosc	CT = 360pF, TJ = 25°C	125	135	145	kHz	
Frequency variation 1	$\Delta F / \Delta V$	Vcc = 10V to 30V	-	±1	±3	%	
Frequency variation 2 ^(Note1)	$\Delta F / \Delta V$	T _A = 25°C to 85°C	-	±1.5	-	%	
Ramp high voltage	VRH	CT = 360pF, TJ = 25°C	2.80	3.08	3.30	V	
Ramp low voltage	VRL	CT = 360pF, TJ = 25°C	0.6	0.9	1.2	V	
Amplitude	Vosc	VPIN7, peak to peak	1.80	2.18	2.50	V	
PULSE WIDTH MODULATION SECTION							
Input threshold voltage(pin2)	VTH(FBD)	Duty cycle = 0%	0.6	0.75	0.95	V	
Input threshold voltage(pin2) ^(Note1)	VTH(FB1) (KA7552)	Duty cycle = Dmax 1	2.1	2.3	2.6	V	
	VTH(FB2) (KA7553)	Duty cycle = Dmax 2	1.6	1.8	2.1	V	
Max. duty cycle	D(Max1) (KA7552)	-	66	70	74	%	
	D _(Max2) (KA7553)	-	43	46	49	%	
Source current(pin2)	ISOURCE(FB)	VPIN2 = 0V	-660	-800	-960	uA	
OVERCURRENT LIMIT SECTION				•	•		
Input threshold voltage	VTH(IS)	-	0.21	0.24	0.27	V	
Source current(pin3)	ISOURCE(IS)	VPIN3 = 0V	-300	-200	-100	uA	
Deley time ^(Note1)	TD	-	-	150	-	ns	
SOFT START SECTION							
Charging current	ICHG	VPIN8 = 0V	-15	-10	-5	uA	
Input threshold voltage(pin8)	VTH(CSO)	-	0.7	0.9	1.1	V	
Input threshold voltage(pin8) ^(Note1)	VTH(CS1) (KA7552)	Duty cycle = Dmax 1	2.2	2.4	2.6	V	
	VTH(CS2) (KA7553)	Duty cycle = Dmax 2	1.7	1.9	2.1	V	
LATCH MODE SHUTDOWN CIRCUIT SECTION							
Sink current(pin8)	ISINK(CS)	VPIN8 = 6V, VPIN2 = 1V	25	45	65	uA	
Shutdown threshold voltage	VTH(SD,CS)	-	6.7	7.2	7.7	V	
OVERLOAD SHUTDOWN SECTION							
Shutdown threshold voltage	VTH(SD,FB)	-	2.6	2.8	3.1	V	

Electrical Characteristics (Continued)

(VCC = 18V, FOSC = 135kHz, TA = 25°C, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit	
UNDER VOLTAGE LOCKOUT SECTION							
Start-up threshold voltage	VTH(ST)	-	15.5	16.0	16.5	V	
Minimum operating voltage	VOPR(Min)	-	8.20	8.70	9.20	V	
Hysteresis	VHYS	-	6.40	7.30	8.20	V	
ON/OFF CONTROL SECTION							
Source current(pin8)	ISOURCE(CS)	VPIN8 = 0V	-15	-10	-5	uA	
On threshold voltage	VTH(ON)	VPIN8 : OFF->ON	0.45	0.56	0.70	V	
Off threshold voltage	VTH(OFF)	VPIN8 : ON -> OFF	0.30	0.42	0.55	V	
OUTPUT SECTION							
Low output voltage	Vol	IO = 100mA, VCC = 18V	-	1.3	1.8	V	
High output voltage	Voh	I _O = -100mA, V _{CC} = 18V	16.0	16.5	18.0	V	
Rise time ^(Note1)	T _R	No load	-	50	-	ns	
Fall time ^(Note1)	TF	No load	-	50	-	ns	
OVERALL							
Stand-by current	ISB	Vcc = 14V	-	90	150	uA	
Operating current	ICC(OPR)	VPIN2 = 0V	-	9	15	mA	
Power supply current off	ICC(OFF)	VPIN8 = 0V	-	1.1	1.8	mA	
Power supply current shutdown	ICC(SD)	VPIN8 = 7.6V	-	1.1	1.8	mA	

Note :

1. These parameters, although guaranteed, are not 100% tested in production.

2. Recommend operating condition :

- Vcc(min) = 12V
- RT = $3.3k\Omega \sim 10k\Omega$
- Oscillation frequency = 5kHz ~ 600kHz
- Soft start capacitor(Cs) = 0.1uF ~ 1uF

Mechanical Dimensions

Package

Dimensions in millimeters



Ordering Information

Product Number	Package	Operating Temperature
KA7552A	8-DIP	-25 ~ +85°C
KA7553A	0-011	

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative