

# NZ9F2V4ST5G, SZNZ9F2V4ST5G SERIES

## Zener Voltage Regulators

### 250 mW SOD-923 Surface Mount

This series of Zener diodes is packaged in a SOD-923 surface mount package. They are designed to provide voltage regulation protection and are especially attractive in situations where space is at a premium. They are well suited for applications such as cellular phones, hand held portables, and high density PC boards.

#### Specification Features

- Standard Zener Breakdown Voltage Range -2.4 V to 18 V
- Steady State Power Rating of 250 mW
- Small Body Outline Dimensions:  
0.039" x 0.024" (1.00 mm x 0.60 mm)
- Low Body Height: 0.016" (0.40 mm)
- ESD Rating of Class 3 (>16 kV) per Human Body Model
- Tight Tolerance  $V_Z$
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These are Pb-Free Devices

#### Mechanical Characteristics

**CASE:** Void-free, transfer-molded, thermosetting plastic  
Epoxy Meets UL 94, V-0

**LEAD FINISH:** 100% Matte Sn (Tin)

**MOUNTING POSITION:** Any

**QUALIFIED MAX REFLOW TEMPERATURE:** 260°C

Device Meets MSL 1 Requirements

#### MAXIMUM RATINGS

Rating	Symbol	Max	Unit
Total Device Dissipation FR-5 Board, (Note 1) @ $T_A = 25^\circ\text{C}$ Derate above 25°C	$P_D$	250 2.0	mW mW/°C
Thermal Resistance from Junction-to-Ambient	$R_{\theta JA}$	500	°C/W
Junction and Storage Temperature Range	$T_J, T_{stg}$	-65 to +150	°C



Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. FR-4 Minimum Pad.




ON Semiconductor®

<http://onsemi.com>



SOD-923  
CASE 514AB

#### MARKING DIAGRAM



- X = Specific Device Code
  - M = Month Code
  - = Pb-Free Package
- (Note: Microdot may be in either location)

#### ORDERING INFORMATION

Device	Package	Shipping†
NZ9FxxxST5G, SZNZ9FxxxST5G	SOD-923 (Pb-Free)	8000/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### DEVICE MARKING INFORMATION

See specific marking information in the device marking column of the Electrical Characteristics table on page 3 of this data sheet.

# NZ9F2V4ST5G, SZNZ9F2V4ST5G SERIES

## ELECTRICAL CHARACTERISTICS

( $T_A = 25^\circ\text{C}$  unless otherwise noted,  
 $V_F = 0.9\text{ V Max. @ } I_F = 10\text{ mA}$  for all types)

Symbol	Parameter
$V_Z$	Reverse Zener Voltage @ $I_{ZT}$
$I_{ZT}$	Reverse Current
$Z_{ZT}$	Maximum Zener Impedance @ $I_{ZT}$
$I_{ZK}$	Reverse Current
$Z_{ZK}$	Maximum Zener Impedance @ $I_{ZK}$
$I_R$	Reverse Leakage Current @ $V_R$
$V_R$	Reverse Voltage
$I_F$	Forward Current
$V_F$	Forward Voltage @ $I_F$
$\Theta V_Z$	Maximum Temperature Coefficient of $V_Z$
C	Max. Capacitance @ $V_R = 0$ and $f = 1\text{ MHz}$



Figure 1. Zener Voltage Regulator




Figure 2. Steady State Power Derating

## NZ9F2V4ST5G, SZNZ9F2V4ST5G SERIES

**ELECTRICAL CHARACTERISTICS** ( $V_F = 0.9$  Max @  $I_F = 10$  mA for all types)

Device***	Device Marking	Zener Voltage VZ		Test Current Izt mA	$Z_{ZT}$ $I_Z = I_{ZT}$ @ 10% Mod $\Omega$ Max	$Z_{ZK}$ $I_Z = 1.0$ mA $\Omega$ Max	$I_{ZK}$ mA	Max IR @ VR		$dV_Z/dt$ (mV/k) @ $I_{ZT1} = 5$ mA		CpF Max @ $V_R = 0$ $f = 1$ MHz
		Min	Max					$\mu$ A	V	Min	Max	
SZ, NZ9F2V4ST5G	2*	2.43	2.63	5	100	1000	1	50	1	-3.5	0	210
SZ, NZ9F2V7ST5G	3*	2.67	2.91	5	100	1000	1	20	1	-3.5	0	210
SZ, NZ9F3V0ST5G	4*	2.94	3.26	5	100	1000	1	10	1	-3.5	0	210
SZ, NZ9F3V3ST5G	5*	3.32	3.53	5	100	1000	1	10	1	-3.5	0	210
SZ, NZ9F3V6ST5G	6*	3.6	3.85	5	100	1000	1	10	1	-3.5	0	210
SZ, NZ9F3V9ST5G	A**	3.89	4.16	5	100	1000	1	5	1	-3.5	-2.5	210
SZ, NZ9F4V3ST5G	D**	4.17	4.43	5	100	1000	1	5	1	-3.5	0	210
SZ, NZ9F4V7ST5G	E**	4.55	4.75	5	100	800	0.5	2	1	-3.5	0.2	150
SZ, NZ9F5V1ST5G	F**	4.989	5.2	5	80	500	0.5	2	1.5	-2.7	1.2	130
SZ, NZ9F5V6ST5G	J**	5.49	5.73	5	60	200	0.5	1	2.5	-2.0	2.5	115
SZ, NZ9F6V2ST5G	K**	6.06	6.33	5	60	100	0.5	1	3	0.4	3.7	110
SZ, NZ9F6V8ST5G	L**	6.65	6.93	5	40	60	0.5	0.5	3.5	1.2	4.5	105
SZ, NZ9F7V5ST5G	P**	7.28	7.6	5	30	60	0.5	0.5	4	2.5	5.3	100
SZ, NZ9F8V2ST5G	Q**	8.02	8.36	5	30	60	0.5	0.5	5	3.2	6.2	90
SZ, NZ9F9V1ST5G	R**	8.85	9.23	5	30	60	0.5	0.5	6	3.8	7	80
SZ, NZ9F10VST5G	T**	9.77	10.21	5	30	60	0.5	0.1	7	4.5	8	80
SZ, NZ9F11VST5G	V**	10.76	11.22	5	30	60	0.5	0.1	8	5.4	9	80
SZ, NZ9F12VST5G	Y**	11.74	12.24	5	30	80	0.5	0.1	9	6	10	80
SZ, NZ9F13VST5G	2**	12.91	13.49	5	37	80	0.5	0.1	10	7	11	75
SZ, NZ9F15VST5G	3**	14.34	14.98	5	42	80	0.5	0.1	11	9.2	13	70
SZ, NZ9F16VST5G	4**	15.85	16.51	5	50	80	0.5	0.1	12	10.4	14	65
SZ, NZ9F18VST5G	5**	17.56	18.35	5	50	80	0.5	0.1	14	12.4	16	60


\*Rotated 90°.

\*\*Rotated 180°.

\*\*\*SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.


# MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS

ON Semiconductor®




STYLE 1      STYLE 2


SCALE 8:1



TOP VIEW




SIDE VIEW



BOTTOM VIEW

### SOLDERING FOOTPRINT\*



DIMENSIONS: MILLIMETERS

SOD-923  
CASE 514AB  
ISSUE D

DATE 03 SEP 2020

#### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
5. DIMENSION L WILL NOT EXCEED 0.30mm.

DIM	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.34	0.37	0.40	0.013	0.015	0.016
b	0.15	0.20	0.25	0.006	0.008	0.010
c	0.07	0.12	0.17	0.003	0.005	0.007
D	0.75	0.80	0.85	0.030	0.031	0.033
E	0.55	0.60	0.65	0.022	0.024	0.026
HE	0.95	1.00	1.05	0.037	0.039	0.041
L	0.19 REF			0.007 REF		
L2	0.05	0.10	0.15	0.002	0.004	0.006

### GENERIC MARKING DIAGRAM\*



STYLE 1

STYLE 2

X = Specific Device Code  
M = Date Code

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present.

STYLE 1: PIN 1. CATHODE (POLARITY BAND)  
          2. ANODE  
STYLE 2: NO POLARITY

See Application Note AND8455/D for more mounting details

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	98AON23284D	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	SOD-923, 1.0X0.6X0.37, MAX HEIGHT 0.40	PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Email Requests to: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**onsemi Website:** [www.onsemi.com](http://www.onsemi.com)

### TECHNICAL SUPPORT

**North American Technical Support:**

Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

**Europe, Middle East and Africa Technical Support:**

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative