


MUR405 THRU MUR4100

ULTRA FAST RECTIFIERS

Reverse Voltage - 200 to 600 Volts Forward Current - 4.0 Amperes

DO-201AD



Dimensions in inches and (millimeters)

FEATURES

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Ultra fast switching for high efficiency
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed:
250°C/10 seconds, 0.375" (9.5mm) lead length,
5 lbs. (2.3kg) tension

MECHANICAL DATA

Case: JEDEC DO-201AD molded plastic body
Terminals: Plated axial leads, solderable per MIL-STD-750, Method 2026
Polarity: Color band denotes cathode end
Mounting Position: Any
Weight: 0.04 ounce, 1.10 grams

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.
 Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

MDD Catalog Number	SYMBOLS	MUR405	MUR410	MUR415	MUR420	MUR440	MUR460	MUR480	MUR4100	UNITS	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	150	200	400	600	800	1000	VOLTS	
Maximum RMS voltage	V_{RMS}	35	70	105	140	280	420	550	700	VOLTS	
Maximum DC blocking voltage	V_{DC}	50	100	150	200	400	600	800	1000	VOLTS	
Maximum average forward rectified current 0.375" (9.5mm) lead length	$I_{(AV)}$	4.0								Amps	
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	150								Amps	
Maximum instantaneous forward voltage at 4.0A	V_F	0.875			1.25		1.85			Volts	
Maximum DC reverse current at rated DC blocking voltage $T_A=25^\circ\text{C}$ $T_A=150^\circ\text{C}$	I_R	2.0 50.0			5.0 150.0					μA	
Maximum reverse recovery time (NOTE 1)	t_{rr}	25			25-50					ns	
Typical thermal resistance (NOTE 2)	$R_{\theta JA}$	27.0			50.0					$^\circ\text{C/W}$	
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +175									$^\circ\text{C}$


Note: 1. Reverse recovery condition $I_F=0.5\text{A}, I_R=1.0\text{A}, I_{rr}=0.25\text{A}$

2. Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length, P.C.B. mounted

RATINGS AND CHARACTERISTIC CURVES MUR405 THRU MUR4100


AVERAGE FORWARD RECTIFIED CURRENT, AMPERES

FIG. 1- FORWARD CURRENT DERATING CURVE




PEAK FORWARD SURGE CURRENT, AMPERES

FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




INSTANTANEOUS FORWARD CURRENT, AMPERES

FIG. 3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS



INSTANTANEOUS REVERSE CURRENT, MICROAMPERES

FIG. 4-TYPICAL REVERSE CHARACTERISTICS



JUNCTION CAPACITANCE, pF

FIG. 5-TYPICAL JUNCTION CAPACITANCE

