



X3025 WR S- XX D-LP SW XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category :
- ③ W-wafer
- ④ Welding Board Angle: R-90°
- ⑤ Welding Way: S-SMT
- ⑥ Row No.-Pin No. XX-Single row
- ⑦ Special NO.
- ⑧ D-Solder Tabs
- ⑨ Material : LP-LCP 94V-0
- ⑩ Planting Category: V**All Gold-Plated G**Gold-Plated Contact *01-Gold Flash ; *02-2U" ; *03-3U" ; *05-5U" *10-10U" ; *15-15U" ; *30-30U" ; *50-50U" SN1-Bright tin plating 70U" SN1-Bright tin plating 120U" Min. ; SW-Fog Tin plating
- ⑪ Color: Blank-natural color

Poles	Dimensions		
	A	B	C
2	6.85	3.00	14.20
3	9.85	6.00	17.20
4	12.85	9.00	20.20
5	15.85	12.00	23.20
6	18.85	15.00	26.20
7	21.85	18.00	29.20
8	24.85	21.00	32.20
9	27.85	24.00	35.20
10	30.85	27.00	38.20
11	33.85	30.00	41.20
12	36.85	33.00	44.20

■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20m Ω
- Mark "*"Indicate Dimensions Need To Controlled In Emphasis

X3025WRS-XXD-LPG15	LCP UL 94V-0	Brass	Contact Area Gold 15u" Min.	Brass	Tin-Plated	X3025H
X3025WRS-XXD-LPSW	LCP UL 94V-0	Brass	Tin Plating Fog	Brass	Tin-Plated	X3025H
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Mates With XK B Housing

广东星坤科技股份有限公司
P.C.B. LAYOUT

生效日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	DSND	DATE	SCALE: N/A	MODEL TYPE:
				DWN	DATE	VIEW:	X3025WRS-XXD-LPXXX
				CHKD	DATE	UNIT: mm/in	PART NO.: 3.00 mm Crimp Style Connectors
				APPD	DATE	SIZE: A4	DWG NO.:
UNSPECIFIED TOLERANCES				XKB INDUSTRIAL PRECISION CO. LIMITED			WEIGHT SHEET REVISION