

Description

The PESDWC9D5VB protects sensitive semiconductor components from damage or upset due to electrostatic discharge (ESD) and other voltage induced transient events. They feature large cross-sectional area junctions for conducting high transient currents, offer desirable electrical characteristics for board level protection, such as fast response time, low operating voltage. It gives designer the flexibility to protect one bi-directional line in applications where arrays are not practical.



Feature

- \rightarrow 40W peak pulse power per line ($t_P = 8/20\mu s$)
- SOD-923 package
- Replacement for MLV(0402)
- Bidirectional configurations
- Response time is typically < 1ns</p>
- High ESD protection
- Low clamping voltage
- RoHS compliant

Applications


- Cellular phones
- Portable devices
- Digital cameras
- Power supplies

Mechanical Characteristics

- Lead finish:100% matte Sn(Tin)
- Mounting position: Any
- Qualified max reflow temperature:260°C
- Device meets MSL 1 requirements
- ➤ Pure tin plating: 7 ~ 17 um
- Pin flatness:≤3mil

Electronics Parameter

Symbol	Parameter		
V_{RWM}	Peak Reverse Working Voltage		
I _R	Reverse Leakage Current @ V _{RWM}		
V_{BR}	Breakdown Voltage @ I⊤		
lτ	Test Current		
Ірр	Maximum Reverse Peak Pulse Current		
Vc	Clamping Voltage @ I _{PP}		
P _{PP}	Peak Pulse Power		
Сл	Junction Capacitance		
lF	Forward Current		
VF	Forward Voltage @ I _F		



Electrical characteristics per line@25°C (unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Peak Reverse Working Voltage	V _{RWM}				5	V
Breakdown Voltage	V _{BR}	It = 1mA	5.6	6.7	7.8	V
Reverse Leakage Current	I _R	V _{RWM} = 5V T=25°C			1.0	μΑ
Clamping Voltage	Vc	I _{PP} =1A			9	V
Junction Capacitance	Cj	V _R =0V f = 1MHz		3		pF

Absolute maximum rating@25℃

Rating	Symbol	Value	Units
Peak Pulse Power (t _p =8/20µs)	P _{pp}	40	W
Operating Temperature	TJ	-55 to 150	°C
Storage Temperature	T _{STG}	-55 to 150	℃

Typical Characteristics




Fig 1.Pulse Waveform






Fig 2.Power Derating Curve









Fig 4. Non Repetitive Peak Pulse Power vs. Pulse time

Solder Reflow Recommendation




Remark: Pb free for 260°C; Pb for 245°C.


PCB Design

For TVS diodes a low-ohmic and low-inductive path to chassis earth is absolutely mandatory in order to achieve good ESD protection. Novices in the area of ESD protection should take following suggestions to heart:


- > Do not use stubs, but place the cathode of the TVS diode directly on the signal trace.
- Do not make false economies and save copper for the ground connection.
- Place via holes to ground as close as possible to the anode of the TVS diode.
- Use as many via holes as possible for the ground connection.
- Keep the length of via holes in mind! The longer the more inductance they will have.

Product dimension (SOD-923)





Dim	Inc	hes	Millimeters		
	MIN	MAX	MIN	MAX	
Α	0.030	0.033	0.75	0.85	
В	0.022	0.026	0.55	0.65	
С	0.037	0.041	0.95	1.05	
D	0.014	0.017	0.36	0.43	
Е	0.006	0.010	0.15	0.25	
F	0.002	0.006	0.05	0.15	
Н	0.003	0.007	0.07	0.17	



Suggested PCB Layout

Marking information



Ordering information

Device	Package	Shipping
PESDWC9D5VB	SOD-923 (Pb-Free)	8000 / Tape & Reel

IMPORTANT NOTICE

 and Prisemi are registered trademarks of Prisemi Electronics Co., Ltd (Prisemi) ,Prisemi reserves the right to make changes without further notice to any products herein. Prisemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Prisemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in Prisemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Prisemi does not convey any license under its patent rights nor the rights of others. The products listed in this document are designed to be used with ordinary electronic equipment or devices, Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

Website: http://www.prisemi.com
For additional information, please contact your local Sales Representative.

©Copyright 2009, Prisemi Electronics

Prisemi is a registered trademark of Prisemi Electronics.

All rights are reserved.