



## Features

- 1.2V ~ 5.5V Operating Voltage Range
- Ultra-low On-Resistance:
  - $R_{DS(ON)} = 50\text{m}\Omega$  at  $V_{IN}=5.5\text{V}$
  - $R_{DS(ON)} = 67\text{m}\Omega$  at  $V_{IN}=3.3\text{V}$
  - $R_{DS(ON)} = 110\text{m}\Omega$  at  $V_{IN}=1.8\text{V}$
  - $R_{DS(ON)} = 230\text{m}\Omega$  at  $V_{IN}=1.2\text{V}$
- Continuous Output Current up to 1.5A
- Output Auto-Discharge
- Active High Enable Control
- WLCSP4, 0.76mm × 0.76mm with 0.4mm Pitch

## Applications


- Mobile Phones
- Tablets
- Digital Cameras
- GPS
- Portable Devices

## Description

The LP5240 is an advanced load switch in an ultra-small package. The internal P-type MOSFET and the slew rate control make it easy to use. An output discharge path is integrated to the external components and simplify the design.


Thanks to the current optimization, LP5240 is suitable for ultra-low current consumption application to save energy. It operates over a wide input voltage range from 1.2V to 5.5V. The device contains a soft-start function to reduce the input inrush current when it is turned on.

The LP5240 is available in a 4-pin WLCSP4 package with 0.4mm pin pitch.




WLCSP4  
0.4mm pin pitch  
0.76 × 0.76 mm<sup>2</sup>

## Ordering Information



## Typical Application Circuit





## Marking Information

Device	Marking	Package	Shipping
LP5240HVF	LPS C6X	WLCSP4	3K/REEL
Marking indication:			
C6: Internal code, X: Production week			




## Pin Configuration



## Pin Description

Pin No.	Name	Description
A1	OUT	Load switch output
A2	IN	Load switch input
B1	GND	Ground
B2	EN	Active high enable input

## Functional Block Diagram





## Absolute Maximum Ratings (Note 1)

- IN to GND ----- -0.3V to 8V
- EN to GND ----- -0.3V to 8V
- OUT to GND ----- -0.3V to ( $V_{IN}$ +0.3V)
- Maximum Junction Temperature ( $T_J$ ) ----- 125°C
- Operating Ambient Temperature Range ( $T_A$ ) ----- -40°C to 85°C
- Maximum Soldering Temperature (At leads, 10 sec) ----- 260°C

\*Note 1: Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

## Thermal Information

- Maximum Power Dissipation ( $P_D$ ,  $T_A \leq 25^\circ\text{C}$ ) ----- 400mW
- Thermal Resistance ( $\theta_{JA}$ ) (Note 2) ----- 150°C/W

\*Note 2: Measured using 2S2P JEDEC standard PCB with ambient temperature  $< 25^\circ\text{C}$

## Electro-Static Discharge and Latch-up

- HBM (Human Body Model, JEDEC JS-001) ----- 8000V
- CDM (Charged Device Model, JEDEC JS-002) ----- 1000V
- MM (Machine Model, JESD22-A115C) ----- 200V
- Latch-Up (Latch-up, JEDEC Standard JESD78E) -----  $\pm 200\text{mA}$

## Recommended Operating Conditions

Characteristics	Symbol	Conditions	Min	Max	Units
Input and power supply	$V_{IN}$		1.2	5.5	V
Maximum dc current	$I_{OUT}$			1.5	A
Maximum peak current	$I_{PEAK}$	Effective Duration $< 1\text{ms}$		2	A
Ambient Temperature Range	$T_A$		-40	85	°C
Decoupling input capacitor	$C_{IN}$		0.1		μF
Decoupling output capacitor	$C_{OUT}$		0.1		μF



## Electrical Characteristics

The parameters are measured under conditions  $V_{IN} = 1.2V$  to  $5.5V$ ,  $C_{IN} = C_{OUT} = 1\mu F$ ,  $T_A = 25^\circ C$ , unless otherwise specified.

Parameter	Symbol	Test Conditions	Min	Typ.	Max	Units
On resistance	$R_{DS(ON)}$	$V_{IN}=5.5V$ , $I_{OUT}=200mA$		50	65	$m\Omega$
		$V_{IN}=3.3V$ , $I_{OUT}=200mA$		67	85	$m\Omega$
		$V_{IN}=1.8V$ , $I_{OUT}=200mA$		110	140	$m\Omega$
		$V_{IN}=1.2V$ , $I_{OUT}=200mA$		230	280	$m\Omega$
Output discharge resistance	$R_{DIS}$	$V_{IN}=3.3V$ , $V_{EN}=0V$		70	110	$\Omega$
EN pull-down resistor	$R_{PD}$			6.5		$M\Omega$
EN logic high voltage	$V_{IH}$	$1.2V \leq V_{IN} \leq 5.5V$	0.8			$V$
EN logic low voltage	$V_{IL}$	$1.2V \leq V_{IN} \leq 5.5V$			0.4	$V$
Input quiescent current	$I_Q$	$V_{IN} = 4.2V$ , $V_{EN} = 3V$ , No load		180	240	$nA$
		$V_{IN} = 5.5V$ , $V_{EN} = 3V$ , No load		190	250	
Input standby current	$I_{STB}$	$V_{IN} = 4.2V$ , $V_{EN} = 0V$ , No load		180	240	$nA$
		$V_{IN} = 5.5V$ , $V_{EN} = 0V$ , No load		190	250	
Switch shutdown leakage current	$I_{SD}$	$V_{IN} = 4.2V$ , $V_{EN} = 0V$ , $V_{OUT} = 0V$ , $T_A = -40^\circ C$ to $85^\circ C$		50	580	$nA$
		$V_{IN} = 5.5V$ , $V_{EN} = 0V$ , $V_{OUT} = 0V$ , $T_A = -40^\circ C$ to $85^\circ C$		65	600	
Enable time <sup>(Note 3)</sup>	$t_{EN}$	$V_{IN}=3.6V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=25\Omega$		170		$\mu s$
		$V_{IN}=5.0V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=25\Omega$		220		$\mu s$
Output rising time <sup>(Note 3)</sup>	$t_R$	$V_{IN}=3.6V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=25\Omega$		140		$\mu s$
		$V_{IN}=5.0V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=25\Omega$		160		$\mu s$
Disable time <sup>(Note 3)</sup>	$t_{DIS}$	$V_{IN}=3.6V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=25\Omega$		4		$\mu s$
		$V_{IN}=5.0V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=25\Omega$		4		$\mu s$
Output falling time <sup>(Note 3)</sup>	$t_F$	$V_{IN}=3.6V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=5\Omega$		14		$\mu s$
		$V_{IN}=3.6V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=25\Omega$		55		$\mu s$
		$V_{IN}=3.6V$ , $C_{OUT}=1\mu F$ , $R_{LOAD}=100\Omega$		100		$\mu s$

\*Note 3: The time period indicated by each parameter is defined as Figure 1.



## Timing Diagram




Figure 1. Timing diagram by EN pin toggled

## Typical Waveforms




Figure 2. Turn on with EN pin  
( $C_{IN}=1\mu F$ ,  $C_{OUT}=1\mu F$ ,  $V_{IN}=3.6V$ ,  $R_{LOAD}=25\Omega$ )




Figure 3. Turn off with EN pin  
( $C_{IN}=1\mu F$ ,  $C_{OUT}=1\mu F$ ,  $V_{IN}=3.6V$ ,  $R_{LOAD}=25\Omega$ )



## Typical Characteristics




Figure 4. Quiescent Current vs Voltage  
(C<sub>IN</sub>=C<sub>OUT</sub>=1μF, T<sub>A</sub>=25°C)




Figure 5. Quiescent Current vs Temperature  
(C<sub>IN</sub>=C<sub>OUT</sub>=1μF)




Figure 6 R<sub>ON</sub> vs Voltage  
(C<sub>IN</sub>=C<sub>OUT</sub>=1μF, T<sub>A</sub>=25°C)




Figure 7 R<sub>ON</sub> vs Temperature  
(C<sub>IN</sub>=C<sub>OUT</sub>=1μF)



## Function Description

### Enable Function

The LP5240 is a single channel load switch in an ultra-small WLCSP package with 1.5A current capability. The device contains a high side, low resistance P-Type MOSFET. The integrated slew rate control makes it suitable for applications that need to limit the input inrush current.

### Enable Function

The EN pin is an active high Logic input pin that is compatible with 1.2V control logic. The internal pass element is turned off when EN pin is tied low.

### Auto Discharge

The LP5240 has a quick discharge function. When the device is disabled, a discharge resistor is connected between OUT and GND. The resistance is 70Ω (typical).

### Soft Start

The device includes a soft-start function in order to limit the input in-rush current and voltage ringing when the EN pin is pulled to a logic high.

## Application Information

### Capacitors consideration

External capacitors on IN and OUT are recommended in application, 0.1μF at least. Closer placement of the capacitors to the device, both IN and OUT, would be better for stability.

### Power Dissipation

The internal power dissipation from the power MOSFET, when it is turned on, is the main source of junction temperature rising. In this case, the power dissipation and the junction temperature in conducting mode can be calculated as following:

$$P_D = R_{DS(ON)} \times (I_{OUT})^2$$

P<sub>D</sub>: Power Dissipation (W)

R<sub>DS(ON)</sub>: Power MOSFET on resistance (Ω)

I<sub>OUT</sub>: Output current (A)

$$T_J = P_D \times \theta_{JA} + T_A$$

T<sub>J</sub>: Junction temperature (°C)

θ<sub>JA</sub>: Package thermal resistance (°C /W) <sup>(Note 4)</sup>


T<sub>A</sub>: Ambient temperature (°C)

**\*Note 4: The calculation base on thermal resistance is only valid in Lab condition. The value of θ<sub>JA</sub> could change in customer PCB environment.**



## Package Dimensions

WLCSP4, 0.76mm x 0.76mm



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Contacts	N		4	
Adjacent Column X-Pitch	E1	0.400	BSC	
Adjacent Row Y-Pitch	D1	0.400	BSC	
Overall Height	A	0.570	0.600	0.630
Die Height	A2	0.387	0.400	0.413
Bump Height	A1	0.180	0.200	0.220
Overall Length	E	0.735	0.755	0.775
Overall Width	D	0.735	0.755	0.775
Ball Diameter	b	0.240	0.260	0.280