




PJ78L05SQ-N

3-Terminal Voltage Regulator

Features

- Input voltage: up to 35V
- Output: 5V
- Output current up to 100 mA, internal thermal overload protection and short-circuit current limiting.

SOT-89




1. OUT 2. GND 3. IN

Marking Code : 78L05

Absolute Maximum Ratings

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	Value	Unit
Input Voltage	V_I	35	V
Output Current	I_O	100	mA
Junction Temperature	T_J	150	°C
Storage Temperature Range	T_{STG}	-55 to +150	°C





Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.


Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit
Output Voltage	V _O	V _I =10V, I _O =40mA	4.85	5.0	5.15	V
		I _O =1mA to 40mA, V _I =7V to 25V	4.8	--	5.2	V
		I _O =1mA to 100mA	4.75	--	5.25	V
Line Regulation	△V _O	V _I =7V to 25V, T _J =25°C	--	18	75	mV
		V _I =8V to 25V, T _J =25°C	--	10	54	mV
Load Regulation	△V _O	I _O =1mA to 100mA, T _J =25°C	--	20	60	mV
		I _O =1mA to 40 mA, T _J =25°C	--	5	30	mV
Ripple Rejection	R _R	V _I =8V to 16V, f=100Hz, T _J =25°C	47	62	--	dB
Quiescent Current	I _Q		--	3.75	6	mA
Quiescent Current Change	△I _Q	V _I =8V to 25V	--	--	1.0	mA
		I _O =1mA to 40mA	--	--	0.3	mA
Output Noise Voltage	V _N	10Hz≤f≤100KHz, T _J =25°C	--	40	--	μV



Package Outline

SOT-89

Dimensions in mm



Ordering Information

Device	Package	Shipping
PJ78L05SQ-N	SOT-89	3,000PCS/Reel&13inches