





## Features

- Advanced trench process technology
- High Density Cell Design For Ultra Low On-Resistance
- High Power and Current handing capability

SOT-23-6



Schematic Diagram



## Absolute Maximum Ratings

Ratings at  $T_C = 25^\circ\text{C}$  unless otherwise specified.

Parameter	Symbol	Maximum	Units
Drain-Source Voltage	$V_{DS}$	20	V
Gate-Source Voltage	$V_{GS}$	$\pm 12$	V
Continuous Drain Current	$I_D$	5	A
Pulsed Drain Current <sup>Note1</sup>	$I_{DM}$	25	A
Power Dissipation	$P_D$	1.25	W
Junction and Storage Temperature Range	$T_J, T_{STG}$	150, -55 to 150	$^\circ\text{C}$

## Thermal Characteristics

Parameter	Symbol	Typ.	Units
Maximum Junction-to-Ambient <sup>Note2</sup>	$R_{\theta JA}$	100	$^\circ\text{C/W}$



## Electrical Characteristics

T<sub>c</sub> = 25°C unless otherwise specified.

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
<b>Static Parameters</b>						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	I <sub>D</sub> =250μA, V <sub>GS</sub> =0V	20	--	--	V
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =20V, V <sub>GS</sub> =0V	--	--	1	μA
Gate-Body Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> =0V, V <sub>GS</sub> =±12V	--	--	±100	nA
Gate Threshold Voltage <sup>Note3</sup>	V <sub>GS(th)</sub>	V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> = 250μA	0.5	0.7	1.2	V
Static Drain-Source On-Resistance <sup>Note3</sup>	R <sub>DS(ON)</sub>	V <sub>GS</sub> =2.5V, I <sub>D</sub> =4A	--	25	32	mΩ
		V <sub>GS</sub> =4.5V, I <sub>D</sub> =5A	--	20	25	mΩ
Forward Transconductance <sup>Note3</sup>	g <sub>FS</sub>	V <sub>DS</sub> =5V, I <sub>D</sub> =5A	--	10	--	S
<b>Dynamic Parameters</b>						
Input Capacitance	C <sub>iss</sub>	V <sub>GS</sub> =0V, V <sub>DS</sub> =10V, f=1MHz	--	550	--	pF
Output Capacitance	C <sub>oss</sub>		--	125	--	pF
Reverse Transfer Capacitance	C <sub>rss</sub>		--	64	--	pF
<b>Switching Parameters</b>						
Total Gate Charge	Q <sub>g</sub>	V <sub>GS</sub> =4.5V, V <sub>DS</sub> =10V, I <sub>D</sub> =5A	--	9.5	--	nC
Gate Source Charge	Q <sub>gs</sub>		--	2.1	--	nC
Gate Drain Charge	Q <sub>gd</sub>		--	1.4	--	nC
Turn-On Delay Time	t <sub>D(on)</sub>	V <sub>GS</sub> =4V, V <sub>DD</sub> =10V, I <sub>D</sub> =5A R <sub>GEN</sub> =10Ω	--	9	--	ns
Turn-On Rise Time	t <sub>r</sub>		--	10	--	ns
Turn-Off Delay Time	t <sub>D(off)</sub>		--	32	--	ns
Turn-Off Fall Time	t <sub>f</sub>		--	24	--	ns
<b>Source-Drain Diode Parameters</b>						
Body Diode Forward Voltage	V <sub>SD</sub>	I <sub>s</sub> =5A, V <sub>GS</sub> =0V	--	0.8	1.2	V
Body Diode Continuous Source Current	I <sub>s</sub>		--	--	5	A

Notes: 1. Repetitive rating: pulsed width limited by maximum junction temperature.







2. Surface Mounted on FR4 Board, t ≤ 10 sec.

3. Pulse width ≤ 300μs, duty cycle ≤ 2%



# PJ8205 N-Channel Power MOSFET





## Electrical Characteristics Curves





# PJ8205

## N-Channel Power MOSFET








## Package Outline

SOT-23-6

Dimensions in mm



## Ordering Information

Device	Package	Shipping
PJ8205	SOT-23-6	3000/Reel&Tape(7inch)