

# US1A THRU US1M

## SURFACE MOUNT ULTRAFAST RECOVERY RECTIFIER

Reverse Voltage - 50 to 1000 V

Forward Current - 1 A

### FEATURES

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Easy to pick and place
- High efficiency
- Lead free in comply with EU RoHS 2011/65/EU directives

### MECHANICAL DATA

- Case: SMAF
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 27mg / 0.00095oz

### PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Top View  
Marking Code: US1A~US1M  
Simplified outline SMAF and symbol

### Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	US1A	US1B	US1D	US1G	US1J	US1K	US1M	Units					
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	50	100	200	400	600	800	1000	V					
Maximum RMS voltage	$V_{RMS}$	35	70	140	280	420	560	700	V					
Maximum DC Blocking Voltage	$V_{DC}$	50	100	200	400	600	800	1000	V					
Maximum Average Forward Rectified Current at $T_c = 125^\circ C$	$I_{F(AV)}$	1							A					
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	$I_{FSM}$	30							A					
Maximum Instantaneous Forward Voltage at 1 A	$V_F$	1.0		1.3		1.65		V						
Maximum DC Reverse Current $T_a = 25^\circ C$ at Rated DC Blocking Voltage $T_a = 125^\circ C$	$I_R$	5 100							$\mu A$					
Maximum Reverse Recovery Time <sup>(1)</sup>	$t_{rr}$	50			75			ns						
Typical Junction Capacitance <sup>(2)</sup>	$C_J$	15							pF					
Typical Thermal Resistance <sup>(3)</sup>	$R_{\theta JA}$	80							$^\circ C/W$					
Operating and Storage Temperature Range	$T_J, T_{stg}$	-55 ~ +150							$^\circ C$					


( 1 ) Measured with  $I_F = 0.5 A$ ,  $I_R = 1 A$ ,  $I_{rr} = 0.25 A$ .

( 2 ) Measured at 1 MHz and applied reverse voltage of 4 V D.C


( 3 ) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.

# US1A THRU US1M


**Fig.1 Forward Current Derating Curve**




**Fig.2 Typical Reverse Characteristics**




**Fig.3 Typical Forward Characteristics**



**Fig.4 Maximum Non-Repetitive Peak Forward Surge Current**




**Fig.5 Typical Junction Capacitance**



# US1A THRU US1M

## PACKAGE OUTLINE

Plastic surface mounted package; 2 leads



## The recommended mounting pad size

