


SOD-323



### SOD-323 Plastic-Encapsulate Schottky Barrier Diode

#### 特征 Features

- 大电流承受能力。High Current Capability
- 正向压降低。Low Forward Voltage Drop

#### 机械数据 Mechanical Data

- 封装: SOD-323 封装 SOD-323 Small Outline Plastic Package
- 极性: 色环端为负极 Polarity: Color band denotes cathode end
- 安装位置: 任意 Mounting Position: Any

极限值和温度特性(TA = 25°C 除非另有规定)

**Maximum Ratings & Thermal Characteristics** (Ratings at 25°C ambient temperature unless otherwise specified.)





参数 Parameters	符号 Symbol	KRB551V-40-7-F	单位 Unit
最大可重复峰值反向电压 Maximum repetitive peak reverse voltage	VRRM	40	V
最大均方根电压 Maximum RMS voltage	VRMS	28	V
最大直流阻断电压 Maximum DC blocking voltage	VDC	40	V
最大正向平均整流电流 Maximum average forward rectified current	IFM	350	mA
峰值正向浪涌电流 8.3ms 单一正弦半波 Peak forward surge current 8.3 ms single half sine-wave	IFSM	1.5	A
功率消耗 Power Dissipation	PD	200	mW
典型热阻 T Typical thermal resistance	R <sub>θJA</sub>	500	°C/W
工作结温 Operating junction temperature	T <sub>j</sub>	125	°C
存储温度 Storage temperature range	T <sub>STG</sub>	-50~+150	°C

电特性 (TA = 25°C 除非另有规定)

**Electrical Characteristics** (Ratings at 25°C ambient temperature unless otherwise specified).

参数 Parameters	符号 Symbol	测试条件 Test conditions	KRB551V-40-7-F	单位 Unit
最大正向电压 Maximum forward voltage	V <sub>F</sub>	IF = 20mA IF = 200mA	0.370 0.600	V
最大反向电流 Maximum reverse breakdown voltage	VR	IR=100uA	40	V
最大反向电流 Maximum reverse current	IR	VR=30V	5.0	uA
典型结电容 Type junction capacitance	C <sub>j</sub>	VR =0V, f = 1MHz	50	pF
反向恢复时间 Reverse recovery time	T <sub>rr</sub>	IF=IR=200mA, I <sub>rr</sub> =0.1×IR,RL=100 Ω	10	ns


### 特性曲线Characteristic Curves



### SOD-323 PACKAGE OUTLINE

Plastic surface mounted package

**SOD-323**



Symbol	Min.(mm)	Max.(mm)
<b>A</b>		1.000
<b>A1</b>	0.000	0.100
<b>A2</b>	0.800	0.900
<b>b</b>	0.250	0.350
<b>c</b>	0.080	0.150
<b>D</b>	1.200	1.400
<b>E</b>	1.600	1.800
<b>E1</b>	2.500	2.700
<b>L</b>	0.475REF	
<b>L1</b>	0.250	0.400
<b>θ</b>	0°	8°