







REV.	ECN NO.	REVISED	DATE




工程部  
2020-01-04  
LQ. HUANG


PCB Layout Diagram  
Top View

UNLESS OTHERWISE SPECIFIED TOLERANCES		<b>MYOUNG 美阳</b> <a href="http://www.meiyangdz.com">www.meiyangdz.com</a>	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND YangFeng	DATE 2020-01-04
WEIGHT: g		CHKD ZhouRuicai	DATE 2020-01-04
SHEET 1 OF 1		APVD XueShunyong	DATE 2020-01-04
TITLE:		SCALE:	VIEW:
PART NO.:		SIZE: A4	REV.: A/0
DRAW NO.:MY-CP-0220		UNIT: mm	OBJECT: MY

1	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20mm	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR



产品




圆孔


封带

载带

标签



Detail A




出料方向


余留封带长: 330 MIN  
载带与封带剥离  
剥离角度: 165°-180°  
剥离强度: 0.1-1.0N  
(200mm/min)

剥离方向


15空穴 共封装 350 只产品 330MIN 15空穴  
末端留空穴载带 前端留空穴载带





6盘



塑料袋



外箱



Detail A

技术要求:

1. 圆孔十个孔距离累计允许公差为±0.2mm
2. 带长250mm内容许弯曲度1mm
3. 材料厚度以在载带边缘测量为准
4. 所有尺寸定义依循EIA-481-C系准则定义之
5. 材料: 黑色PS T=0.5mm
6. 所有卷轮为灰蓝挖空旋转塑胶卷轮
7. 整模成型长度: 9.12M,
8. 非指明公差范围为: ±0.1mm; 超过250mm不计算累计误差
9. 型腔外形凡未标明处倒角R为0.2-0.3; 拔模斜度未标注的为3° 以下

包装信息:

- 1、每卷盘装产品 350 只, 卷盘外侧贴相关标签;
- 2、每 6 卷盘放在一个塑料袋中;
- 3、每外箱装6盘, 产品总数: 2100 只;
- 4、外箱上下用胶纸封成“工”字;
- 5、净重: \*\* KG, 毛重: \*\* KG。



UNLESS OTHERWISE SPECIFIED TOLERANCES		<b>MYOUNG 美阳</b> <a href="http://www.meiyangdz.com">www.meiyangdz.com</a>			
DECIMALS: X : ±*** X.X : ±*** X.XX : ±*** X.XXX : ±***	ANGLES: X : ±*** X.X : ±***	DSND	YangFeng	DATE	2020-12-14
		CHKD	ZhouRuicai	DATE	2020-12-14
		APVD	XueShun Yong	DATE	2020-12-14
WEIGHT:		SCALE:	SIZE: A4	VIEW:	
SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY	TITLE: 电池扣CR2032-B DIP 卷装
		PART NO.: MY-2032-19-R			DRAW NO.:MY-BD-0041