



LNTK4003M3T5G

S-LNTK4003M3T5G

30 V, 0.56 A, Single, N-Channel,
Gate ESD Protection

1. FEATURES

- Low gate voltage threshold(VGS(th))to facilitate drive circuit design
- Low gate charge for fast switching
- ESD protected gate
- Minimum breakdown voltage rating of 30 V
- We declare that the material of product compliance with RoHS requirements and Halogen Free.
- S- prefix for automotive and other applications requiring unique site and control change requirements; AEC-Q101 qualified and PPAP capable.



2. APPLICATIONS

- Level shifters
- Level switches
- Low side load switches
- Portable applications

3. DEVICE MARKING AND ORDERING INFORMATION

Device	Marking	Shipping
LNTK4003M3T5G	KM	8000/Tape&Reel

4. MAXIMUM RATINGS(Ta = 25°C)

Parameter	Symbol	Limits	Unit
Drain-Source Voltage	VDSS	30	V
Gate-to-Source Voltage – Continuous	VGS	±20	V
Current (Note 1) Steady State	ID	0.5 0.37	A
Continuous Drain Current (Note 1) t<10s	TA = 25°C TA = 85°C	0.56 0.4	
Pulsed Drain Current(tp=10μs)	IDM	1.7	A
Continuous Source Current (Body Diode)	IS	1	A
Maximum Power Dissipation(Note 1) Steady State t<5s	PD	0.44 0.55	W
Junction and Storage temperature	TJ,Tstg	-55 ~ +150	°C
Maximum Temperature for Soldering Purposes	TL	260	°C

5. THERMAL CHARACTERISTICS

Parameter	Symbol	Limits	Unit
Thermal Resistance, Junction-to-Ambient Steady State(Note 1) $t = 5\text{s}$ (Note 1)	$R_{\Theta JA}$	280 228	$^{\circ}\text{C/W}$

6. ELECTRICAL CHARACTERISTICS ($T_a = 25^{\circ}\text{C}$)

OFF CHARACTERISTICS

Characteristic	Symbol	Min.	Typ.	Max.	Unit
Drain–Source Breakdown Voltage ($V_{GS} = 0$, $ID = 100\mu\text{A}_{\text{dc}}$)	$V(BR)_{DSS}$	30	-	-	Vdc
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V(BR)_{DSS}/T_J$	-	40	-	$\text{mV/}^{\circ}\text{C}$
Zero Gate Voltage Drain Current ($V_{DS}=30\text{V}$, $V_{GS}=0\text{V}$)	ID_{SS}	-	-	1.0	μA_{dc}
Gate–Body Leakage Current, Forward ($V_{DS} = 0 \text{ V}$, $V_{GS} = \pm 10 \text{ V}$)	IG_{SS}	-	-	± 1.0	μA_{dc}

ON CHARACTERISTICS (Note 2)

Gate Threshold Voltage ($V_{DS} = V_{GS}$, $ID = 250\mu\text{A}_{\text{dc}}$)	$V_{GS(\text{th})}$	0.8	-	1.6	Vdc
Negative Threshold Temperature Coefficient	$V_{GS(\text{TH})}/T_J$	-	3.4	-	$\text{mV/}^{\circ}\text{C}$
Static Drain–Source On–State Resistance ($V_{GS} = 4.0 \text{ V}$, $ID = 10 \text{ mA}$) ($V_{GS} = 2.5 \text{ V}$, $ID = 10 \text{ mA}$)	$R_{DS(\text{on})}$	-	1 1.5	1.5 2	Ω
Forward Transconductance ($V_{DS} = 3.0 \text{ V}$, $ID = 10 \text{ mA}$)	g_{fs}	-	0.33	-	S

DYNAMIC CHARACTERISTICS

Input Capacitance ($V_{GS} = 0 \text{ V}$, $f = 1.0\text{MHz}$, $V_{DS} = 5 \text{ V}$)	C_{iss}	-	41	-	pF
Output Capacitance ($V_{GS} = 0 \text{ V}$, $f = 1.0\text{MHz}$, $V_{DS} = 5 \text{ V}$)	C_{oss}	-	12	-	pF
Reverse Transfer Capacitance ($V_{GS} = 0 \text{ V}$, $f = 1.0\text{MHz}$, $V_{DS} = 5 \text{ V}$)	C_{rss}	-	8.1	-	pF

SWITCHING CHARACTERISTICS

Turn-On Delay Time	($V_{GS} = 4.5 \text{ V}$, $V_{DD} = 5.0 \text{ V}$, $ID = 0.1 \text{ A}$, $RG = 50\Omega$)	$td(\text{on})$	-	16.7	-	ns
Rise Time		tr	-	47.9	-	
Turn-Off Delay Time		$td(\text{off})$	-	65.1	-	
Fall Time		tf	-	64.2	-	

SOURCE–DRAIN DIODE CHARACTERISTICS





Forward Voltage ($V_{GS} = 0 \text{ Vdc}$, $ISD = 10 \text{ mA}_{\text{dc}}$)	V_{SD}	-	0.65	0.7	V
Reverse Recovery Time ($V_{GS} = 0 \text{ V}$, $dIS/dt = 8\text{A}/\mu\text{s}$, $IS = 10 \text{ mA}$)	tr_{rr}	-	14	-	ns

1. Surface-mounted on FR4 board using 1 in sq pad size


(Cu area = 1.127 in sq [1 oz] including traces).

2. Pulse Test: Pulse Width $\leq 300 \mu\text{s}$, Duty Cycle $\leq 2.0\%$.


7. ELECTRICAL CHARACTERISTICS CURVES




7. ELECTRICAL CHARACTERISTICS CURVES (Con.)



Source-to-Drain diode Forward Characteristics




Capacitance Variation



Diode Forward Characteristics

8.OUTLINE AND DIMENSIONS



Notes:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.

DIM	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.45	0.50	0.55	0.018	0.020	0.039
b	0.15	0.21	0.27	0.006	0.008	0.011
b1	0.25	0.31	0.37	0.010	0.012	0.015
C	0.07	0.12	0.17	0.003	0.005	0.007
D	1.15	1.20	1.25	0.045	0.047	0.049
E	0.75	0.80	0.85	0.030	0.031	0.033
e	0.40REF			0.016REF		
H _E	1.15	1.20	1.25	0.045	0.047	0.049
L	0.29REF			0.011REF		
L ₂	0.15	0.20	0.25	0.006	0.008	0.010

9.SOLDERING FOOTPRINT

